



Rated electric load: DC12V 50mA
 额定电负荷: DC12V 50mA
 Insulation resistance: $\geq 100\text{M}\Omega$ min(DC100v)
 绝缘电阻: $\geq 100\text{M}\Omega$ min(DC100V)
 Withstand voltage strength: AC100V (50/60Hz foy 1minute)
 耐压强度: AC100V (50/60Hz foy 1minute)
 Electrical life: 10000 cycles min
 电气寿命: 10000 cycles min
 Ambient temperature: $-10\text{ }^{\circ}\text{C} \sim +60\text{ }^{\circ}\text{C}$
 环境温度: $10\text{ }^{\circ}\text{C} \sim +60\text{ }^{\circ}\text{C}$
 Action force: $200\text{gf} \pm 100\text{gf}$
 力度: $200\text{gf} \pm 100\text{gf}$

D	Lid	1	SUS	Silvery white
C	Contact reed	2	Beryllium bronze	Silver/silvery white
B	Press handle	1	PA46	Black
A	Base	1	LCP/BRASS	Silver/black
Serial number	NAME	QUANTITY	Texture of material	Plating/colour

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP-33004
DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
ROCPCU TECHNOLOGY CO.,LTD				
<small>Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission</small>				