




NOTE :  
 Rating 额定功率: DC 12V 50mA  
 Operating Force 操作力: 200±100gf  
 Lifetime 寿命: 10,000 Cycles



ITEM	PAPT NAME	TER.NO	QTY	MATERIAL	FINISHING	REMARK
⑤	Terminal	8	8	Brass (0.30t)	ag Plated	
④	Contact spring	1	1	Phosphor branze	ag Plated	
③	Base	1	1	Pa46	Black	
②	Cover	1	1	Sus	Natural	
①	Keystake	1	1	Pa46	Black	

A4			
A3			
A2			
A1			
REV	DATE	REVISION DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP-3301L1
DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
<b>ROCPCU TECHNOLOGY CO.,LTD</b>				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				