



NOTE:  
 Rating:DC 30V 0.1A  
 Operating Force:30±10gf  
 Lifetime:100,000 Cycles  
 Operating Force:25±10gf



|               |                |          |                     |                |
|---------------|----------------|----------|---------------------|----------------|
| E             | Contact Spring | 1        | Phosphor Bronze     | Plating silver |
| D             | Terminal       | 4        | Phosphor Bronze     | Plating silver |
| C             | Base           | 1        | LCP                 |                |
| B             | Cover          | 1        | SUS                 | Natural        |
| A             | Keystake       | 1        | Nylon               |                |
| Serial number | NAME           | QUANTITY | Texture of material | Plating/colour |

|     |      |          |             |       |
|-----|------|----------|-------------|-------|
| A4  |      |          |             |       |
| A3  |      |          |             |       |
| A2  |      |          |             |       |
| A1  |      |          |             |       |
| REV | DATE | REVISION | DESCRIPTION | ISSUE |



COMMON TOLERANCE

|         |        |
|---------|--------|
| X.XX    | ± 0.10 |
| X.X     | ± 0.15 |
| X       | ± 0.25 |
| ANGULAR | —      |

|  |        |            |      |                      |
|--|--------|------------|------|----------------------|
| UNIT   | MM     | PROJECTED  |      | PRODUCT NAME:        |
| DRAWN BY   | FUYUAN | CHECKED BY | COCO | MODEL NO: TP-33108   |
| DATE   | 2019   | APPROVAL B | ALEN | Https: www.rocpcu.tw |
| <b>ROCPCU TECHNOLOGY CO.,LTD</b>   |        |            |      |                      |
| <small>Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission</small> |        |            |      |                      |