




LEFT SIDE VIEW




FRONT VIEW



BOTTOM VIEW




RIGHT SIDE VIEW




RECOMMENDED PCB LAYOUT VIEWED FROM COMPONENT SIDE


XKB Connectivity



TOP VIEW




BACK VIEW



LED Specification

Standard LED Color	LED Wavelength	Foward(A)	Foward(V)
Green	569nm	20mA	1.85-2.45V
Yellow	589nm	20mA	1.7-2.2V



XKB Connectivity

MATERIAL 材料:

HOUSING 外壳: PA46,UL94V-0,BLACK.  
 TERMINAL 端子: PHOSPHOR BRONZE, Ø=0.46MM,  
 GOLD PLATING ON CONTACT AREA.  
 SHIELD:C2680,T=0.20MM,20U" MIN NICKEL PLATING ON ALL AREA.

MECHANICAL 机械:

DURABILITY 耐用性: 750 CYCLES MIN.12.5MM/MINUTE  
 INSERTION FORCE 插入力: 2.2KG.F MAX  
 RETENTION STRENGTH 固位力: 7.7KG.F BETWEEN JACK AND PLUG  
 OPERATING TEMPERATURE 工作温度: -40°C~+85°C.  
 STORAGE TEMPERATURE 储存温度: -40°C~+85°C.  
 ALL CRITICAL DIMENSIONS WITH ""

ELECTRICAL 电动:

VOLTAGE 电压:125 VOLTS AC  
 CURRENT RATING 额定电流:1.5AMP  
 DIELECTRIC STRENGTH 介电强度:1000 VAC RMS 50HZ OR 60HZ,1MIN  
 INSULATION RESISTANCE 绝缘电阻:500 MEGA OHMS MIN.INITIAL  
 AFTER 500V DC FOR 1 MINUTE  
 CONTACT RESISTANCE 接触电阻:SINGLE TERMINAL 30 MILLIOHMS MAX  
 INITIAL 50 MILLIOHMS MAX.AFTER DURABILITY TEST

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	DSND	DATE	SCALE: N/A	MODEL TYPE: RJ JACK
Δx					ANGLAR ±5°	DWN	DATE	VIEW:	PART NO.:
Δx					L ≤ 4 ±0.2	CHKD	DATE	UNIT: mm/in	DWG NO.:
Δx					4 < L ≤ 16 ±0.3	APPD	DATE	SIZE: A4	X12ADAB1A3DY1027
Δx					16 < L ≤ 63 ±0.4	XKB INDUSTRIAL PRECISION CO.,LIMITED			
Δx					L > 63 ±0.5				
REVISIONS									
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn						1.0g 1/1 A0			