
POLYMER PTC RESETTABLE FUSE

TLC Electronic 亮 沃 电 子[®] 电路保护元器件专业制造商

Web: http://www.tlcet.com.cn

Product: Resettable Fuse Revision: F INDATE: 2020-08-18 Page No.: 1 OF 1

Part Number: TLC-MSMD260/12



2、 Electrical Characteristics

Part Number	I _H (A)	I _T (A)	V _{max} (V)	I _{max} (A)	T _{trij} (Max time Current(A)		$\begin{array}{c} Pd_{typ} \\ (W) \end{array}$	${f R}_{ m min} \ (\Omega)$	$\begin{array}{c} R1_{max} \\ (\Omega) \end{array}$
TLC-MSMD260/12	2.60	5.20	12	100	8.0	5.00	1.2	0.015	0.080

 $I_{\text{H}}:$ Holding Current: maximum current at which the device will not trip in 25°C still air.

 $I_T:$ Tripping Current minimum current at which the device will trip in 25 $^\circ\!\mathbb{C}$ still air.

 $V_{\mbox{\scriptsize max}}$: Maximum voltage device can withstand without damage at rated current.

I max: Maximum fault current device can withstand without damage at rated voltage.

 T_{trip} : Maximum time to trip(s) at assigned current.

Pd_{typ}: Rated working power.

 R_{min} : Minimum resistance of device prior to trip at 25°C.


R1 max: Maximum resistance of device is measured one hours post reflow at 25°C.


Noted: All electrical function test is conducted after PCB mounted.

3、Thermal Derating

TLC-MSMD260/12	Maximum ambient operating temperature									
	-40℃	-20℃	0°C	25℃	40°C	50℃	60℃	70℃	85℃	
Hold Current(A)	4.00	3.52	3.06	2.60	2.34	2.08	1.95	1.39	1.04	
Trip Current(A)	8.00	7.04	6.12	5.20	4.68	4.16	3.90	2.78	2.08	

4. Solder Reflow Recommendations





Notes: If reflow temperatures exceed the recommended

profile, devices may not meet the performance requirements.

5. Package Information

Packing quantity:1500PCS/Reel

Note:Reel packaging per EIA-481-1 standard

6. Agency Recognition:



Caution:Operation beyond the rated voltage or current may result in rupture electrical arcing or flame.Specifications are subject to change without notice.

TEL: 86-0769-3892 0554FAX: 86-0769-8793 2077E-mail:sales@tlcet.com.cnAddress:No.18,5th GaoLi Road, TangXia Town, DongGuan, GuangDong, P.R China 523710