







6	7	8
版本	变更内容	工程确认 日期



NOTES:

1. MECHANICAL:
MATING FORCE: 5-20N .
UNMATING FORCE: 8-20N .
DURABILITY: 10000 CYCLES MIN.

2. ELECTRICAL:
CURRENT: 5.0A MAX
VOLTAGE: 20V MAX
WITHSTANDING VOLTAGE: 100V AC
CONTACT RESISTANCE: 40 mΩ MAX INITIAL;
50 mΩ MAX AFTER 10000 CYCLES

3. ENVIRONMENTAL
OPERATING TEMPERATURE RANGE -30°C ~ +80°C

④	GND LATCH	1	STAINLESS STEEL	NICKEL PLATED OVERALL, TAB WITH LEAD FREE TIN ALLOY.
③	CONTACT	16	COPPER ALLOY	NICKEL UNDERPLATING OVER ALL, GOLD PLATING AT - CONTACT AREA. LEAD FREE TIN ALLOY AT TERMINATION.
②	SHELL	1	STAINLESS STEEL	CLEAN.
①	HOUSING	2	THERMOPLASTIC UL 94V-0	MOLDED COLOR:BLACK, white
NO.	DESCRIPTION	QTY.	MATERIAL	TREATMENT

一般公差加工参考表

Φ	单位	MM	比例
---	----	----	----

深圳市怡远科技有限公司			
YIYUAN TECH 0755-82784562			
设计	LUO JIE	品名	Type C 16p 公头 立式 贴片 H=11.94
审核	ROGER LI	图号	YTC-TC16S-128
核准	ROC CHAO	版本	A
		页码	