



HSF

Recommended P.C.B Layout (Top Side)
(PCB BOARD TOLERANCE ±0.05)

NOTES:
Rated Current: 3.0AMP.
Contact Resistance: 20mΩ Max.
Withstand Voltage: 1000V AC/DC
Insulation Resistance: 1000MΩ Min.
Operation Temperature: -40℃ to +105℃

Contact Material: Brass
Contact Plating: Au or Sn Over Ni
Insulator Material: PA9T+33%G.F UL94V-0 BK



A2



Ordering Information

1125-11 XX XX R XXX C 0 XX

No. of Pins	Contact Plating	Pin Length	Insulator Material	Packing	Series No.
02-40	G0=Gold Flash G3=10u"Gold G4=15u"Gold G5=30u"Gold S0=Gold Flash/Tin S3=10u"Gold/Tin S4=15u"Gold/Tin S5=30u"Gold/Tin SN=Tin SM=Matte Tin	L=A+B+D+3.75 Standard: 110=11.0 140=14.0 148=14.8	C=PA9T	0=PE Bag T=Tube	01-99



Item	Pin Length	A	E	B	Mating
Standard	11.00	3.00	4.02	3.00	2135
	14.00	3.00	4.02	6.00	2171 2185
	14.80	3.00	4.82	6.00	2171 2185
Alternate					

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	Fit	PART NO.
A2	2018/06/02	Cancel PBT & Modify P/N	A2	x.x ±0.40	Surong Xu	2018/06/02	UNIT	mm	1125-11XXXXRXXXCOXX A1 A2
A1	2018/01/22	Modify P/N	A1	x.xx ±0.25	CHECK	DATE	SIZE	A4	TITLE: PH2.54 SINGLE ROW 90° PLANE BENDING H=2.5
A0	2012/05/17	NEW	----	x.xxx ±0.15	APPROVE	DATE	SHEET	1/1	Customer NO.
				Angle ± 3°			PROJ.		
				DIM TOL					

WCON

Http: www.wcon.com

WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com	WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: salesks@wcon.com
---	--