



HSF

NOTES:
 Rated Current: 3.0AMP.
 Rating Voltage: 250V AC/DC
 Contact Resistance: 20mΩ Max.
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ Min.
 Operation Temperature: -40℃ to +105℃
 Contact Material: Brass
 Contact Plating: Au or Sn Over Ni
 Insulator Material: PA9T+33%G.F UL94V-0 BK



Recommended P.C.B Layout (Top Side)
 (PCB BOARD TOLERANCE±0.05)



Ordering Information

1125-12 XX XX R XXX C 0 XX

No. of Pins Per Row: 02-40	Contact Plating G0=Gold Flash G3=10u"Gold G4=15u"Gold G5=30u"Gold S0=Gold Flash/Tin S3=10u"Gold/Tin S4=15u"Gold/Tin S5=30u"Gold/Tin SN=Tin SM=Matte Tin	Pin Length(Short) L=A+B+D+3.75 Standard: 110=11.0 140=14.0 148=14.8	Insulator Material C=PA9T	Packing 0=PE Bag T=Tube	Series No. 01-99
-------------------------------	---	---	------------------------------	-------------------------------	---------------------



Item	Pin Length	A	E	B	Mating
Standard	11.00	3.00	4.02	3.00	2135
	14.00	3.00	4.02	6.00	2171 2185
	14.80	3.00	4.82	6.00	2171 2185
Alternate					

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	Fit	PART NO.
A2	2018/06/02	Cancel PBT & Modify P/N	A2	x.x ±0.40	Surong Xu	2018/06/02	UNIT	mm	1125-12XXXXRXXXCOXX A1 A2
A1	2018/01/22	Modify P/N	A1	x.xx ±0.25	CHECK	DATE	SIZE	A4	TITLE:
A0	2012/05/28	NEW	-----	x.xxx ±0.15	APPROVE	DATE	SHEET	1/1	PH2. 54 DUAL ROW 90° CONCAVE BENDING H=2.5
				Angle ± 3°			PROJ.		Customer NO.
				DIM TOL					

WCON

Http: www.wcon.com

WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com	WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: salesks@wcon.com
---	--