


HSF




NOTES:

Rated Current:2.0AMP.
 Contact Resistance:20mΩ Max.
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ Min.
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Au or Sn Over Ni
 Insulator Material:PA9T+33%G.F UL94V-0 BK



Recommended P.C.B Layout (Top Side)
 (PCB BOARD TOLERANCE±0.05)



Ordering Information

1220-12 XX XX Z XXX C R XX

No.of Pins Per Row:02~40	Contact Plating G0=Gold Flash G3=10u"Gold G4=15u"Gold G5=30u"Gold S0=Gold Flash/Tin S3=10u"Gold/Tin S4=15u"Gold/Tin S5=30u"Gold/Tin SN=Tin SM=Matte Tin	Pin Length(Short) L=A1+B+2.2 Standard:069=6.9 080=8.0 090=9.0	Insulator Material C=PA9T	Packing T=Tube P=Tube+CAP R=Tape&Reel+CAP	Series No. 01~99
-----------------------------	---	---	---------------------------------	--	---------------------

Item	Pin Length	A1	A	B	Mating
Standard	6.90	2.80	6.22	1.90	
	8.00	2.80	6.22	3.00	
	9.00	2.80	6.22	4.00	2240 2243 2263 2272
Alternate					

				OPERATION	DRAW	DATE	SCALE	Fit	PART NO.
				x.X ±0.40	Liu	2018.01.19	UNIT	mm	1220-12XXXXXXCRXX
A1	2018/01/19		Modify P/N	x.XX ±0.25	CHECK	DATE	SIZE	A4	TITLE:
AO	2012/04/26		NEW	x.XXX ±0.15	APPROVE	DATE	SHEET	1/1	PH2.00 DUAL ROW 90° SMT H=2.0 WITH POST
REV	DATE		MODIFICATION DESCRIPTION	Angle ± 3'			PROJ.		Customer NO.
			CHANGE	DIM TOL					

WCON
 Http: www.wcon.com

WCON-Dongguan
 Tel: +86 769 85358920
 Fax: +86 769 85358915
 E-mail: sales@wcon.com

WCON-Kunshan
 Tel: +86 512 57468408
 Fax: +86 512 57468468
 E-mail: salesks@wcon.com