



# HSF

NOTES:  
 Current Rating: 2.0AMP  
 Contact Resistance: 20mΩ Max  
 Withstand Voltage: 500V AC/DC  
 Insulation Resistance: 1000MΩ Min  
 Operation Temperature: -40°C to +105°C

Contact Material: Brass  
 Contact plating: Au Or Sn over Ni  
 Insulator Material: PA9T+33%G.F UL94V-0  
 LCP+30%G.F UL94V-0  
 6P-64P With Slot "E"  $\Delta$



Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE  $\pm 0.05$ )



## Ordering Information

3122-XX S XX B K00 X X

No. of Pins	Contact Plating	Color Insulator	Packing
$\Delta$ 06 26	G0=Gold Flash	B=Black	T=Tube
08 28	G3=10u"Gold	W=White	
10 30	G4=15u"Gold		
12 34	G5=30u"Gold		
14 36	S0=Gold Flash/Tin		
16 40	S3=10u"Gold/Tin		
18 44	S4=15u"Gold/Tin		
20 50	S5=30u"Gold/Tin		
22 60	SN=Tin		
24 64			



Item	Pitch	Mating	Dip(A)
Standard	2.00	5224	2.80
Alternate			

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	FIT	PART NO.
A1	2017/05/12	Modify drawing	$\Delta$	x.X ±0.40	Ding	2017/05/12	UNIT mm		3122-XXSXXBK00XX
AO	2012/09/24	NEW	-----	x.XX ±0.25	CHECK	DATE	SIZE A4		TITLE: 2.00 BOX HEADER 180° H=6.10 "F" TYPE
				x.XXX ±0.15	APPROVE	DATE	SHEET 1/1		Customer NO.
				Angle ± 3'			PROJ.		
				DIM TOL					

# WCON

Http: www.wcon.com

WCON-Dongguan  
 Tel: +86 769 85358920  
 Fax: +86 769 85358915  
 E-mail: sales@wcon.com

WCON-Kunshan  
 Tel: +86 512 57468408  
 Fax: +86 512 57468468  
 E-mail: sales@wcon.com