# PCI EXPRESS GEN 2 PACKET SWITCH

3-Port, 3-Lane, ExtremeLo PCIe 2.0 Packet Switch

DATASHEET REVISION 2-2 August 2017



1545 Barber Lane Milpitas, CA 95035 Telephone: 408-232-9100

FAX: 408-434-1040

Internet: <a href="http://www.diodes.com">http://www.diodes.com</a>





#### IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies w hose products are represented on Diodes Incorporated w ebsite, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
- 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the

failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2016, Diodes Incorporated

www.diodes.com





# **REVISION HISTORY**

Date	Revision Number	Description
7/13/11	0.1	Preliminary Datasheet
9/13/11	0.2	Updated Section 3.3 Miscellaneous Signals (GPIO[2] and GPIO[3])
		Updated Section 4.1 Pin List (GPIO[2] and GPIO[3])
11/23/11	0.3	Updated Section 1 Features (integrated reference clock)
		Updated Section 3.1 PCI Express Interface Signals (Added REFCLKI P, REFCLKI N,
		REFCLKO P[2:0], REFCLKO N[2:0], and IREF)
8/10/12	1.0	Updated Section 1 Features (OBFF and LTR support)
		Updated Section 3 Pin Description (VDDC, VDDCAUX, and AVDD)
		Updated Section 6 EEPROM Interface And System Management Bus
		Updated Section 7 Register Description
11/22/12	1.1	Updated Section 3.3 Miscellaneous Signals (NC and Test)
		Updated Section 4.1 Pin List
		Updated Figure 12 1 Package outline drawing
		Updated Table 8-1 Clock Requirement
1/2/13	1.2	Updated Section 3 Pin Description (PWR SAV, TCK, TRST L, and NC)
1,2,13	1.2	Added Section 11.4 AC Switching Characteristics of Clock Buffer
		Updated Section 4.1 Pin List
7/15/14	1.3	Updated Section 1.11 in Elst  Updated Section 1 (512-byte maximum payload size support, No-blocking capability)
7/13/11	1.5	Updated Section 3 (Removed internal resistance for DWNRST L[2:1], CLKBUF PD,
		VC1 EN, RXPOLINV DIS, PL 512B, PRSNT[2:1], SLOTCLK, SLOT IMP[2:1],
		EEPD, SMBCLK, SMBDATA, SCAN EN, GPIO[7:0], PWR SAV, TMS, TDI, and
		TRST L)
		Updated Section 3.2 Port Configuration Signals
		Updated Section 3.2 Miscellaneous Signals
		Updated Section 4.1 Pin List Of 136-Pin QFN
		Updated Section 5.1 Physical Layer Circuit
		Updated Section 5.1.7 Drive De-Emphasis
		Updated Section 7.2.75 Device Capabilities Register (Max Payload Size Supported)
		Updated Section 13 Ordering Information
		Updated Table 11-2 DC Electrical Characteristics
		Updated Figure 12-2 Package Bottom View
11/17/14	1.4	Updated Section 7.2 Transparent Mode Configuration Registers
11/1//14	1.4	Updated Section 8 Clock Scheme
07/16/15	1.5	Updated Section 3.1 PCI Express Interface Signals
0 // 10/ 13	1.5	Updated Section 3.2 Port Configuration Signals
		Updated Section 5.2 Poly Configuration Signals  Updated Section 5.1 Physical Layer Circuit
		Updated Section 6.1 EEPROM Interface
		Updated Section 7.2 Transparent Mode Configuration Registers
		Updated Section 8 Clock Scheme
		Updated Table 9-1 Instruction Register Codes
		Updated Table 9-1 Instruction Register Codes Updated Table 9-2 JTAG Device ID Register
		Updated Table 9-2 JTAG Device ID Register Updated Table 9-3 JTAG Boundary Scan Register Definition
		Updated Table 11-2 DC Electrical Characteristics
09/07/15	1.6	Updated Table 11-1 Absolute maximum ratings
12/23/15	1.6	Updated Section 3.1 PIN Description
12/23/13	1./	
		Updated Table 11-1 Absolute Maximum Ratings  Undeted Table 11-2 DC Floatrical Characteristics
02/26/16	1.0	Updated Table 11-2 DC Electrical Characteristics
02/26/16	1.8	Added Section 11 Power Sequence






Date	Revision Number	Description
08/31/17	2-2	Updated Section 1 Features
		Updated Section 3.2 Port Configuration Signals
		Updated Section 5.1 Physical Layer Circuit
		Updated Section 6.1.4 Mapping EEPROM Contents to Configuration Registers
		Updated Section 7.2 Transparent Mode Configuration Registers
		Updated Section 12.1 Absolute Maximum Ratings
		Updated Table 12-2 DC Electrical Characteristics
		Added Section 12.4 Operating Ambient Temperature
		Added Section 12.5 Power Consumption
		Revision numbering system changed to whole number



# TABLE OF CONTENTS

1 FEA	ATURES	11
2 GEI	NERAL DES CRIPTION	12
3 PIN	DES CRIPTION	14
3.1	PCI EXPRESS INTERFACE SIGNALS	14
3.2	PORT CONFIGURATION SIGNALS	
3.3	MISCELLANEOUS SIGNALS	
3.4	JTA G BOUNDARY SCAN SIGNALS	
3.5	POW ER PINS	17
4 PIN	ASSIGNMENTS	18
4.1	PIN LIST OF 136-PIN QFN	18
5 FUI	NCTIONAL DES CRIPTION	19
5.1	PHYSICA L LA YER CIRCUIT	19
5.1	1 RECEIVER DETECTION	19
5.1		
5.1	3 RECEIVER EQUALIZATION	20
5.1	4 TRANSMITTER SWING	20
5.1		20
5.1	6 DRIVE AMPLITUDE	21
5.1	7 DRIVE DE-EMPHASIS	22
5.1	8 TRANSMITTER ELECTRICAL IDLE LATENCY	22
5.2	DATA LINK LAYER (DLL)	
5.3	TRANSACTION LA YER RECEIVE BLOCK (TLP DECAPSULATION)	
5.4	ROUTING	
5.5	TC/VC MAPPING	
5.6	QUEUE	
5.6		
5.6		
5.6		
5.6		
5.6		
5.7	TRANSACTION ORDERING	
5.8	PORT ARBITRATION	
5.9	VC ARBITRATION	
5.10 5.11	FLOW CONTROLTRANSATION LA YER TRANSMIT BLOCK (TLP ENCAPSULATION)	
6 EEI	PROM INTERFACE AND SYSTEM MANAGEMENT BUS	27
6.1	EEPROM INTERFACE	27
6.1		
6.1		
6.1		
6.1		
6.2	SMBUS INTERFA CE	
7 RE	GISTER DES CRIPTION	38
7.1	REGISTER TYPES	38
7.2	TRANSPARENT MODE CONFIGURATION REGISTERS	
7.2		







7.2.2	DEVICE ID REGISTER – OFFSET 00h	40
7.2.3	COMMAND REGISTER – OFFSET 04h	40
7.2.4	PRIMARY STATUS REGISTER – OFFSET 04h	
7.2.5	REVISION ID REGISTER – OFFSET 08h	42
7.2.6	CLASS CODE REGISTER – OFFSET 08h	
7.2.7	CACHE LINE REGISTER – OFFSET 0Ch	42
7.2.8	PRIMARY LATENCY TIMER REGISTER – OFFSET 0Ch	42
7.2.9	HEADER TYPE REGISTER – OFFSET 0Ch	42
7.2.10	PRIMARY BUS NUMBER REGISTER – OFFSET 18h	
7.2.11	SECONDARY BUS NUMBER REGISTER – OFFSET 18h	42
7.2.12	SUBORDINATE BUS NUMBER REGISTER – OFFSET 18h	43
7.2.13	SECONDARY LATENCY TIMER REGISTER – OFFSET 18h	43
7.2.14	I/O BASE ADDRESS REGISTER – OFFSET 1Ch	43
7.2.15	I/O LIMIT ADDRESS REGISTER – OFFSET 1 Ch	43
7.2.16	SECONDARY STATUS REGISTER - OFFSET 1Ch	43
7.2.17	MEMORY BASE ADDRESS REGISTER – OFFSET 20h	44
7.2.18	MEMORY LIMIT ADDRESS REGISTER – OFFSET 20h	44
7.2.19	PREFETCHABLE MEMORY BASE ADDRESS REGISTER – OFFSET 24h	44
7.2.20	PREFETCHABLE MEMORY LIMIT ADDRESS REGISTER – OFFSET 24h	45
7.2.21	PREFETCHABLE MEMORY BASE ADDRESS UPPER 32-BITS REGISTER – OFFSET 28h	45
7.2.22	PREFETCHABLE MEMORY LIMIT ADDRESS UPPER 32-BITS REGISTER – OFFSET 2Ch	
7.2.23	I/O BASE ADDRESS UPPER 16-BITS REGISTER – OFFSET 30h	
7.2.24	I/O LIMIT ADDRESS UPPER 16-BITS REGISTER – OFFSET 30h	
7.2.25	CAPABILITY POINTER REGISTER – OFFSET 34h	
7.2.26	INTERRUPT LINE REGISTER – OFFSET 3Ch	46
7.2.27	INTERRUPT PIN REGISTER – OF FSET 3Ch	
7.2.28	BRIDGE CONTROL REGISTER – OFFSET 3Ch	
7.2.29	POWER MANAGEMENT CAPABILITY REGISTER - OFFSET 40h	
7.2.30	POWER MANAGEMENT DATA REGISTER – OFFSET 44h	
7.2.31	PPB SUPPORT EXTENSIONS – OFFSET 44h	
7.2.32	DATA REGISTER – OFFSET 44h	
7.2.33	MSI CAPABILITY REGISTER – OFFSET 4Ch (Downstream Port Only)	
7.2.34	MESSAGE CONTROL REGISTER – OFFSET 4Ch (Downstream Port Only)	
7.2.35	MESSAGE ADDRESS REGISTER – OFFSET 50h (Downstream Port Only)	49
7.2.36	MESSAGE UPPER ADDRESS REGISTER - OFFSET 54h (Downstream Port Only)	49
7.2.37	MESSAGE DATA REGISTER – OF FSET 58h (Downstream Port Only)	49
7.2.38	VPD CAP ABILITY REGISTER – OFFSET 5Ch (Upstream Port Only)	49
7.2.39	VPD REGISTER – OFFSET 5Ch (Upstream Port Only)	49
7.2.40	VPD DATA REGISTER – OFFSET 60h (Upstream Port Only)	50
7.2.41	VENDOR SPECIFIC CAPABILITY REGISTER – OFFSET 64h	
7.2.42	XPIP CSR0 – OFFSET 68h (Test Purpose Only)	
7.2.43	XPIP CSR1 – OFFSET 6Ch (Test Purpose Only)	
7.2.44	REPLAY TIME-OUT COUNTER – OFFSET 70h	
7.2.45	ACKNOWLEDGE LATENCY TIMER – OFFSET 70h	
7.2.46	SWITCH OPERATION MODE – OFFSET 74h (Upstream Port Only)	
7.2.47	SWITCH OPERATION MODE – OFFSET 74h (Downstream Port Only)	
7.2.48	XPIP CSR2 – OFFSET 78h	
7.2.49	PHY PARAMETER 1 – OFFSET 78h	
7.2.50	PHY PARAMETER 2 – OFFSET 7Ch	
7.2.51	XPIP CSR3 – OFFSET 80h	
7.2.52	XPIP CSR4 – OFFSET 84h	
7.2.53	XPIP CSR5 – OFFSET 88h	
7.2.54	TL CSR – OFFSET 8Ch	
7.2.55	PHY PARAMETER 3 – OFFSET 90h	
7.2.56	PHY PARAMETER 4 - OFFSET 94h	







7.2.57	OPERATION MODE –OFFSET 98h	
7.2.58	SSID/SSVID CAPABILITY REGISTER – OFFSET B0h	56
7.2.59	SUBSYSTEM VENDOR ID REGISTER – OFFSET B4h	57
7.2.60	SUBSYSTEM ID REGISTER – OFFSET B4h	
7.2.61	GPIO CONTROL REGISTER - OFFSET B8h (Upstream Port Only)	
7.2.62	EEPROM CONTROL REGISTER - OFFSET BCh (Upstream Port Only)	58
7.2.63	EEPROM ADDRESS REGISTER - OFFSET BCh (Upstream Port Only)	59
7.2.64	EEPROM DATA REGISTER - OFFSET BCh (Upstream Port Only)	59
7.2.65	PCI EXPRESS CAPABILITY REGISTER – OFFSET C0h	59
7.2.66	DEVICE CAPABILITIES REGISTER – OFFSET C4h	
7.2.67	DEVICE CONTROL REGISTER – OFFSET C8h	
7.2.68	DEVICE STATUS REGISTER – OFFSET C8h	
7.2.69	LINK CAPABILITIES REGISTER – OFFSET CCh	
7.2.70	LINK CONTROL REGISTER - OFFSET D0h	
7.2.71	LINK STATUS REGISTER – OFFSET D0h	
7.2.72	SLOT CAPABILITIES REGISTER - OFFSET D4h (Downstream Port Only)	
7.2.73	SLOT CONTROL REGISTER - OFFSET D8h (Downstream Port Only)	65
7.2.74	SLOT STATUS REGISTER OFFSET D8h (Downstream Port Only)	66
7.2.75	DEVICE CAPABILITIES REGISTER 2 – OFFSET E4h	
7.2.76	DEVICE CONTROL REGISTER 2 – OFFSET E8h	
7.2.77	DEVIDE STATUS REGISTER 2 – OFFSET E8h	
7.2.78	LINK CAPABILITIES REGISTER 2 – OFFSET ECh	
7.2.79	LINK CONTROL REGISTER 2 – OFFSET F0h	
7.2.80	LINK STATUS REGISTER 2 – OFFSET F0h	
7.2.81	SLOT CAPABILITIES REGISTER 2 – OFFSET F4h	
7.2.82	SLOT CONTORL REGISTER 2 – OFFSET F8h SLOT STATUS REGISTER 2 – OFFSET F8h	
7.2.83 7.2.84	PCI EXPRESS ADVANCED ERROR REPORTING CAPABILITY REGISTER – OFFSET 10	
7.2.85	UNCORRECTABLE ERROR STATUS REGISTER – OFFSET 104h	
7.2.86	UNCORRECTABLE ERROR STATES REGISTER – OFFSET 104nUNCORRECTABLE ERROR MASK REGISTER – OFFSET 108h	
7.2.87	UNCORRECTABLE ERROR SEVERITY REGISTER – OFFSET 10Ch	
7.2.88	CORRECTABLE ERROR STATUS REGISTER – OFFSET 110 h	
7.2.89	CORRECTABLE ERROR MASK REGISTER – OFFSET 114 h	
7.2.90	ADVANCE ERROR CAPABILITIES AND CONTROL REGISTER – OFFSET 118h	
7.2.91	HEADER LOG REGISTER – OFFSET From 11Ch to 128h	
7.2.92	PCI EXPRESS VIRTUAL CHANNEL CAPABILITY REGISTER - OFFSET 140h	
7.2.93	PORT VC CAPA BILITY REGISTER 1 – OFFSET 144h	
7.2.94	PORT VC CAPABILITY REGISTER 2 – OFFSET 148h	
7.2.95	PORT VC CONTROL REGISTER – OFFSET 14Ch	
7.2.96	PORT VC STATUS REGISTER – OFFSET 14Ch	73
7.2.97	VC RESOURCE CAPABILITY REGISTER (0) – OFFSET 150h	73
7.2.98	VC RESOURCE CONTROL REGISTER (0) – OFFSET 154h	74
7.2.99	VC RESOURCE STATUS REGISTER (0) – OFFSET 158h	
7.2.100	VC RESOURCE CAPABILITY REGISTER (1) – OFFSET 15Ch	
7.2.101	VC RESOURCE CONTROL REGISTER (1) – OFFSET 160h	
7.2.102	VC RESOURCE STATUS REGISTER (1) – OFFSET 164h	
7.2.103	VC ARBITRATION TABLE REGISTER – OFFSET 170h	
7.2.104	PORT ARBITRATION TABLE REGISTER (0) and (1) - OFFSET 180h and 1C0h	
7.2.105	PCI EXPRESS POWER BUDGETING CAPABILITY REGISTER – OFFSET 20Ch	
7.2.106	DATA SELECT REGISTER – OFFSET 210h	
7.2.107	POWER BUDGETING DATA REGISTER - OFFSET 214h	
7.2.108	POWER BUDGET CAPABILITY REGISTER – OFFSET 218h	
7.2.109	ACS EXTENDED CAPABILITY HEADER – OFFSET 220h (Downstream Port Only)	
7.2.110 7.2.111	ACS CAPABILITY REGISTER – OFFSET 224h (Downstream Port Only) EGRESS CONTROL VECTOR – OFFSET 228h (Downstream Port Only)	/8
7.4.111	ECINEDO CON ENCLEVECTOR — OFFOET 220N (DOWNSTRAM PORTONIV)	/ 9



# A Product Line of Diodes Incorporated



7.2	2.112 LTR EXTENDED CAPABILITY HEADER - OFFSET 230h (Upstream Port Only)	79	
7.2	2.113 MAX SNOOP LATENCY REGISTER – OFFSET 234h (Upstream Port Only)	79	
7.2	2.114 MAX NO-SNOOP LATENCY REGISTER – OFFSET 234h (Upstream Port Only)	80	
8 CI	OCKSCHEME		31
9 IE	EE 1149.1 COMPATIBLE JTAG CONTROLLER		32
9.1	INSTRUCTION REGISTER	82	
9.2	BYPASS REGISTER	82	
9.3	DEVICE ID REGISTER	82	
9.4	BOUNDARY SCAN REGISTER	83	
9.5	JTAG BOUNDARY SCAN REGISTER ORDER		
	OWER MANAGEMENT		
	OWER SEQUENCE		
12 EL	ECTRICAL AND TIMING SPECIFICATIONS		37
12.1	ABSOLUTE MAXIMUM RATINGS		
12.2	DC SPECIFICATIONS		
12.3	AC SPECIFICATIONS		
12.4	OPERATING AMBIENT TEMPERATURE	89	
12.5	POW ER CONSUMPTION	89	
13 PA	CKAGE INFORMATION	9	<b>)</b> 0
14 OR	RDERING INFORMATION	(	92



# A Product Line of Diodes Incorporated



### PI7C9X2G303EL

# **TABLE OF FIGURES**

FIGURE 5-1 DRIVER OUTPUT WAVEFORM	21
FIGURE 6-1 SMBUS ARCHITECTURE IMPLEMENTATION ON PI7C9X2G303EL	37
FIGURE 11-1 INITIAL POWER-UP SEQUENCE	86
FIGURE 13-1 PACKAGE OUTLINE DRAWING.	90
FIGURE 13-2 PACKAGE BOTTOM VIEW	91
LIST OF TABLES	
TABLE 5-1 RECEIVER DETECTION THRESHOLD SETTINGS	19
TABLE 5-2 RECEIVER SIGNAL DETECT THRESHOLD	
TABLE 5-3 RECEIVER EQUALIZATION SETTINGS.	20
TABLE 5-4 TRANSMITTER SWING SETTINGS	20
TABLE 5-5 DRIVE AMPLITUDE BASE LEVEL REGISTERS	21
TABLE 5-6 DRIVE AMPLITUDE BASE LEVEL SETTINGS.	21
TABLE 5-7 DRIVE DE-EMPHASIS BASE LEVEL REGISTER	22
TABLE 5-8 DRIVE DE-EMPHASIS BASE LEVEL SETTINGS	22
TABLE 5-9 SUMMARY OF PCI EXPRESS ORDERING RULES	25
TABLE 6-1 SMBUS ADDRESS PIN CONFIGURATION	37
TABLE 7-1 REGISTER ARRAY LAYOUT FOR VC ARBITRATION	76
TABLE 7-2 TABLE ENTRY SIZE IN 4 BITS.	76
TABLE 8-1 AC SWITCHING CHARACTERISTICS	
TABLE 9-1 INSTRUCTION REGISTER CODES.	
TABLE 9-2 JTA G DEVICE ID REGISTER	
TABLE 9-3 JTA G BOUNDARY SCAN REGISTER DEFINITION.	
TABLE 12-1 ABSOLUTE MAXIMUM RATINGS	
TABLE 12-2 DC ELECTRICAL CHARACTERISTICS	
TABLE 12-3 PCI EXPRESS INTERFACE - DIFFERENTIAL TRANSMITTER (TX) OUTPUT (5.0 GBPS) CHARACTERISTICS	
TABLE 12-4 PCI EXPRESS INTERFACE - DIFFERENTIAL TRANSMITTER (TX) OUT PUT (2.5 GBPS) CHARACTERISTICS	
TABLE 12-5 PCI EXPRESS INTERFACE - DIFFERENTIAL RECEIVER (RX) INPUT (5.0 GBPS) CHARACTERISTICS	
TABLE 12-6 PCI EXPRESS INTERFACE - DIFFERENTIAL RECEIVER (RX) INPUT (2.5 GBPS) CHARACTERISTICS	
TABLE 12-7 OPERATING AMBIENT TEMPERATURE	
TABLE 12-8 POWER CONSUMPTION	89






## 1 FEATURES

- 3-lane PCI Express Gen 2 Switch with 3 PCI Express ports
- Supports "Cut-through" (Default) as well as "Store and Forward" mode for packet switching
- Peer-to-peer switching between any two downstream ports
- 150 ns typical latency for packet routed through Switch without blocking
- Integrated reference clock for downstream ports
- Strapped pins configurable with optional EEPROM or SMBus
- SMBus interface support
- Compliant with System Management (SM) Bus, Version 1.0
- Compliant with PCI Express Base Specification Revision 2.1
- Compliant with PCI Express CEM Specification Revision 2.0
- Compliant with PCI-to-PCI Bridge Architecture Specification Revision 1.2
- Compliant with Advanced Configuration Power Interface (ACPI) Specification
- Reliability, Availability and Serviceability
  - Supports Data Poisoning and End-to-End CRC
  - Advanced Error Reporting and Logging
  - IEEE 1149.1 JTAG interface support
- Advanced Power Saving
  - Empty downstream ports are set to idle state to minimize power consumption
- Link Power Management
  - Supports L0, L0s, L1, L2, L2/L3<sub>Ready</sub> and L3 link power states
  - Active state power management for L0s and L1 states
- Device State Power Management
  - Supports D0, D3<sub>Hot</sub> and D3<sub>Cold</sub> device power states
  - 3.3V Aux Power support in D3<sub>Cold</sub> power state
- Port Arbitration: Round Robin (RR), Weighted RR and Time-based Weighted RR
- Extended Virtual Channel capability
  - Two Virtual Channels (VC) and Eight Traffic Class (TC) support
  - Disabled VCs' buffer is assigned to enabled VCs for resource sharing
  - Independent TC/VC mapping for each port
  - Provides VC arbitration selections: Strict Priority, Round Robin (RR) and Programmable Weighted RR
- Supports Isochronous Traffic
  - Isochronous traffic class mapped to VC1 only
  - Strict time based credit policing
- Supports up to 512-byte maximum payload size
- Programmable driver current and de-emphasis level at each individual port
- Support Access Control Service (ACS) for peer-to-peer traffic
- Support Address Translation (AT) packet for SR-IOV application
- Support OBFF and LTR
- Low Power Dissipation: 650 mW typical in L0 normal mode
- Industrial Temperature Range -40° to 85°C
- 136-pin aQFN 8mm x 8mm package







## 2 GENERAL DESCRIPTION

Similar to the role of PCI/PCIX Bridge in PCI/PCIX bus architecture, the function of PCI Express (PCIE) Switch is to expand the connectivity to allow more end devices to be reached by host controllers in PCIE serial interconnect architecture. The 3-lane PCIE Switch is in 3-port type configuration. It provides users the flexibility to expand or fan-out the PCI Express lanes based on their application needs.


In the PCI Express Architecture, the PCIE Switch forwards posted and non-posted requests, and completion packets in either downstream or upstream direction concurrently as if a virtual PCI Bridge is in operation on each port. By visualizing the port as a virtual Bridge, the Switch can be logically viewed as two-level cascaded multiple virtual PCI-to-PCI Bridges, where one upstream-port Bridge sits on all downstream-port Bridges. Similar to a PCI Bridge during enumeration, each port is given a unique bus number, device number, and function number by the initiating software. The bus number, device number, and function number are combined to form a destination ID for each specific port. In addition to that, the memory-map and IO address ranges are exclusively allocated to each port as well. After the software enumeration is finished, the packets are routed to the dedicated port based on the embedded address or destination ID. To ensure the packet integrity during forwarding, the Switch is not allowed to split the packets to multiple small packets or merge the received packets into a large transmit packet. Also, the IDs of the requesters and completers are kept unchanged along the path between ingress and egress port.

The Switch employs the architecture of Combined Input and Output Queue (CIOQ) in implementation. The main reason for choosing CIOQ is that the required memory bandwidth of input queue equals to the bandwidth of ingress port rather than increasing proportionally with port numbers as an output queue Switch does. The CIOQ at each ingress port contains separate dedicated queues to store packets. The packets are arbitrated to the egress port based on the PCIe transaction-ordering rule. For the packets without ordering information, they are permitted to pass over each other in case that the addressed egress port is available to accept them. As to the packets required to follow the ordering rule, the Head-Of-Line (HOL) issue becomes unavoidable for packets destined to different egress ports since the operation of producer-consumer model has to be retained; otherwise the system might occur hang-up problem. On the other hand, the Switch places replay buffer at each egress port to defer the packets before sending it out. This can assure the maximum throughput being achieved and therefore the Switch works efficiently. Another advantage of implementing CIOQ in PCIe Switch is that the credit announcement to the counterpart is simplified and streamlined because of the credit-based flow control protocol. The protocol requires that each ingress port maintains the credits independently without checking other ports' credit availability, which is otherwise required by pure output queue architecture.

The Switch supports two virtual channels (VC0, VC1) and eight traffic classes (TC0  $\sim$  TC7) at each port. The ingress port independently assigns packets into the preferred virtual channel while the egress port outputs the packet based on the predefined port and VC arbitration algorithm. For instance, the isochronous packet is given a special traffic class number other than TC0 and mapped into VC1 accordingly. By employing the strict time based credit policy for port arbitration and assigning higher priority to VC1 than VC0, the Switch can therefore guarantee the time-sensitive packet is not blocked by regular traffic to assure the quality of service. In addition, some datacentric applications only carry TC0/VC0 traffic. As a result, there are no packets that would consume VC1 bandwidth. In order to improve the efficiency of buffer usage, the unused VC1 queues can be reassigned to VC0 and enable each of the ingress ports to handle more data traffic bursts. This virtual channel resource relocation feature enhances the performance of the PCIe Switch further.

The Switch provides the advanced feature of Access Control Service (ACS). This feature regulates which components are allowed to communicate with each other within the PCIe multiple-point fabric, and allows the system to have more control over packet routing in the Switch. As a result, peer-to-peer traffic can be facilitated more accurately and efficiently. When the system also implements Address Translation Service (ATS), the peer-to-peer requests with translated address can be routed directly by enabling the corresponding option in ACS to avoid possible performance bottleneck associated with re-direction, which introduces extra latency and may increase link and RC congestion.







The built-in Integrated Reference Clock Buffer of the PCI Express Switch supports three reference clock outputs. The clock buffer is from a single 100MHz clock input, and distributes the clock source to three outputs, which can be used by the downstream PCI Express end devices. The clock buffer feature can be enabled and disabled by strapping pin setting.





# 3 PIN DESCRIPTION

## 3.1 PCI EXPRESS INTERFACE SIGNALS

NAME	PIN	TYPE	DESCRIPTION
REFCLKP	A24	I	Reference Clock In put Pair: Connect to 100MHz differential clock
REFCLKN	A22		when integrated reference clock buffer is disabled (CLKBUF_PD=1),
			or connect to one of the Integrated Reference Clock Out put Pairs
			(REFCLKO_P and REFCLKO_N) of this Switch when integrated
			reference clock buffer is enabled (CLKBUF_PD=0).
			The input clock signals must be delivered to the clock buffer cell
			through an AC-coupled interface so that only the AC information of
			the clock is received, converted, and buffered. It is recommended that a
PERP[2:0]	A28, C33, C9	T	0.1 uF be used in the AC-coupling.  PCI Express Data Serial Input Pairs: Differential data receive
F EKF [2.0]	A26, C33, C9	1	signals in three ports.
			signals in timee poits.
			Port 0 (Upstream Port) is PERP[0] and PERN[0]
PERN[2:0]	A26, C31,	I	Port 1 (Downstream Port) is PERP[1] and PERN[1]
	C11		Port 2 (Downstream Port) is PERP[2] and PERN[2]
PETP[2:0]	C25, C29,	О	PCI Express Data Serial Output Pairs: Differential data transmit
	A10		signals in three ports.
			Port 0 (Upstream Port) is PETP[0] and PETN[0]
			Port 1 (Downstream Port) is PETP[1] and PETN[1]
PETN[2:0]	C23, C27,	O	Port 2 (Downstream Port) is PETP[2] and PETN[2]
	A12		
PERST L	M1	I	System Reset (Active LOW): When PERST L is asserted, the
_			internal states of whole chip except sticky logics are initialized.
			Please refer to Table 11-2 for PERST_L spec.
DWNRST_L[2:1]	J3, F1	O	Downstream Device Reset (Active LOW): DWNRST_L provides a
			reset signal to the devices connected to the downstream ports of the
			switch. The signal is active when either PERST_L is asserted or the
			device is just plugged into the switch. DWNRST_L [x] corresponds to
DEVE	A 1.0	т	Portx, where x=1,2,3.
REXT	A18	I	External Reference Resistor: Connect an external resistor (1.43K
			Ohm +/- 1%) to REXT_GND to provide a reference to both the bias currents and impedance calibration circuitry.
REXT GND	C15	I	External Reference Resistor Ground: Connect to an external resistor
12271_0110		1	to REXT.
REFCLKI P.	AE35, AH37	I	Integrated Reference Clock Input Pair: Connect to external
REFCLKI_N	, , ,		100MHz differential clock for the integrated reference clock buffer.
REFCLKO_P[2:0]	AB37, V37,	О	Integrated Reference Clock Output Pairs: 100MHz external
	P37		differential HCSL clock outputs for the integrated reference clock
REFCLKO_N[2:0]	AD37, Y37,	O	buffer.
	T37		
IREF	R35	I	Differential Reference Clock Output Current Resistor: External
			resistor (475 Ohm +/- 1%) connection to set the differential reference
CLUDITE DD	A D 2 O	т	clock output current.
CLKBUF_PD	AR29	I	Reference Clock Output Pairs Power Down: When CLKBUF_PD is asserted high, the integrated reference clock buffer and Reference
			Clock Outputs are disabled. When it is asserted low, the integrated
			reference clock buffer and Reference Clock Outputs are enabled. This
			pin has internal pull-down. If no board trace is connected to this pin,
			the internal pull-down resistor of this pin is enough. However, if pin is
			connected to a board trace and not driven, it is recommended that an
			external 330-ohm pull-down resistor be used.
	1		





### 3.2 PORT CONFIGURATION SIGNALS

NAME	PIN	TYPE	DESCRIPTION
VC1_EN	W3	I	Virtual Channel 1 Resource Sharing Enable: The chip provides the capability to support virtual channel 1 (VC1), in addition to the standard virtual channel 0. When this pin is asserted high, Virtual Channel 1 is enabled, and virtual channel resource sharing is not available. When it is asserted low, the chip would allocate the additional VC1 resource to VC0, and VC1 capability is disabled. This pin has internal pull-down resistor. If no board trace is connected to this pin, the internal pull-down resistor of this pin is enough. However, if pin is connected to a board trace and not driven, it is recommended that an external 330-ohm pull-down resistor be used.
RXPOLINV_DIS	AE3	I	Rx Polarity Inversion Disable: When RXPOLINV_DIS is asserted high, it indicates to disable Rx Polarity Inversion detection function. Otherwise, it indicates to enable Rx Polarity Inversion detection function. This pin has internal pull-down resistor. If no board trace is connected to this pin, the internal pull-down resistor of this pin is enough. However, if pin is connected to a board trace and not driven, it is recommended that an external 330-ohm pull-down resistor be used.
PL_512B	AR23	I	Max. Payload Size 512B: When PL 512B is asserted high, it indicates the max. payload size capability is 512B. Otherwise, it indicates the max. Payload size is 256B. This pin has internal pull-down resistor. If no board trace is connected to this pin, the internal pull-down resistor of this pin is enough. However, if pin is connected to a board trace and not driven, it is recommended that an external 330-ohm pull-down resistor be used.
PRSNT[2:1]	AA3, Y1	I	<b>Present:</b> When PRSNT is asserted low, it indicates that the device is present in the slot of downstream port. Otherwise, it indicates the absence of the device. PRSNT [x] is correspondent to Port x, where x=1,2,3. These pins have internal pull-down resistors.
SLOTCLK	AR7	I	Slot Clock Configuration: It determines if the downstream component uses the same physical reference clock that the platform provides on the connector. When SLOTCLK is high, the platform reference clock is employed. By default, all downstream ports use the same physical reference clock provided by platform. This pin has internal pull-down resistor. If no board trace is connected to this pin, the internal pull-down resistor of this pin is enough. However, if pin is connected to a board trace and not driven, it is recommended that an external 330-ohm pull-down resistor be used.
SLOT_IMP[2:1]	AU16, AR15	I	Slot Implemented: These signals are asserted to indicate that the downstream ports are connected to slots. SLOT_IMP[x] corresponds to Portx, where x=1,2,3. When SLOT_IMP[x] is asserted, the Portx is connected to slot. Otherwise, it is chip-to-chip connection directly. These pins have internal pull-down resistors. If no board trace is connected to these pins, the internal pull-down resistors of these pins are enough. However, if pins are connected to a board trace and not driven, it is recommended that external 330-ohm pull-down resistors be used.
PORTSTATUS[2:0]	AM37, AL35, AP37	0	Port Status: These signals indicate the status of each port. Please connect to pin header for debug used.  PORT STATUS[x] is correspondent to Port x, where x=0, 1, 2.

# 3.3 MISCELLANEOUS SIGNALS

NAME	PIN	TYPE	DESCRIPTION
EECLK	AJ35	O	<b>EEPRO M Clock:</b> Clock signal to the EEPROM interface.
EEPD	AK37	I/O	<b>EEPRO M Data:</b> Bi-directional serial data interface to and from the
			EEPROM. The pin is set to '1' by default.
SMBCLK	AH1	I	SM Bus Clock: System management Bus Clock. This pin requires an
			external 5.1K-ohm pull-up resistor.
SMBDATA	AK1	I/O	SM Bus Data: Bi-Directional System Management Bus Data. This pin
			requires an external 5.1K-ohm pull-up resistor.





NAME	PIN	TYPE	DESCRIPTION
SCAN_EN	AG35	I/O	Full-Scan En able Control: For normal operation, SCAN_EN is an output
_			with a value of "0". SCAN_EN becomes an input during manufacturing
			testing.
GPIO[7:0]	AU14, AR13,	I/O	General Purpose Input and Output: These eight general-purpose pins are
	AU12, AU10,		programmed as either input-only or bi-directional pins by writing the GPIO
	AR11, AU8,		output enable control register.
	AU6, AR9		When SMBus is implemented, GPIO[7:5] act as the SMBus address pins,
			which set Bit 2 to 0 of the SMBus address.
			<b>Debug Mode Selection:</b> In debug mode, GPIO[4:0] are used for Debug Mode Selection.
PWR SAV	AJ3	I	Power Saving Mode: PWR_SAV is a strapping pin. When this pin is
T W K_SA V	AJS	1	pulled high when system is reset, the Power Saving Mode is enabled. When
			this pin is pulled low when system is reset, the Power Saving Mode is
			disabled. When this pin is pulled low, it should be tied to ground through a
			330-ohm pull-down resistor. When this pin is pulled high, a 5.1K-ohm pull-
			up resistor should be used.
TEST3	V1	I	Test3/5/6: These pins are for internal test purpose. Test3, Test5 and Test6
TEST 5	AF1		should be tied to ground through a 330-ohm pull-down resistor.
TEST6	AR21		First the second of the second
TEST4	AD1	I	<b>Test4:</b> The pin is for internal test purpose. It should be tied to ground
			through a 330-ohm pull-down resist or for normal operation.
			Port Status Output Enable: In debug mode, it is used to enable PortStatus
			output.
TEST1	N3	I	<b>Test1:</b> The pin is for internal test purpose. It should be tied to 3.3V through
			a 5.1 K-ohm pull-up resistor for normal operation.
			<b>De bug Mode En able</b> : In debug mode, it need be tired to low through a
TEST2	T1	I	330-ohm pull-down resistor.  Test2: The pin is for internal test purpose. Test2 should be tied to 3.3V
1 E51 2	1 1	1	through a 5.1 K-ohm pull-up resistor.
NC	AF37, A2,		Not Connected: These pins can be just left open.
1.0	A4, A6, A8,		The connected these phile can be just letter pain.
	A14, A16,		
	A20, A30,		
	A32, A34,		
	A36, B1,		
	B37, C3, C5,		
	C7, C13,		
	C35, D1,		
	D37, F37,		
	G3, H1, K1,		
	U35, AB1,		
	AC3, AC35,		
	AG3, AL3,		
	AM1, AN3,		
	AP1, AR3,		
	AR5, AR17,		
	AR25, AR27,		
	AR33, AR35,		
	AT 1, AT 37, AU2, AU4,		
	AU18, AU20, AU22, AU24,		
	AU26, AU28,		
	AU34, AU36		
	AUJ4, AUJ0		

# 3.4 JTAG BOUNDARY SCAN SIGNALS

Name	Pin	Type	Description
TCK	K37	I	<b>Test Clock:</b> Used to clock state information and data into and out of the
			chip during boundary scan. When JT AG boundary scan function is not
			implemented, this pin should be left open (NC).





Name	Pin	Type	Description
TMS	H37	I	Test Mode Select: Used to control the state of the Test Access Port
			controller. When JT AG boundary scan function is not implemented, this pin
			should be pulled low through a 330-Ohm pull-down resistor.
TDO	N35	О	Test Data Output: When SCAN_EN is high, it is used (in conjunction
			with TCK) to shift data out of the Test Access Port (TAP) in a serial bit
			stream. When JT AG boundary scan function is not implemented, this pin
			should be left open (NC).
TDI	J35	I	Test Data Input: When SCAN_EN is high, it is used (in conjunction with
			TCK) to shift data and instructions into the TAP in a serial bit stream.
			When JT AG boundary scan function is not implemented, this pin should be
			left open (NC).
TRST_L	G35	I	Test Reset (Active LOW): Active LOW signal to reset the TAP controller
			into an initialized state. When JTAG boundary scan function is not
			implemented, this pin should be pulled low through a 330-Ohm pull-down
			resistor.

# 3.5 POWER PINS

NAME	PIN	TYPE	DESCRIPTION
VDDC	AN35, B, L,	P	VDDC Supply (1.0V): Used as digital core power pins.
	L35		
VDDR	E3, L3, AR19,	P	VDDR Supply (3.3V): Used as digital I/O power pins.
	AU32, AR31,		
	E35		
CVDDR	R	P	CVDDR Supply (3.3V): Used as reference clock power pin.
VDDCAUX	P1, R3	P	VDDC AUX Supply (1.0V): Used as auxiliary core power pins.
VAUX	U3	P	VAUX Supply (3.3V): Used as auxiliary I/O power pins.
AVDD	T	P	AVDD Supply (1.0V): Used as PCI Express analog power pins.
AVDDH	C17,	P	AVDDH Supply (3.3V): Used as PCI Express analog high voltage power
			pins.
AGND	C19, C21	P	Ground: Used as analog ground pins.
DGND	M37, AU30	P	Ground: Used as digital ground pins.
CGND	W35, AA35	P	Ground: Used as reference clock ground pins.
VSS	GND	P	VSS Ground: Used as ground pin.





# **4 PIN ASSIGNMENTS**

## 4.1 PIN LIST of 136-PIN QFN

PIN	NAME	PIN	NAME	PIN	NAME	PIN	NAME
A2	NC	C35	NC	AA35	CGND	AR21	TEST 6
A4	NC	D1	NC	AB1	NC	AR23	PL 512B
A6	NC	D37	NC	AB37	REFCLKO P[2]	AR25	NC
A8	NC	E3	VDDR	AC3	NC	AR27	NC
A10	PETP[0]	E35	VDDR	AC35	NC	AR29	CLKBUF PD
A12	PETN[0]	F1	DWNRST L[1]	AD1	TEST4	AR31	VDDR
A14	NC	F37	NC	AD37	REFCLKO_N[2]	AR33	NC
A16	NC	G3	NC	AE3	RXPOLINV DIS	AR35	NC
A18	REXT	G35	TRST L	AE35	REFCLKI P	AT1	NC
A20	NC	H1	NC	AF1	TEST 5	AT37	NC
A22	REFCLKN	H37	TMS	AF37	NC	AU2	NC
A24	REFCLKP	J3	DWNRST_L[2]	AG3	NC	AU4	NC
A26	PERN[2]	J35	TDI	AG35	SCAN_EN	AU6	GPIO[1]
A28	PERP[2]	K1	NC	AH1	SMBCLK	AU8	GPIO[2]
A30	NC	K37	TCK	AH37	REFCLKI_N	AU10	GPIO[4]
A32	NC	L3	VDDR	AJ3	PWR_SAV	AU12	GPIO[5]
A34	NC	L35	VDDC	AJ35	EECLK	AU14	GPIO[7]
A36	NC	M1	PERST_L	AK1	SMBDATA	AU16	SLOT_IMP[2]
B1	NC	M37	DGND	AK37	EEPD	AU18	NC
B37	NC	N3	TEST1	AL3	NC	AU20	NC
C3	NC	N35	TDO	AL35	PORT ST ATUS[1]	AU22	NC
C5	NC	P1	VDDCAUX	AM1	NC	AU24	NC
C7	NC	P37	REFCLKO_P[0]	AM37	PORT ST ATUS[2]	AU26	NC
C9	PERP[0]	R3	VDDCAUX	AN3	NC	AU28	NC
C11	PERN[0]	R35	IREF	AN35	VDDC	AU30	DGND
C13	NC	T1	TEST2	AP1	NC	AU32	VDDR
C15	REXT_GND	T37	REFCLKO_N[0]	AP37	PORT ST ATUS[0]	AU34	NC
C17	AVDDH	U3	VAUX	AR3	NC	AU36	NC
C19	AGND	U35	NC	AR5	NC	T	AVDD
C21	AGND	V1	TEST3	AR7	SLOTCLK	В	VDDC
C23	PETN[2]	V37	REFCLKO_P[1]	AR9	GPIO[0]	R	CVDDR
C25	PETP[2]	W3	VC1_EN	AR11	GPIO[3]	L	VDDC
C27	PETN[1]	W35	CGND	AR13	GPIO[6]	GND	VSS
C29	PETP[1]	Y1	PRSNT[1]	AR15	SLOT_IMP[1]		
C31	PERN[1]	Y37	REFCLKO_N[1]	AR17	NC	]	
C33	PERP[1]	AA3	PRSNT[2]	AR19	VDDR	1	





## 5 FUNCTIONAL DESCRIPTION

Multiple virtual PCI-to-PCI Bridges (VPPB), connected by a virtual PCI bus, reside in the Switch. Each VPPB contains the complete PCIe architecture layers that consist of the physical, data link, and transaction layer. The packets entering the Switch via one of VPPBs are first converted from serial bit-stream into parallel bus signals in physical layer, stripped off the link-related header by data link layer, and then relayed up to the transaction layer to extract out the transaction header. According to the address or ID embedded in the transaction header, the entire transaction packets are forwarded to the destination VPPB for formatting as a serial-type PCIe packet through the transmit circuits in the data link layer and physical layer. The following sections describe these function elements for processing PCIe packets within the Switch.

#### 5.1 PHYSICAL LAYER CIRCUIT

The physical layer circuit design is based on the PHY Interface for PCI Express Architecture (PIPE). It contains Physical Media Attachment (PMA) and Physical Coding Sub-layer (PCS) blocks. PMA includes Serializer/ Deserializer (SERDES), PLL¹, Clock Recovery module, receiver detection circuits, beacon transmitter, electrical idle detector, and input/output buffers. PCS consists of framer, 8B/10B encoder/decoder, receiver elastic buffer, and PIPE PHY control/status circuitries. To provide the flexibility for port configuration, each lane has its own control and status signals for MAC to access individually. In addition, a pair of PRBS generator and checker is included for PHY built-in self test. The main functions of physical layer circuits include the conversion between serial-link and parallel bus, provision of clock source for the Switch, resolving clock difference in receiver end, and detection of physical layer errors.

In order to meet the needs of different application, the drive amplitude, de-emphasis and equalization of each transmitting channels can be adjusted using EEPROM individually. De-emphasis of -3.5 db is implemented by the transmitters when full swing signaling is used, while an offset can be individually applied to each channel.

#### 5.1.1 RECEIVER DETECTION

The physical layer circuits implement receiver detection, which detects the presence of an attached 50 ohm to ground termination as per PCI Express Specification. The detect circuits determine if the voltage levels of the receiver have crossed the internal threshold after a configurable time determined by the Receiver Detection Threshold field in the PHY Parameter 2 Register (offset 7Ch, bit[6:4]) as listed in Table 5-1, which can be configured by EEPROM or SMBUS settings.

Table 5-1 Receiver Detection Threshold Settings

Receiver Detection	Threshold
Threshold	
000	1.0 us
001	2.0 us
010	4.0 us (Recommended)
011	5.0 us
100	10 us
101	20 us
110	40 us
111	50 us

\_

<sup>&</sup>lt;sup>1</sup> Multiple lanes could share the PLL.





#### 5.1.2 RECEIVER SIGNAL DETECTION

Receiver signal idling is detected with levels above a programmable threshold specified by Receiver Signal Detect field in the PHY Parameter 2 Register (Offset 7Ch, bit[21:20]) as listed in Table 5-2, which can be configured on a per-port basis via EEPROM or SMBUS settings.

Table 5-2 Receiver Signal Detect Threshold

Receiver Signal Detect	Min (mV ppd)	Max (mV ppd)
00	50	80
01 (Recommended)	65	175
10	75	200
11	120	240

#### 5.1.3 RECEIVER EQUALIZATION

The receiver implements programmable equalizer via the Receiver Equalization field in the PHY Parameter 2 Register (Offset 7Ch, bit[25:22]) as listed in Table 5-3, which can be configured on a per-port basis via EEPROM or SMBUS settings.

Table 5-3 Receiver Equalization Settings

Receiver Equalization	Equalization
0000	Off
0010	Low
0110 (Recommended)	Medium
1110	High

### 5.1.4 TRANSMITTER SWING

The PCI Express transmitters support implementations of both full voltage swing and half (low) voltage swing. In full swing signaling mode, the transmitters implement de-emphasis, while in half swing mode, the transmitters do not. The Transmitter Swing field in the PHY Parameter 2 Register (offset 7Ch, Bit[30]) is used for the selection of full swing signaling or half swing signaling, which can be configured on a per-port basis via EEPROM or SMBUS settings.

Table 5-4 Transmitter Swing Settings

Transmitter Swing	Mode	De-emphasis	
0	Full Voltage Swing	Implemented	
1	Half Voltage Swing	Not implemented	

#### 5.1.5 DRIVE AMPLITUDE AND DE-EMPHASIS SETTINGS

Depending on the operation condition (voltage swing and de-emphasis condition), one of the Drive Amplitude Base Level fields in the Switch Operation Mode Register (offset 74h) and one of the Drive De-Emphasis Base Level fields in the PHY Parameter 1 Register (offset 78h) are active for configuration of the amplitude and de-emphasis.

The final drive amplitude and drive de-emphasis are the summation of the base level value and the offset value. The offset value for drive amplitude is 25 mV pd, and 6.25 mV pd for drive de-emphasis.





The driver output waveform is the synthesis of amplitude and de-emphasis as shown in Figure 5-1. The driver amplitude without de-emphasis is specified as a peak differential voltage level (mVpd), and the driver de-emphasis modifies the driver amplitude.




Figure 5-1 Driver Output Waveform

#### 5.1.6 DRIVE AMPLITUDE

Only one of the Drive Amplitude Level field in the Switch Operation Mode Register (offset 74h, bit[20:16], bit[25:21] and bit[30:26]) listed in Table 5-5 is active depending on the de-emphasis and swing condition. The settings and the corresponding values of the amplitude level are listed in Table 5-6, which can be configured by EEPROM or SMBUS settings.

Table 5-5 Drive Amplitude Base Level Registers

Active Register	De-Emphasis Condition	Swing Condition
C_DRV_LVL_3P5_NOM	-3.5 db	Full
C_DRV_LVL_6P0_NOM	-6.0 db	Full
C_DRV_LVL_HALF_NOM	N/A	Half

Table 5-6 Drive Amplitude Base Level Settings

Setting	Amplitude (mV pd)	Setting	Amplitude (mV pd)	Setting	Amplitude (mV pd)
00000	0	00111	175	01110	350
00001	25	01000	200	01111	375
00010	50	01001	225	10000	400
00011	75	01010	250	10001	425
00100	100	01011	275	10010	450
00101	125	01100	300	10011	475
00110	150	01101	325	Others	Reserved

Note:

1. Nominal levels. Actual levels will vary with temperature, voltage and board effects.





- 2. The maximum nominal amplitude of the output driver is 475 mV pd. Combined values of driver amplitude and de-emphasis greater than 475 mV pd should be avoided.
- 3. At higher amplitudes, actual swings will be less than the theoretical value due to process variations and environment factors, such as voltage overhead compression, package losses, board losses, and other effects.

#### 5.1.7 DRIVE DE-EMPHASIS

The Drive De-Emphasis Level field in the PHY Parameter 1 Register (Offset 78h, bit[20:16], bit[25:21] and bit[30:26]) listed in Table 5-7 controls the de-emphasis base level. The settings and the corresponding values of the de-emphasis level are listed in Table 5-8, which can be globally via EEPROM or SMBUS settings.

Table 5-7 Drive De-Emphasis Base Level Register

Register	De-Emphasis Condition
C_EMP_POST_GEN1_3P5_NOM	-3.5 db
C_EMP_POST_GEN2_3P5_NOM	-3.5 db
C EMP POST GEN2 6P0 NOM	-6.0 db

Table 5-8 Drive De-Emphasis Base Level Settings

Setting	De-Emphasis (mV pd)	Setting	De-Emphasis (mV pd)	Setting	De-Emphasis (mV pd)
00000	0.0	01011	69.0	10110	137.5
00001	6.0	01100	75.0	10111	144.0
00010	12.5	01101	81.0	11000	150.0
00011	19.0	01110	87.0	11001	156.0
00100	25.0	01111	94.0	11010	162.5
00101	31.0	10000	100.0	11011	169.0
00110	37.5	10001	106.0	11100	175.0
00111	44.0	10010	112.5	11101	181.0
01000	50.0	10011	119.0	11110	187.5
01001	56.0	10100	125.0	11111	194.0
01010	62.5	10101	131.0	-	-

#### Note:

- 1. Nominal levels. Actual levels will vary with temperature, voltage and board effects.
- 2. The maximum nominal amplitude of the output driver is 475 mV pd. Combined values of driver amplitude and de-emphasis greater than 475 mV pd should be avoided.
- 3. At higher amplitudes, actual swings will be less than the theoretical value due to process variations and environment factors, such as voltage overhead compression, package losses, board losses, and other effects.


#### 5.1.8 TRANSMITTER ELECTRICAL IDLE LATENCY

After the last character of the PCI Express transmission, the output current is reduced, and a differential voltage of less than 20 mV with common mode of VTX-CM-DC is established within 20 UI. This delay time is programmable via Transmitter PHY Latency field in the PHY Parameter 2 Register (Offset 7Ch, bit[3:0]), which can be configured by EEPROM or SMBUS settings.

## 5.2 DATA LINK LAYER (DLL)

The Data Link Layer (DLL) provides a reliable data transmission between two PCI Express points. An ACK/NACK protocol is employed to guarantee the integrity of the packets delivered. Each Transaction Layer Packet (TLP) is protected by a 32-bit LCRC for error detection. The DLL receiver performs LCRC calculation to determine if the incoming packet is corrupted in the serial link. If an LCRC error is found, the DLL transmitter would issue a NACK data link layer packet (DLLP) to the opposite end to request a re-transmission, otherwise an ACK DLLP would be sent out to acknowledge on reception of a good TLP.







In the transmitter, a retry buffer is implemented to store the transmitted TLPs whose corresponding ACK/NACK DLLP have not been received yet. When an ACK is received, the TLPs with sequence number equals to and smaller than that carried in the ACK would be flushed out from the buffer. If a NACK is received or no ACK/NACK is returned from the link partner after the replay timer expires, then a replay mechanism built in DLL transmitter is triggered to re-transmit the corresponding packet that receives NACK or time-out and any other TLP transmitted after that packet.

Meanwhile, the DLL is also responsible for the initialization, updating, and monitoring of the flow-control credit. All of the flow control information is carried by DLLP to the other end of the link. Unlike TLP, DLLP is guarded by 16-bit CRC to detect if data corruption occurs.

In addition, the Media Access Control (MAC) block, which is consisted of LTSSM, multiple lanes de-skew, scrambler/de-scrambler, clock correction from inserting skip order-set, and PIPE-related control/status circuits, is implemented to interface physical layer with data link layer.

## 5.3 TRANSACTION LAYER RECEIVE BLOCK (TLP DECAPSULATION)

The receiving end of the transaction layer performs header information retrieval and TC/VC mapping (see section 5.5), and it validates the correctness of the transaction type and format. If the TLP is found to contain an illegal header or the indicated packet length mismatches with the actual packet length, then a Malformed TLP is reported as an error associated with the receiving port. To ensure end-to-end data integrity, a 32-bit ECRC is checked against the TLP at the receiver if the digest bit is set in header.

#### 5.4 ROUTING


The transaction layer implements three types of routing protocols: ID-based, address-based, and implicit routing. For configuration reads, configuration writes, transaction completion, and user-defined messages, the packets are routed by their destination ID constituted of bus number, device number, and function number. Address routing is employed to forward I/O or memory transactions to the destination port, which is located within the address range indicated by the address field carried in the packet header. The packet header indicates the packet types including memory read, memory write, IO read, IO write, Message Signaling Interrupt (MSI) and user-defined message. Implicit routing is mainly used to forward system message transactions such as virtual interrupt line, power management, and so on. The message type embedded in the packet header determines the routing mechanism.

If the incoming packet can not be forwarded to any other port due to a miss to hit the defined address range or targeted ID, this is considered as Unsupported Request (UR) packet, which is similar to a master abort event in PCI protocol.

#### 5.5 TC/VC MAPPING

The 3-bit TC field defined in the header identifies the traffic class of the incoming packets. To enable the differential service, a TC/VC mapping table at destination port that is pre-programmed by system software or EEPROM pre-load is utilized to cast the TC labeled packets into the desired virtual channel. Note that TC0 traffic is mapped into VC0 channel by default. After the TC/VC mapping, the receive block dispatches the incoming request, completion, or data into the appropriate VC0 and VC1 queues.







#### 5.6 QUEUE

In PCI Express, it defines six different packet types to represent request, completion, and data. They are respectively Posted Request Header (PH), Posted Request Data payload (PD), Non-Posted Request Header (NPH), Non-Posted Data Payload (NPD), Completion Header (CPLH) and Completion Data payload (CPLD). Each packet with different type would be put into a separate queue in order to facilitate the following ordering processor. Since NPD usually contains one DW, it can be merged with the corresponding NPH into a common queue named NPHD. Except NPHD, each virtual channel (VC0 or VC1) has its own corresponding packet header and data queue. When only VC0 is needed in some applications, VC1 can be disabled and its resources assigned to VC0 by asserting VC1\_EN (Virtual Channel 1 Enable) to low.

#### 5.6.1 PH

PH queue provides TLP header spaces for posted memory writes and various message request headers. Each header space occupies sixteen bytes to accommodate 3 DW or 4 DW headers. There are two PH queues for VC0 and VC1 respectively.

#### 5.6.2 PD

PD queue is used for storing posted request data. If the received TLP is of the posted request type and is determined to have payload coming with the header, the payload data would be put into PD queue. There are two PD queues for VC0 and VC1 respectively.

#### 5.6.3 NPHD

NPHD queue provides TLP header spaces for non-posted request packets, which include memory read, IO read, IO write, configuration read, and configuration write. Each header space takes twenty bytes to accommodate a 3-DW header, s 4-DW header, s 3-WD header with 1-DW data, and a 4-DW header with 1-DW data. There is only one NPHD queue for VC0, since non-posted request cannot be mapped into VC1.

#### 5.6.4 CPLH

CPLH queue provides TLP header space for completion packets. Each header space takes twelve bytes to accommodate a 3-DW header. Please note that there are no 4-DW completion headers. There are two CPLH queues for VC0 and VC1 respectively.

#### 5.6.5 CPLD

CPLD queue is used for storing completion data. If the received TLP is of the completion type and is determined to have payload coming with the header, the payload data would be put into CPLD queue. There are two CPLD queues for VC0 and VC1 respectively.





#### 5.7 TRANSACTION ORDERING

Within a VPPB, a set of ordering rules is defined to regulate the transactions on the PCI Express Switch including Memory, IO, Configuration and Messages, in order to avoid deadlocks and to support the Producer-Consumer model. The ordering rules defined in table 5-4 apply within a single Traffic Class (TC). There is no ordering requirement among transactions within different TC labels. Since the transactions with the same TC label are not allowed to map into different virtual channels, it implies no ordering relationship between the traffic in VC0 and VC1.

Table 5-9 Summary of PCI Express Ordering Rules


Row Pass Column	Posted	Read	Non-posted Write	Read	Non-posted Write
	Request	Request	Request	Completion	Completion
Posted Request	Yes/No1	Yes <sup>5</sup>	Yes <sup>5</sup>	Yes <sup>5</sup>	Yes <sup>5</sup>
Read Request	No <sup>2</sup>	Yes	Yes	Yes	Yes
Non-posted Write Request	No <sup>2</sup>	Yes	Yes	Yes	Yes
Read Completion	Yes/No3	Yes	Yes	Yes	Yes
Non-Posted Write	Yes <sup>4</sup>	Yes	Yes	Yes	Yes
Completion					

- 1. When the Relaxed Ordering Attribute bit is cleared, the Posted Request transactions including memory write and message request must complete on the egress bus of VPPB in the order in which they are received on the ingress bus of VPPB. If the Relaxed Ordering Attribute bit is set, the Posted Request is permitted to pass over other Posted Requests occurring before it.
- 2. A Read Request transmitting in the same direction as a previously queued Posted Request transaction must push the posted write data ahead of it. The Posted Request transaction must complete on the egress bus before the Read Request can be attempted on the egress bus. The Read transaction can go to the same location as the Posted data. Therefore, if the Read transaction were to pass the Posted transaction, it would return stale data.
- 3. When the Relaxed Ordering Attribute bit is cleared, a Read completion must "pull" ahead of previously queued posted data transmitting in the same direction. In this case, the read data transmits in the same direction as the posted data, and the requestor of the read transaction is on the same side of the VPPB as the completer of the posted transaction. The posted transaction must deliver to the completer before the read data is returned to the requestor. If the Relaxed Ordering Attribute bit is set, then a read completion is permitted to pass a previously queued Memory Write or Message Request.
- 4. Non-Posted Write Completions are permitted to pass a previous Memory Write or Message Request transaction. Such transactions are actually transmitting in the opposite directions and hence have no ordering relationship.
- 5. Posted Request transactions must be given opportunities to pass Non-posted Read and Write Requests as well as Completions. Otherwise, deadlocks may occur when some older bridges, which do not support delayed transactions are mixed with PCIe Switch in the same system. A fairness algorithm is used to arbitrate between the Posted Write queue and the Non-posted transaction queue

#### 5.8 PORT ARBITRATION

Among multiple ingress ports, the port arbitration built in the egress port determines which incoming packets to be forwarded to the output port. The arbitration algorithm contains hardware fixed Round Robin, 128-phase Weighted Round-Robin and programmable 128-phase time-based WRR. The port arbitration is held within the same VC channel. It means that each port has two port arbitration circuitries for VC0 and VC1 respectively. At the upstream ports, in addition to the inter-port packets, the intra-port packet such as configurations completion would also join the arbitration loop to get the service from Virtual Channel 0.







### 5.9 VC ARBITRATION

After port arbitration, VC arbitration is executed among different VC channels within the same source. Three arbitration algorithms are provided to choose the appropriate VC: Strict Priority, Round Robin or Weighted Round Robin.

#### 5.10 FLOW CONTROL

PCI Express employs Credit-Based Flow Control mechanism to make buffer utilization more efficient. The transaction layer transmitter ensures that it does not transmit a TLP to an opposite receiver unless the receiver has enough buffer space to accept the TLP. The transaction layer receiver has the responsibility to advertise the free buffer space to an opposite transmitter to avoid packet stale. In this Switch, each port has its own separate queues for different traffic types and the credits are sent to data link layer on the fly. The data link layer compares the current available credits with the monitored ones and reports the updated credit to the counterpart. If no new credit is acquired, the credit reported is scheduled for every 30 us to prevent the link from entering retrain. On the other hand, the receiver at each egress port gets the usable credits from the opposite end in a link. The output port broadcasts them to all the other ingress ports to get packet transmission.

### 5.11 TRANSATION LAYER TRANSMIT BLOCK (TLP ENCAPSULATION)

The transmit portion of transaction layer performs the following functions. They construct the all types of forwarded TLP generated from VC arbiter, respond with the completion packets when the local resource (i.e. configuration register) is accessed, and regenerate the message that terminates at receiver to RC if acting as an upstream port.





## **6 EEPROM INTERFACE AND SYSTEM MANAGEMENT BUS**

The EEPROM interface consists of two pins: EECLK (EEPROM clock output) and EEPD (EEPROM bi-directional serial data). The Switch may control an ISSI IS24C04 or compatible parts using into 512x8 bits. The EEPROM is used to initialize a number of registers before enumeration. This is accomplished after PRST# is de-asserted, at which time the data from the EEPROM is loaded. The EEPROM interface is organized into a 16-bit base, and the Switch supplies a 7-bit EEPROM word address. The Switch does not control the EEPROM address input. It can only access the EEPROM with address input set to 0.

The System Management Bus interface consists of two pins: SMBCLK (System Management Bus Clock input) and SMBDATA (System Management Bus Data input/ output).

#### 6.1 EEPROMINTERFACE

#### 6.1.1 AUTO MODE EERPOM ACCESS

The Switch may access the EEPROM in a WORD format by utilizing the auto mode through a hardware sequencer. The EEPROM start-control, address, and read/write commands can be accessed through the configuration register. Before each access, the software should check the Autoload Status bit before issuing the next start.


#### 6.1.2 EEPROM MODE AT RESET

During a reset, the Switch will automatically load the information/data from the EEPROM if the automatic load condition is met. The first offset in the EEPROM contains a signature. If the signature is recognized, the autoload initiates right after the reset.

During the autoload, the Bridge will read sequential words from the EEPROM and write to the appropriate registers. Before the Bridge registers can be accessed through the host, the autoload condition should be verified by reading bit [3] offset DCh (EEPROM Autoload Status). The host access is allowed only after the status of this bit is set to '0' which indicates that the autoload initialization sequence is complete.

#### 6.1.3 EEPROM SPACE ADDRESS MAP

15 – 8	7 – 0	BYTE OFFSET
EEPROM Signature (1516h)		00h
Vend	lor ID	02h
Devi	ce ID	04h
Extended VC Count / Link Capability / Switch	Mode Operation / Interrupt pin for Port $1 \sim 2$	06h
Subsystem	Vender ID	08h
Subsys	tem ID	0Ah
Max_Payload_Size Support / ASPM	Support / Role_Base Error Reporting	0Ch
Global PHY TX Margin	Parameter for Port 0~2	0Eh
Global PHY Parameter 0 for Port 0~2		10h
Global XPIP_CSR6[0] / Global PHY Parameter 1 for Port 0~2		12h
Global XPIP_CSR6[4:1] / Global PHY Parameter 2/3 for Port 0~2		14h
Global XPIP_CSR4[15:0] for Port 0~2		16h
Global XPIP_CSR4[31:16] for Port 0~2		18h
Global XPIP_CSR5[15:0] for Port 0~2		1Ah
Buffer_ctrl[4:0] /	Global XPIP_CSR5[23:16] for Port 0~2	1 Ch
Globe XPIP_CSR6[7:5] for Port 0~2		
MAC_CTR / Global PHY Parameter 3 for Port 0~2		1Eh







15 -		7 – 0	BYTE OFFSET
		/ Deskw mode select for Port 0	20h
NFTS / Scramble / XPIP_CSR2 / Deskew mode select for Port 1		22h	
NFTS / Scramble / XPIP_XSR2 / Deskew mode select for Port 2		24h	
Reserved		26h 28h	
Reserved Reserved		28h	
		erved	2Ch
		erved	2Eh
		er2 1 for Port 0	30h
	PHY Paramet	er2_1 for Port 1	32h
	PHY Paramet	er2_1 for Port 2	34h
		erved	36h
		erved	38h
		erved	3Ah
		erved	3Ch
D 1 //		erved	3Eh
Do_change_rate_cnt/ XPIP_CSR_2 for Port 0	PHY Parame	eter 3/ PHY Parameter2_2 for Port 0	40h
Sel_deemp/ Do_change_rate_cnt/ XPIP_CSR_2 for Port 1	PHY Parame	eter 3/ PHY Parameter2_2 for Port 1	42h
Sel_deemp/ Do_change_rate_cnt/ XPIP_CSR_2 for Port 2	PHY Parame	eter 3/ PHY Parameter2_2 for Port 2	44h
	Res	erved	46h
	Res	erved	48h
		erved	4Ah
		erved	4Ch
		erved	4Eh
PM Data 1		PM Capability for Port 0	50h
PM Data t		PM Capability for Port 1 PM Capability for Port 2	52h 54h
r Wi Data i		erved	56h
		erved	58h
		erved	5Ah
Reserved			5Ch
	Res	erved	5Eh
TC/VC Map for Port 0 (VC0)		Slot Clock / LPVC Count / Port Num for Port 0	60h
TC/VC Map for Port 1 (VC0)		Slot Implemented   Slot Clock   LPVC Count     Port Num for Port 1	62h
T C/VC Map for Port 2 (VC0)  Slot Implemented / Slot Clock / LPVC ( / Port Num for Port 2		/ Port Num for Port 2	64h
		erved erved	66h 68h
		erved	6Ah
Reserved			6Ch
		erved	6Eh
J		bility Register for Port 0	70h
Power Budgeting Capability Register for Port 1		pility Register for Port 1	72h
	Power Budgeting Capability Register for Port 2		74h
	Power Budgeting Capal	Reserved	
	Res		76h
	Rese Rese	erved	78h
	Reso Reso Reso	erved erved	78h 7Ah
	Resi Resi Resi Resi	erved erved erved	78h 7Ah 7Ch
I	Resi Resi Resi Resi Resi	erved erved erved erved erved	78h 7Ah 7Ch 7Eh
XPIP_CSR5[30	Resi Resi Resi Resi Resi 24] for Port 0	erved erved erved erved erved PM Control Para/Rx Polarity for Port 0	78h 7Ah 7Ch 7Eh 80h
XPIP_CSR5[30 XPIP_CSR5[30	Resi Resi Resi Resi 24] for Port 0 24] for Port 1	erved erved erved erved PM Control Para/Rx Polarity for Port 0 PM Control Para/Rx Polarity for Port 1	78h 7Ah 7Ch 7Eh 80h 82h
XPIP_CSR5[30	Resi Resi Resi Resi 24] for Port 0 :24] for Port 1 :24] for Port 2	erved erved erved erved PM Control Para/Rx Polarity for Port 0 PM Control Para/Rx Polarity for Port 1 PM Control Para/Rx Polarity for Port 2	78h 7Ah 7Ch 7Eh 80h 82h 84h
XPIP_CSR5[30 XPIP_CSR5[30	Resi Resi Resi Resi 24] for Port 0 :24] for Port 1 :24] for Port 2	erved erved erved erved PM Control Para/Rx Polarity for Port 0 PM Control Para/Rx Polarity for Port 1	78h 7Ah 7Ch 7Eh 80h 82h







15 – 8	7 – 0	BYTE OFFSET
	Reserved	8Ch
	Reserved	8Eh
	Reserved	90h
Slot Cap	ability 0 for Port 1	92h
Slot Cap	ability 0 for Port 2	94h
	Reserved	96h
	Reserved	98h
	Reserved	9Ah
	Reserved	9Ch
	Reserved	9Eh
	Reserved	A0h
Slot Cap	ability 1 for Port 1	A2h
Slot Cap	ability 1 for Port 2	A4h
•	Reserved	A6h
	Reserved	A8h
	Reserved	AAh
	Reserved	ACh
	Reserved	AEh
XPIP CS	SR3[15:0] for Port 0	B0h
	SR3[15:0] for Port 1	B2h
	SR3[15:0] for Port 2	B4h
74 H _C	Reserved	B6h
	Reserved	B8h
	Reserved	BAh
	Reserved	BCh
	Reserved	BEh
VDID CS	R3[16:31] for Port 0	C0h
	R3[16:31] for Port 1	C2h
	R3[16:31] for Port 2	C4h
AFIF_CS	Reserved	C4n C6h
	Reserved	C8h
	Reserved	CAh
	Reserved	CCh
DELL'EC CED/D 1	Reserved	CEh
REV_IS_CIR/Repla	ay Time-out Counter for Port 0	D0h
REV_TS_CTR /Replay Time-out Counter for Port 1		D2h
REV_TS_CTR /Replay Time-out Counter for Port 2		D4h
	Reserved	D6h
Reserved		D8h DAh
	Reserved	
	Reserved	
Reserved		DEh
	Latency Timer for Port 0	E0h
	Latency Timer for Port 1	E2h
Acknowledge 1	Latency Timer for Port 2	E4h
	Reserved	E6h
	Reserved	E8h
	Reserved	EAh
	Reserved	ECh
	Reserved	EEh
TC/VC Map for Port 0 (VC1)	Maximum Time Slot for Port 0	F0h
TC/VC Map for Port 1 (VC1)	Maximum Time Slot for Port 0	F2h
TC/VC Map for Port 2 (VC1)	Maximum Time Slot for Port 0	F4h
	Reserved	F6h
	Reserved	F8h
	Reserved	FAh
	Reserved	
	Reserved	FCh FEh





# 6.1.4 MAPPING EEPROM CONTENTS TO CONFIGURATION REGISTERS

ADDRESS	PCI CFG OFFSET	DESCRIPTION
00h		EEPRO M signature – 1516h
02h	00h ~ 01h	VendorID
04h	02h ~ 03h	Device ID
06h	144h (Port 0~2)	Extended VC Count for Port 0~2
	144h: Bit [0]	<ul> <li>Bit [0]: It represents the supported VC count other than the default</li> </ul>
		VC
	CCh (Port 0~2)	Link Capability for Port 0~2
	CCh: Bit [14:12]	Bit [3:1]: It represents L0s Exit Latency for all ports
	CCh: Bit [17:15]	Bit [6:4]: It represents L1 Exit Latency for all ports
	74h (Port 0~2)	Switch Mode Operation for Port 0
	74h: Bit [5]	Bit [8]: no ordering on packets for different egress port mode
	74h: Bit [6]	Bit [9]: no ordering on different tag of completion mode
	74h: Bit [0]	Bit [10]: Store and Forward
	74h: Bit [2:1]	Bit [12:11]: Cut-through Threshold
	74h: Bit [3]	Bit [13]: Port arbitrator Mode
	74h: Bit [4]	Bit [14]: Credit Update Mode
	, III. Dit [1]	Bit [11]. Credit OptationTode
	3Ch (Port 1~2)	Interrupt pin for Port 1~2
	3Ch: Bit [8]	Bit [15]: Set when INTA is requested for interrupt resource
08h	B4h ~ B5h	Subsystem Vender ID
0Ah	B6h~B7h	Subsystem ID
0Ch	C4h (Port 0~2)	Max_Payload_Size Support for Port 0~2
o Ch	C4h (1010~2) C4h: Bit [1:0]	Bit [1:0]: Indicated the maximum payload size that the device can
	C III. Dit [1.0]	support for the TLP
		TT
	CCh (Port 0~2)	ASPM Support for Port 0~2
	CCh: Bit [11:10]	<ul> <li>Bit [3:2]: Indicate the level of ASPM supported on the PCIe link</li> </ul>
	, ,	
	C4h (Port0~2)	Role Base Error Reporting for Port 0~2
	C4h: Bit [15]	Bit [4]: Indicate implement the role-base error reporting
	70h (Port 0~2)	MSICapability Disable for Port 0~2
	70h: Bit [14]	<ul><li>Bit [5]: Disable MSI capability</li></ul>
	74h (Port 0~2)	Compliance Pattern Parity Control Disable for Port 0~2
	74h: Bit [15]	<ul> <li>Bit [6]: Disable compliance pattern parity</li> </ul>
	70h (Port 0~2)	Power Management Capability Disable for Port 0~2
	70h: Bit [13]	■ Bit [7]: Disable Power Management Capability
	8Ch (Port 0~2)	ORDER RULE5 Enable for port 0~2
	8Ch: Bit [5]	<ul> <li>Bit [8]: Capability for Post packet Pass Non-Post packet</li> </ul>
	CCh (Port 1~2)	Link Bandwidth Notification Capability for port 1~2
	CCh: Bit [21]	■ Bit [9]: Link Bandwidth Notification Capability
	0.C1 (D +0.0)	
	8Ch (Port 0~2)	Ordering Frozen for Port 0~2
	8Ch: Bit [6]	Bit [10]: Freeze the ordering feature
	9Ch (Dant 0 2)	TV COEL stance. Made for Dont 0. 2
	8Ch (Port 0~2) 8Ch: Bit [0]	TX SOFLatency Mode for Port0~2  Bit [11]: Set to zero to shorten latency
	oen. Dit [0]	Dit [11]. Set to zero to shorten latency
	CCh (Port 0~2)	Surprise Down C apability Enable for Port 0~2
	CCn (Port 0~2) CCh: Bit [19]	Bit [12]: Enable Surprise Down Capability
	CCII. Dit [17]	Dit [12]. Ditable outpribe Down Cupublity
	8Ch (Port0~2)	Power Management's Data Select Register R/W Capability for Port 0~2
	8Ch: Bit [1]	Bit [13]: Enable Data Select Register R/W
	E4h (Port 0~2)	LTR Capability Enable for Port 0~2
	E4h: Bit [12]	Bit [14]: LTR capability enable
	2 [12]	Site [1.1]. Site on province of the state of
	8Ch (Port 0~2)	4KB Boundary Check Enable for Port 0~2
	8Ch: Bit [3]	Bit [15]: Enable 4KB Boundary Check





ADDDECC	DCI CEC O EESET	DECCRIPTION
ADDRESS 0Eh	PCICFG OFFSET	DESC RIPTION PHY TX Margin Parameter for Port 0~2
OEII	<b>94h (Port 0~2)</b> 94h: Bit [4:0]	Bit [4:0]: C_DRV_LVL_3P5_MGN2
	94h: Bit [9:5]	Bit [9:5]: C_DRV_LVL_6P0_MGN2
	94h: Bit [14:10]	Bit [14:10]: C_DRV_LVL_HALF_MGN2
	, []	
	E4h (Port 0~2)	OBFF Capability Enable for Port 0~2
	E4h: Bit [18]	Bit [15]: enable OBFF capability
10h	74h (Port 0~2)	PHY Parameter 0 for Port 0~2
	74h: Bit [20:16]	<ul><li>Bit [4:0]: C_DRV_LVL_3P5_NOM</li></ul>
	74h: Bit [25:21]	<ul><li>Bit [9:5]: C_DRV_LVL_6P0_NOM</li></ul>
	74h: Bit [30:26]	<ul><li>Bit [14:10]: C_DRV_LVL_HALF_NOM</li></ul>
	8Ch (Port 0~2)	TL_CSR[31] for Port 0~2
12h	8Ch: Bit [31]	Bit [15]: P35_GEN2_MODE
1211	<b>78h (Port 0~2)</b> 78h: Bit [20:16]	PHY Parameter 1 for Port 0~2  Bit [4:0]: C_EMP_POST_GEN1_3P5_NOM
	78h: Bit [25:21]	Bit [9:5]: C EMP POST GEN2 3P5 NOM
	78h: Bit [30:26]	Bit [14:10]: C EMP POST GEN2 6P0 NOM
	, , , , , , , , , , , , , , , , , , , ,	(c. 1100), eT-110 To 000 T-110 17. 17. 17. 1
	8Ch (Port 0~2)	XPIP CSR6[0] for Port 0~2
	8Ch: Bit [16]	Bit [15]: XPIP_CSR6[0]
14h	7Ch (Port 0~2)	PHY Parameter 2 for Port 0~2
	7Ch: Bit [3:0]	<ul><li>Bit [3:0]: C_TX_PHY_LATENCY</li></ul>
	7Ch: Bit [6:4]	<ul><li>Bit [6:4]: C_REC_DETECT_USEC</li></ul>
	90h (Port 0~2)	PHY Parameter 3 for Port 0~2
	90h: Bit [19:15]	<ul><li>Bit [11:7]: C_EMP_POST_HALF_DELTA</li></ul>
	8Ch (Port 0~2)	XPIP CSR6[4:1] for Port0~2
	8Ch: Bit [20:17]	Bit [15:12]: XPIP_CSR6[4:1]
16h	84h (Port 0~2)	XPIP CSR4[15:0] for Port 0~2
	84h: Bit [15:0]	Bit [15:0]: XPIP_CSR4[15:0]
18h	84h (Port 0~2)	XPIP_CSR4[31:16] for Port 0~2
	84h: Bit [31:16]	<ul> <li>Bit [15:0]: XPIP_CSR4[31:16]</li> </ul>
1A	88h (Port 0~2)	XPIP_CSR5[15:0] for Port 0~2
1C	88h: Bit [15:0]	Bit [15:0]: XPIP_CSR5[15:0]
IC.	<b>88h (Port 0~2)</b> 88h: Bit [23:16]	XPIP_CSR5[28:16] for Port 0~2 Bit [7:0]: XPIP_CSR5[23:16]
	0011. Dit [23.10]	- Bit [7.0]. At it _ColO[25.10]
	8Ch (Port 0~2)	XPIP CSR6[7:5] for Port0~2
	8Ch: Bit [23:21]	Bit [10:8]: XPIP CSR6[7:5]
		. , ,
	98h (Port 0~2)	BUFFER_CTRL[4:0] for Port 0~2
	98h: Bit [20:16]	Bit [15:11]: Reference clock Buffer control
1E	90h (Port 0~2)	PHY parameter 3 for Port 0~2
	90h: Bit [21:20]	Bit [1:0]: C_DRV_LVL_3P5_DELTA
	90h: Bit [23:22] 90h: Bit [25:24]	<ul> <li>Bit [3:2]: C_DRV_LVL_6PO_DELTA</li> <li>Bit [5:4]: C_DRV_LVL_HALF_DELTA</li> </ul>
	90h: Bit [25:24] 90h: Bit [27:26]	Bit [5:4]: C_DRV_LVL_HALF_DELTA  Bit [7:6]: C_EMP_POST_GEN1_3P5_DELTA
	90h: Bit [29:28]	Bit [9:8]: C_EMP_POST_GEN2_3P5_DELTA
	90h: Bit [31:30]	Bit [11:10]: C EMP POST GEN2 6P0 DELTA
	, , , , , , , , , , , , , , , , , , , ,	
	8Ch (Port 0~2)	MAC control parameter for Port 0~2
	8Ch: Bit [29:26]	■ Bit [15:12]: MAC_CTR
20h	78h (Port 0)	FTS Number for Port 0
	78h: Bit [7:0]	■ Bit [7:0]: FTS number at receiver side
	(01 (D +0)	
	<b>68h (Port 0)</b> 68h: Bit [14:13]	Deskew Mode Select for Port 0  Bit [9:8]: deskew mode select
	0011. Dit [14.13]	- Dit [7.0], desired mode select
	78h (Port 0)	Scrambler Control for Port 0
	78h: Bit [9:8]	Bit [11:10]: scrambler control
	78h: Bit [10]	Bit [12]: L0s
	78h (Port 0)	Change_Speed_Sel for Port 0
	78h: Bit [13:12]	Bit [14:13]: Change Speed select





ADDRESS	PCI CFG OFFSET	DESCRIPTION
ADDRESS	78h (Port 0)	Change Speed En for Port 0
	78h: Bit [14]	Bit [15]: Change Speed enable
22h	<b>78h (Port 1)</b> 78h: Bit [7:0]	FTS Number for Port 1 Bit [7:0]: FTS number at receiver side
	<b>68h (Port 1)</b> 68h: Bit [14:13]	Deskew Mode Select for Port 01Bit [9:8]: deskew mode select
	<b>78h (Port 1)</b> 78h: Bit [9:8]	Scrambler Control for Port 1  Bit [11:10]: scrambler control
	78h: Bit [10]	■ Bit [12]: L0s
	<b>78h (Port 1)</b> 78h: Bit [13:12]	Change Speed Sel for Port 1 Bit [ 14:13]: Change Speed select
	<b>78h (Port 1)</b> 78h: Bit [14]	Change_Speed_En for Port 1 Bit [15]: Change Speed enable
24h	<b>78h (Port 2)</b> 78h: Bit [7:0]	FTS Number for Port2 Bit [7:0]: FTS number at receiver side
	<b>68h (Port 2)</b> 68h: Bit [14:13]	Deskew Mode Selectfor Port 2  Bit [9:8]: deskew mode select
	78h (Port 2)	Scrambler Control for Port 2
	78h: Bit [9:8] 78h: Bit [10]	<ul><li>Bit [11:10]: scrambler control</li><li>Bit [12]: L0s</li></ul>
	<b>78h (Port 2)</b> 78h: Bit [13:12]	Change_Speed_Sel for Port 2 Bit [14:13]: Change Speed select
	<b>78h (Port 2)</b> 78h: Bit [14]	Change_Speed_En for Port2 Bit [15]: Change Speed enable
30h	<b>7Ch (Port 0)</b> 7Ch: Bit [30:16]	PHY Parameter2_1 for Port 0 Bit [14:0]: PHY parameter 2
32h	<b>7Ch (Port 1)</b> 7Ch: Bit [30:16]	PHY Parameter 2 1 for Port 1 Bit [14:0]: PHY parameter 2
34h	7 <b>Ch (Port 2)</b> 7 <b>Ch</b> : Bit [30:16]	PHY Parameter 2 1 for Port 2 Bit [14:0]: PHY parameter 2
40h	7Ch (Port0) 7Ch: Bit [12:8]	PHY Parameter 2 1 for Port 0 Bit [4:0]: PHY parameter 2
	<b>90h (Port 0)</b> 90h: Bit [6:0]	PHY Parameter 3 for Port 0 Bit [11:5]: PHY parameter 3
	<b>F0h (Port 0)</b> F0h: Bit [6]	Selectable De-emphasis for Port 0  Bit [12]: Selectable De-emphasis
	<b>78h (Port 0)</b> 78h: Bit [11]	Compliance to Detect for Port 0 Bit [13]: compliance to detect
(2)	<b>8Ch (Port0)</b> 8Ch: Bit [9:8]	DO_CHG_DATA_CNT_SEL for Port 0  Bit [15:14]: DO_CHG_DATA_CNT_SEL
42h	7Ch (Port 1) 7Ch: Bit [12:8]	PHY Parameter 2_1 for Port 1 Bit [4:0]: PHY parameter 2
	90h (Port 1) 90h: Bit [6:0]	PHY Parameter 3 for Port 1 Bit [11:5]: PHY parameter 3
	<b>F0h (Port 0)</b> F0h: Bit [6]	Selectable De-emphasis for Port 1 Bit [12]: Selectable De-emphasis
	<b>78h (Port 1)</b> 78h: Bit [11]	Compliance to Detect for Port 1 Bit [13]: compliance to detect
	<b>8Ch (Port 1)</b> 8Ch: Bit [9:8]	DO_CHG_DATA_CNT_SEL for Port 1 - Bit [15:14]: DO_CHG_DATA_CNT_SEL
44h	7 <b>Ch (Port2)</b> 7 <b>Ch</b> : Bit [12:8]	PHY Parameter 2 1 for Port 2  Bit [4:0]: PHY parameter 2





ADDRESS	PCI CFG OFFSET	DESCRIPTION
	<b>90h (Port 2)</b> 90h: Bit [6:0]	PHY Parameter 3 for Port 2 Bit [11:5]: PHY parameter 3
	F0h (Port 2) F0h: Bit [6]	Selectable De-emphasis for Port 2  Bit [12]: Selectable De-emphasis
	<b>78h (Port 2)</b> 78h: Bit [11]	Compliance to Detect for Port 2 Bit [13]: compliance to detect
	<b>8Ch (Port2)</b> 8Ch: Bit [9:8]	DO_CHG_DATA_CNT_SEL for Port 2  Bit [15:14]: DO_CHG_DATA_CNT_SEL
50h	<b>44h (Port 0)</b> 44h: Bit [3]	No_Soft_Reset for Port 0 Bit [0]: No_Soft_Reset.
	<b>40h</b> ( <b>Port 0</b> ) 40h: Bit [24:22] 40h: Bit [25]	Power Management Capability for Port 0  Bit [3:1]: AUX Current. Bit [4]: read only as 1 to indicate Bridge supports the D1 power
	40h: Bit [26]	<ul> <li>management state</li> <li>Bit [5]: read only as 1 to indicate Bridge supports the D2 power management state</li> </ul>
51h	40h: Bit [29:28] 44h (Port 0) 44h: Bit [31:24]	<ul> <li>Bit [7:6]: PME Support for D2 and D1 states</li> <li>Power Management Data for Port 0</li> <li>Bit [15:8]: read only as Data register</li> </ul>
52h	44h (Port 1) 44h: Bit [3]	No_Soft_Reset for Port 1 Bit [0]: No_Soft_Reset.
	<b>40h (Port 1)</b> 40h: Bit [24:22]	Power Management Capability for Port 1 Bit [3:1]: AUX Current.
	40h: Bit [25]	Bit [4]: read only as 1 to indicate Bridge supports the D1 power management state    D1   D2   D3   D4   D4   D4   D5   D6   D7   D7   D7   D7   D7   D7   D7
	40h: Bit [26] 40h: Bit [29:28]	<ul> <li>Bit [5]: read only as 1 to indicate Bridge supports the D2 power management state</li> <li>Bit [7:6]: PME Support for D2 and D1 states</li> </ul>
53h	<b>44h (Port 1)</b> 44h: Bit [31:24]	Power Management Data for Port 1  Bit [15:8]: read only as Dataregister
54h	44h (Port 2) 44h: Bit [3]	No_Soft_Reset for Port 2 Bit [0]: No_Soft_Reset
	<b>40h</b> ( <b>Port 2</b> ) 40h: Bit [24:22] 40h: Bit [25]	Power Management Capability for Port 2  Bit [3:1]: AUX Current Bit [4]: read only as 1 to indicate Bridge supports the D1 power
	40h: Bit [26]	<ul> <li>management state</li> <li>Bit [5]: read only as 1 to indicate Bridge supports the D2 power management state</li> </ul>
55h	40h: Bit [29:28] 44h (Port 2)	Bit [7:6]: PME Support for D2 and D1 states  Power Management Data for Port 2
60h	44h: Bit [31:24] <b>D0h (Port0)</b>	Bit [15:8]: read only as Data register  Slot Clock Configuration for Port 0
	D0h: Bit [28]	Bit [1]: When set, the component uses the clock provided on the connector
	<b>40h (Port 0)</b> 40h: Bit[21]	Device specific Initialization for Port 0  Bit [2]: When set, the DSI is required
	144h (Port 0) 144h: Bit [4]	LPVC Countfor Port0 Bit [3]: When set, the VC1 is allocated to LPVC of Egress Port 0
	CCh (Port 0) CCh: Bit [26:24]	Port Number for Port 0  Bit [6:4]: It represents the logic port numbering for physical port 0
	<b>154h (Port 0)</b> 154h: Bit [7:1]	VC0 TC/VC Map for Port 0 ■ Bit [15:9]: When set, it indicates the corresponding TC is mapped into VC0





ADDRESS	PCI CFG OFFSET	DESCRIPTION
62h	C0h (Port1)	PCIe Capability Slot Implemented for Port 1
\(\frac{1}{2}\)!	Con (1011) Coh: Bit [24]	Bit [0]: When set, the slot is implemented for Port 1
	D0h (Dout1)	Slot Clark Conformation for Don't 1
	D0h (Port 1) D0h: Bit [28]	Slot Clock Configuration for Port 1  Bit [1]: When set, the component uses the clock provided on the
	Don. Bit [20]	Connector
	40h (Do-41)	Device specific Initialization for Port 1
	<b>40h (Port 1)</b> 40h: Bit [21]	Bit [2]: When set, the DSI is required
	<b>144h (Port 1)</b> 144h: Bit [4]	LPVC Countfor Port1 Bit [3]: When set, the VC1 is allocated to LPVC of Egress Port 1
	144II. Dit [4]	Bit [5]. Whenset, the Ver Is unocated to Er Ve of Egress 1 (it i
	CCh (Port 1)	Port Number for Port 1
	CCh: Bit [26:24] 154h (Port 1)	Bit [6:4]: It represents the logic port numbering for physical port 1  VC0 TC/VC Map for Port 1
	154h: Bit [7:1]	Bit [15:9]: When set, it indicates the corresponding TC is mapped
		into VC0
64h	C0h (Port 2) C0h: Bit [24]	PCIe Capability Slot Implemented for Port 2  Bit [0]: When set, the slot is implemented for Port 2
	Con. Dit [24]	Dit [0]. When set, the stot is implemented for 1 of t2
	D0h (Port2)	Slot Clock Configuration for Port 2
	D0h: Bit [28]	<ul> <li>Bit [1]: When set, the component uses the clock provided on the Connector</li> </ul>
		Connector
	40h (Port 2)	Device specific Initialization for Port 2
	40h: Bit [21]	■ Bit [2]: When set, the DSI is required
	144h (Port2)	LPVC Countfor Port 2
	144h: Bit [4]	■ Bit [3]: When set, the VC1 is allocated to LPVC of Egress Port 2
	CCh (Port 2)	Port Number for Port 2
	CCh: Bit [26:24]	Bit [6:4]: It represents the logic port numbering for physical port 2
	154h (Port2)	VC0 TC/VC Map for Port 2
	154h: Bit [7:1]	<ul> <li>Bit [15:9]: When set, it indicates the corresponding TC is mapped into VC0</li> </ul>
70h	214h (Port 0)	Power Budget Register for Port 0
	214h: Bit [7:0]	Bit [7:0]: Base Power
	214h: Bit [9:8] 214h: Bit [14:13]	<ul> <li>Bit [9:8]: Data Scale</li> <li>Bit [11:10]: PM State</li> </ul>
	218h: Bit [0]	Bit [15]: System Allocated
72h	214h (Port 1)	Power Budget Register for Port 1
	214h: Bit [7:0] 214h: Bit [9:8]	<ul> <li>Bit [7:0]: Base Power</li> <li>Bit [9:8]: Data Scale</li> </ul>
	214h: Bit [9.8] 214h: Bit [14:13]	Bit [11:10]: PM State
7.11	218h: Bit [0]	<ul> <li>Bit [15]: System Allocated</li> </ul>
74h	<b>214h (Port2)</b> 214h: Bit [7:0]	Power Budget Register for Port 2  Bit [7:0]: Base Power
	214h: Bit [9:8]	Bit [9:8]: Data Scale
	214h: Bit [14:13]	<ul> <li>Bit [11:10]: PM State</li> </ul>
80h	218h: Bit [0] 74h (Port 0)	Bit [15]: System Allocated  PM Control Parameter for Port 0
OUII	74h (Port 0) 74h: Bit [13:8]	Bit [1:0]: D3 enters L1
		Bit [3:2]: L1 delay count select
	74h · Bit [14]	Bit [5:4]: L0s enable Bit [6]: Disable Rx polarity capability
	74h: Bit [14]	- Dit [0] . Disable KX polarity capability
	70h (Port 0)	VGA Decode Enable for Port 0
	70h: Bit [31]	■ Bit [7]: Enable VGA decode
	88h (Port 0)	XPIP CSR5[31:24] for Port 0
	88h: Bit [31:24]	Bit[15:8]: XPIP_CSR5[31:24]





ADDDECC	DCI CEC O EEGER	DESCRIPTION
ADDRESS 82h	PCI CFG OFFSET 74h (Port 1)	DESCRIPTION PM Control Parameter for Port 1
0211	74h (Port 1) 74h: Bit [13:8]	Bit [1:0]: D3 enters L1
	/4II. Dit [13.0]	Bit [3:2]: L1 delay count select
		Bit [5:4]: L0s enable
	74h: Bit [14]	Bit [6]: Disable Rx polarity capability
	, []	[-]
	70h (Port 1)	VGA Decode Enable for Port 1
	70h: Bit [31]	■ Bit [7]: Enable VGA decode
	88h (Port 1)	XPIP_CSR5[31:24] for Port 1
	88h: Bit [31:24]	■ Bit[15:8]: XPIP_CSR5[31:24]
84h	74h (Port 2)	PM Control Parameter for Port 2
	74h: Bit [13:8]	<ul> <li>Bit [1:0]: D3 enters L1</li> <li>Bit [3:2]: L1 delay count select</li> </ul>
		Bit [5:4]: L0s enable
	74h: Bit [14]	Bit [6]: Disable Rx polarity capability
	/4II. Dit [14]	Dit [0]. Disuble tex potatity capability
	70h (Port 2)	VGA Decode Enable for Port 2
	70h: Bit [31]	<ul> <li>Bit [7]: Enable VGA decode</li> </ul>
	88h (Port 2)	XPIP_CSR5[31:24] for Port 2
	88h: Bit [31:24]	■ Bit[15:8]: XPIP_CSR5[31:24]
92h	D4h (Port1)	Slot Capability 0 of Port 1
94h	D4h: Bit [15:0]	Bit [15:0]: Mapping to the low word of slot capability register
9411	<b>D4h (Port2)</b> D4h: Bit [15:0]	Slot Capability 0 of Port 2  Bit [15:0]: Mapping to the low word of slot capability register
A2h	D4h. Bit [13.0]	Slot Capability 1 of Port 1
71211	D4h: Bit [31:16]	Bit [15:0]: Mapping to the high word of slot capability register
A4h	D4h (Port2)	Slot Canability 1 of Port 2
	D4h: Bit [31:16]	<ul> <li>Bit [15:0]: Mapping to the high word of slot capability register</li> </ul>
B0h	80h (Port 0)	XPIP_CSR3_0 for Port 0
	80h: Bit [15:0]	■ Bit [15:0]: XPIP_CSR3[15:0]
B2h	80h (Port 1)	XPIP_CSR3_0 for Port 1
B4h	80h: Bit [15:0] 80h (Port 2)	Bit [15:0]: XPIP_CSR3[15:0]  XPIP_CSR3_0 for Port 2
DHII	80h: Bit [15:0]	Bit [15:0]: XPIP CSR3[15:0]
C0h	80h (Port 0)	XPIP CSR3 1 for Port 0
	80h: Bit [31:16]	Bit [15:0]: XPIP_CSR3[31:16]
C2h	80h (Port 1)	XPIP CSR3 1 for Port 1
	80h: Bit [31:16]	■ Bit [15:0]: XPIP_CSR3[31:16]
C4h	80h (Port 2)	XPIP_CSR3_1 for Port 2
D0h	80h: Bit [31:16]	Bit [15:0]: XPIP_CSR3[31:16]
ווועם	<b>70h (Port 0)</b> 70h: Bit [12:0]	Replay Time-out Counter for Port 0  Bit [12:0]: Relay Time-out Counter
	, on. Dit [12.0]	Sit [12.0]. Rolly I also out Counter
	8Ch (Port0)	REV TS CTR for Port 0
	8Ch: Bit [25:24]	■ Bit [14:13] REV_TS_CTR
D2h	70h (Port 1)	Replay Time-out Counterfor Port 1
	70h: Bit [12:0]	Bit [12:0]: Relay Time-out Counter
	0CL (D. (1)	DEN TO CODE D 44
	8Ch (Port1) 8Ch: Bit [25:24]	REV_TS_CTR for Port 1 Bit [14:13] REV TS CTR
D4h	70h (Port 2)	Replay Time-out Counterfor Port2
2 111	70h (10h 2) 70h: Bit [12:0]	Bit [12:0]: Relay Time-out Counter
	8Ch (Port2)	REV_TS_CTR for Port 2
	8Ch: Bit [25:24]	■ Bit [14:13] REV_TS_CTR
E0h	70h (Port 0)	Acknowledge Latency Timer for Port 0
E2h	70h: Bit [30:16]	Bit [30:16]: Acknowledge Latency Timer
E2II	<b>70h (Port 1)</b> 70h: Bit [30:16]	Acknowledge Latency Timer for Port 1  Bit [30:16]: Acknowledge Latency Timer
E4h	70h: Bit [30:16]	Acknowledge Latency Timer for Port 2
Lin	70h (1 0h 2) 70h: Bit [30:16]	Bit [30:16]: Acknowledge Latency Timer
L	21 [20.10]	1 Die [ St. 1 o ] . Termonie ago Datenoj Time





ADDRESS	PCI CFG OFFSET	DESCRIPTION
F0h	<b>15Ch (Port 0)</b> 15Ch: Bit [22:16]	VC1 MAXTime Slot and TC/VC Map for Port 0 Bit [6:0]: The maximum time slot supported by VC1
	<b>160h (Port0)</b> 160h: Bit [7:0]	TC/VC Map for Port0 Bit [15:8]: When set, it indicates the corresponding TC is mapped into VC1
F2h	<b>15Ch (Port 1)</b> 15Ch: Bit [22:16]	VC1 MAX Time Slot and TC/VC Map for Port 1 Bit [6:0]: The maximum time slot supported by VC1
	<b>160h (Port 1)</b> 160h: Bit [7:0]	TC/VC Map for Port1 Bit [15:8]: When set, it indicates the corresponding TC is mapped into VC1
F4h	<b>15Ch (Port 2)</b> 15Ch: Bit [22:16]	VC1 MAX Time Slot and TC/VC Map for Port 2  Bit [6:0]: The maximum time slot supported by VC1
	<b>160h (Port2)</b> 160h: Bit [7:0]	TC/VC Map for Port 2 Bit [15:8]: When set, it indicates the corresponding TC is mapped into VC1





#### 6.2 SMBus INTERFACE

The PI7C9X2G303EL provides the System Management Bus (SMBus), a two-wire interface through which a simple device can communicate with the rest of the system. The SMBus interface on the PI7C9X2G303EL is a bi-directional slave interface. It can receive data from the SMBus master or send data to the master. The interface allows full access to the configuration registers. A SMBus master, such as the processor or other SMBus devices, can read or write to every RW configuration register (read/write register). In addition, the RO and HwInt registers (read-only and hardware initialized registers) that can be auto-loaded by the EEPROM interface can also be read and written by the SMBus interface. This feature allows increases in the system expandability and flexibility in system implementation.

Processor (SMBus Master)

Other SMBus Devices

SMBCLK
SMBDATA

Figure 6-1 SMBus Architecture Implementation on PI7C9X2G303EL

The SMBus interface on the PI7C9X2G303EL consists of one SMBus clock pin (SMBCLK), a SMBus data pin (SMBDATA), and 3 SMBus address pins (GPIO[5:7]). The SMBus clock pin provides or receives the clock signal. The SMBus data pin facilitates the data transmission and reception. Both of the clock and data pins are bidirectional. The SMBus address pins determine the address to which the PI7C9X2G303EL responds to. The SMBus address pins generate addresses according to the following table:

Table 6-1 SMBus Address Pin Configuration

BIT	SMBus Address
0	GPIO[5]
1	GPIO[6]
2	GPIO[7]
3	1
4	0
5	1
6	1





## 7 REGISTER DESCRIPTION

#### 7.1 REGISTER TYPES

REGISTER TYPE	DEFINITIO N
HwInt	Hardware Initialization
RO	Read Only
RW	Read/Write
RWC	Read / Write 1 to Clear
RWCS	Sticky – Read Only / Write 1 to Clear
RWS	Sticky – Read/Write
ROS	Sticky – Read Only

#### 7.2 TRANSPARENT MODE CONFIGURATION REGISTERS

When the port of the Switch is set to operate at the transparent mode, it is represented by a logical PCI-to-PCI Bridge that implements type 1 configuration space header. The following table details the allocation of the register fields of the PCI 2.3 compatible type 1 configuration space header.

31 –24	23 – 16	15 – 8	7 –0	BYTE OFFSET 00h			
	Device ID		Vendor ID				
Primar	y Status	Com	mand	04h			
	Class Code		Revision ID	08h			
Reserved	Header Type	Primary Latency Timer	Cache Line Size	0Ch			
		erved		10h – 17h			
Secondary Latency Timer	Subordinate Bus Number	Secondary Bus Number	Primary Bus Number	18h			
Seconda	ary Status	I/O Limit Address	I/O Base Address	1Ch			
	imit Address	Memory B	ase Address	20h			
Prefetchable Men	nory Limit Address	Prefetchable Men	nory Base Address	24h			
		Base Address Upper 32-bit		28h			
	Prefetchable Memory L	imit Address Upper 32-bi	it	2Ch			
I/O Limit Addr	ess Upper 16-bit	I/O Base Addre		30h			
	Reserved		Capability Pointer to 80h(40h)	34h			
	Res	erved	` ` `	38h			
Bridge	Control	Interrupt Pin	Interrupt Line	3Ch			
Power Manager	Power Management Capabilities		Capability ID=01	40h			
PM Data	PPB Support Extensions	Power Management Data		44h			
Message	e Control	Next Item Pointer=: 64	Capability ID=05	4Ch			
	Messag	e Address		50h			
	Message U	pper Address		54h			
Res	erved	Messag	ge Data	58h			
VPD I	Register	Next Item Pointer=64	Capability ID=03	5Ch			
	VPD Da	ta Register		60h			
Length in	Bytes (34h)	Next Item Pointer=B0	Capability ID=09	64h			
	XPIP	_CSR0		68h			
	XPIP	CSR1		6Ch			
ACK Late	ency Timer	Replay Time-out Counter		70h			
	rameter 0	Switch Modes		74h			
PHY Pa	rameter 1	XPIP_CSR2		78h 7Ch			
	PHY Parameter 2						
	XPIP_CSR3						
		CSR4		84h			
·		CSR5		88h			
XPIP_CSR7	XPIP_CSR6	TL	_CSR	8Ch			





31 –24	31 –24 23 – 16		7 –0	BYTE OFFSET		
	PHY parameter 3					
Reserved	PHYL1 RXEQ	PHY TX Mar	rgin parameter	94h		
Reserved	Buffer Ctrl	OP I	Mode	98h		
	Res	erved		(9Ch – ACh)		
Rese	erved	Next Item Pointer=C0	SSID/SSVID	B0h		
			Capability ID=0D			
SS	AID .	SSV	ЛD	B4h		
		and Control		B8h		
	OM Data	EEPROM Address	EEPROM Control	BCh		
PCI Express Cap	pabilities Register	Next Item Pointer=00	Capability ID=10	C0h		
	Device C	Capabilities		C4h		
Device	Status	Device Control		C8h		
		apabilities		CCh		
Link	Status	Link C	Control	D0h		
	Slot Capabilities					
Slot	Status	Slot C	ontrol	D8h		
	Res	erved		DCh		
	Res	erved		E0h		
	Device Capabilities 2					
	Device Status / Control 2					
	ECh					
	Link Status /Control 2					
	Slot Capabilities 2					
		s /Control 2		F8h		
	Res	erved		FCh		

Other than the PCI 2.3 compatible configuration space header, the Switch also implements PCI express extended configuration space header, which includes advanced error reporting, virtual channel, and power budgeting capability registers. The following table details the allocation of the register fields of PCI express extended capability space header. The first extended capability always begins at offset 100h with a PCI Express Enhanced Capability header and the rest of capabilities are located at an offset greater than 0FFh relative to the beginning of PCI compatible configuration space.

31 –24		- 16	15 - 8	7 –0	BYTE OFFSET	
Next Capability Offs	set=140h	Cap. Version	PCI Express Extende	d Capability ID=0001h	100h	
	104h					
	Unc	orrectable En	ror Mask Register		108h	
	Unco	rrectable Erro	or Severity Register		10Ch	
	Cor	rrectable Erro	r Status Register		110h	
	Co:	rrectable Erro	or Mask Register		114h	
	Advanced E	Error Capabili	ties and Control Registe	r	118h	
		Header Lo	g Register		11Ch – 128h	
		Rese	rved		12Ch – 13Fh	
Next Capability Offs	et=20Ch	Cap. Version	PCI Express Extende	d Capability ID=0002h	140h	
	P	ort VC Capab	ility Register 1		144h	
VC Arbitration Table Offset=3		148h				
Port VC St	atus Register	r	Port VC Co	ntrol Register	14Ch	
Port Arbitration Table Offset=4		VC Re	source Capability Regist	ter (0)	150h	
	VC	Resource Cor	ntrol Register (0)		154h	
VC Resource St				erved	158h	
Port Arbitration Table Offset=6		VC Re	source Capability Regist	ter (1)	15Ch	
	VC	Resource Cor	ntrol Register (1)		160h	
VC Resource St	VC Resource Status Register (1) Reserved					
	Reserved					
	VC Arbitration Table with 32 Phases					
	Port Arbiti	ation Table v	vith 128 Phases for VCC	)	180h – 1BCh	
	Port Arbiti	ation Table v	vith 128 Phases for VC1		1C0h – 1FCh	
		Rese	rved		200h – 20Bh	





31 –24	23 – 16		15		7 –0	BYTE OFFSET
Next Capability Offs	Next Capability Offset=220/230h Cap.		PCI Expr	ess Extende	d Capability ID=0004h	20Ch
		Version				
	Rese	erved			Data Select Register	210h
		Data F	Register			214h
	Rese	erved			Power Budget	218h
					Capability Register	
	Rese	erved				21Ch
Next Capability C	ffset=000h	Cap	PCI Expre	PCI Express Extended Capability ID=000Dh		220h
		version				
AC	S Control		ACS Capability		224h	
	Reserved				Egress Control Vector	228h
	Rese					22Ch
Next Capability C	ffset=000h	Cap	PCI Expr	ess Extended	d Capability ID=0018h	230h
version				-		
Reserved Max No	- Max N	o-Snoop	Reserved	Max	Max Snoop Latency	234h
Snoop	Laten	cy Value		Snoop	Value	
Latenc	7	-		Latency		
Scale				Scale		

## 7.2.1 VENDOR ID REGISTER - OFFSET 00h

BIT	FUNCTION	TYPE	DESCRIPTION
15:0	Vendor ID	RO	Identifies Pericom as the vendor of this device. The default value may be
			changed by SMBus or auto-loading from EEPROM.
			Reset to 12D8h.

# 7.2.2 DEVICE ID REGISTER - OFFSET 00h

BIT	FUNCTION	TYPE	DESCRIPTION
31:16	Device ID	RO	Identifies this device as the PI7C9X2G303EL. The default value may be changed by SMBus or auto-loading from EEPROM.
			Resets to 2303h.

## 7.2.3 COMMAND REGISTER - OFFSET 04h

BIT	FUNCTION	TYPE	DESCRIPTION
0	I/O Space Enable	RW	0b: Ignores I/O transactions on the primary interface 1b: Enables responses to I/O transactions on the primary interface Resets to 0b.
1	Memory Space Enable	RW	0b: Ignores memory transactions on the primary interface 1b: Enables responses to memory transactions on the primary interface Reset to 0b.
2	Bus Master Enable	RW	0b: Does not initiate memory or I/O transactions on the upstream port and handles as an Unsupported Request (UR) to memory and I/O transactions on the downstream port. For Non-Posted Requests, a completion with UR completion status must be returned  1b: Enables the Switch Port to forward memory and I/O Read/Write transactions in the upstream direction  Reset to 0b.
3	Special Cycle Enable	RO	Does not apply to PCI Express. Must be hardwired to 0b.
4	Memory Write And Invalidate Enable	RO	Does not apply to PCI Express. Must be hardwired to 0b.
5	VGA Palette Snoop	RO	Does not apply to PCI Express. Must be hardwired to 0b.






BIT	FUNCTIO N	TYPE	DESCRIPTION
	Enable		
6	Parity Error Response Enable	RW	Ob: Switch may ignore any parity errors that it detects and continue normal operation  1b: Switch must take its normal action when a parity error is detected  Reset to 0b.
7	Wait Cycle Control	RO	Does not apply to PCI Express. Must be hardwired to 0.
8	SERR# enable	RW	0b: Disables the reporting of Non-fatal and Fatal errors detected by the Switch to the Root Complex b1: Enables the Non-fatal and Fatal error reporting to Root Complex Reset to 0b.
9	Fast Back-to-Back Enable	RO	Does not apply to PCI Express. Must be hardwired to 0b.
10	Interrupt Disable	RW	Controls the ability of a PCI Express device to generate INTx Interrupt Messages. In the Switch, this bit does not affect the forwarding of INTx messages from the downstream ports.  Reset to 0b.
15:11	Reserved	RsvdP	Not Support.

## 7.2.4 PRIMARY STATUS REGISTER - OFFSET 04h

BIT	FUNCTION	TYPE	DESCRIPTION
18:16	Reserved	RsvdP	Not Support.
19	Interrupt Status	RO	Indicates that an INTx Interrupt Message is pending internally to the device. In the Switch, the forwarding of INTx messages from the downstream device of the Switch port is not reflected in this bit. Must be hardwired to 0b.
20	Capabilities List	RO	Set to 1 to enable support for the capability list (offset 34h is the pointer to the data structure).  Reset to 1b.
21	66MHz Capable	RO	Does not apply to PCI Express. Must be hardwired to 0b.
22	Reserved	RsvdP	Not Support.
23	Fast Back-to-Back Capable	RO	Does not apply to PCI Express. Must be hardwired to 0b.
24	Master Data Parity Error	RWC	Set to 1 (by a requester) whenever a Parity error is detected or forwarded on the primary side of the port in a Switch.  If the Parity Error Response Enable bit is cleared, this bit is never set.  Reset to 0b.
26:25	DEVSEL# timing	RO	Does not apply to PCI Express. Must be hardwired to 0b.
27	Signaled Target Abort	RO	Set to 1 (by a completer) whenever completing a request on the primary side using the Completer Abort Completion Status.  Reset to 0b.
28	Received Target Abort	RO	Set to 1 (by a requestor) whenever receiving a Completion with Completer Abort Completion Status on the primary side.  Reset to 0b.
29	Received Master Abort	RO	Set to 1 (by a requestor) whenever receiving a Completion with Unsupported Request Completion Status on primary side.  Reset to 0b.
30	Signaled System Error	RWC	Set to 1 when the Switch sends an ERR_FATAL or ERR_NONFATAL Message, and the SERR Enable bit in the Command register is 1.  Reset to 0b.
31	Detected Parity Error	RWC	Set to 1 whenever the primary side of the port in a Switch receives a Poisoned TLP.  Reset to 0b.







#### 7.2.5 REVISION ID REGISTER - OFFSET 08h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Revision	RO	Indicates revision number of device. Hardwired to 05h.

#### 7.2.6 CLASS CODE REGISTER - OFFSET 08h

BIT	FUNCTION	TYPE	DESCRIPTION
15:8	Programming	RO	Read as 00h to indicate no programming interfaces have been defined for
	Interface		PCI-to-PCI Bridges.
23:16	Sub-Class Code	RO	Read as 04h to indicate device is a PCI-to-PCI Bridge.
31:24	Base Class Code	RO	Read as 06h to indicate device is a Bridge device.

#### 7.2.7 CACHE LINE REGISTER - OFFSET 0Ch

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Cache Line Size	RW	The cache line size register is set by the system firmware and the operating system cache line size. This field is implemented by PCI Express devices as a RW field for legacy compatibility, but it has no impact on any PCI Express device functionality.  Reset to 00h.

#### 7.2.8 PRIMARY LATENCY TIMER REGISTER – OFFSET 0Ch

BIT	FUNCTION	TYPE	DESCRIPTION
15:8	Primary Latency timer	RO	Does not apply to PCI Express. Must be hardwired to 00h.

#### 7.2.9 HEADER TYPE REGISTER - OFFSET 0Ch

BIT	FUNCTION	TYPE	DESCRIPTION
23:16	Header Type	RO	Read as 01h to indicate that the register layout conforms to the standard PCI-to-PCI Bridge layout.

## 7.2.10 PRIMARY BUS NUMBER REGISTER - OFFSET 18h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Primary Bus Number	RW	Indicates the number of the PCI bus to which the primary interface is connected. The value is set in software during configuration.
			Reset to 00h.

## 7.2.11 SECONDARY BUS NUMBER REGISTER - OFFSET 18h

BIT	FUNCTION	TYPE	DESCRIPTION
15:8	Secondary Bus Number	RW	Indicates the number of the PCI bus to which the secondary interface is connected. The value is set in software during configuration.
	- 1,022200		Reset to 00h.





#### 7.2.12 SUBORDINATE BUS NUMBER REGISTER - OFFSET 18h

BIT	FUNCTION	TYPE	DESCRIPTION
23:16	Subordinate Bus Number	RW	Indicates the number of the PCI bus with the highest number that is subordinate to the Bridge. The value is set in software during configuration.  Reset to 00h.

## 7.2.13 SECONDARY LATENCY TIMER REGISTER - OFFSET 18h

BIT	FUNCTION	TYPE	DESCRIPTION
31:24	Secondary Latency Timer	RO	Does not apply to PCI Express. Must be hardwired to 00h.

#### 7.2.14 VO BASE ADDRESS REGISTER - OFFSET 1Ch

BIT	FUNCTION	TYPE	DESCRIPTION
3:0	32-bit Indicator	RO	Read as 01h to indicate 32-bit I/O addressing.
7:4	I/O Base Address [15:12]	RW	Defines the bottom address of the I/O address range for the Bridge to determine when to forward I/O transactions from one interface to the other. The upper 4 bits correspond to address bits [15:12] and are writable. The lower 12 bits corresponding to address bits [11:0] are assumed to be 0. The upper 16 bits corresponding to address bits [31:16] are defined in the I/O base address upper 16 bits address register.  Reset to 0h.

## 7.2.15 VO LIMIT ADDRESS REGISTER - OFFSET 1Ch

BIT	FUNCTION	TYPE	DESCRIPTION
11:8	32-bit Indicator	RO	Read as 01h to indicate 32-bit I/O addressing.
15:12	I/O Limit Address [15:12]	RW	Defines the top address of the I/O address range for the Bridge to determine when to forward I/O transactions from one interface to the other. The upper 4 bits correspond to address bits [15:12] and are writable. The lower 12 bits corresponding to address bits [11:0] are assumed to be FFFh. The upper 16 bits corresponding to address bits [31:16] are defined in the I/O limit address upper 16 bits address register.  Reset to 0h.

## 7.2.16 SECONDARY STATUS REGISTER - OFFSET 1Ch

BIT	FUNCTION	TYPE	DESCRIPTION
20:16	Reserved	RsvdP	Not Support.
21	66MHz Capable	RO	Does not apply to PCI Express. Must be hardwired to 0b.
22	Reserved	RsvdP	Not Support.
23	Fast Back-to-Back Capable	RO	Does not apply to PCI Express. Must be hardwired to 0b.
			Set to 1 (by a requester) whenever a Parity error is detected or forwarded on the secondary side of the port in a Switch.
24	Master Data Parity Error	RWC	If the Parity Error Response Enable bit is cleared, this bit is never set.
			Reset to 0b.





BIT	FUNCTION	TYPE	DESCRIPTION
26:25	DEVSEL_L timing	RO	Does not apply to PCI Express. Must be hardwired to 0b.
27	Signaled Target Abort	RO	Set to 1 (by a completer) whenever completing a request in the secondary side using Completer Abort Completion Status.  Reset to 0b.
28	Received Target Abort	RO	Set to 1 (by a requestor) whenever receiving a Completion with Completer Abort Completion Status in the secondary side.  Reset to 0b.
29	Received Master Abort	RO	Set to 1 (by a requestor) whenever receiving a Completion with Unsupported Request Completion Status in secondary side.  Reset to 0b.
30	Received System Error	RWC	Set to 1 when the Switch sends an ERR_FATAL or ERR_NONFATAL Message, and the SERR Enable bit in the Bridge Control register is 1.  Reset to 0b.
31	Detected Parity Error	RWC	Set to 1 whenever the secondary side of the port in a Switch receives a Poisoned TLP.  Reset to 0b.

## 7.2.17 MEMORY BASE ADDRESS REGISTER - OFFSET 20h

BIT	FUNCTION	TYPE	DESCRIPTION
3:0	Reserved	RsvdP	Not Support.
15:4	Memory Base Address [15:4]	RW	Defines the bottom address of an address range for the Bridge to determine when to forward memory transactions from one interface to the other. The upper 12 bits correspond to address bits [31:20] and are able to be written to. The lower 20 bits corresponding to address bits [19:0] are assumed to be 0.  Reset to 000h.

## 7.2.18 MEMORY LIMIT ADDRESS REGISTER - OFFSET 20h

BIT	FUNCTION	TYPE	DESCRIPTION
19:16	Reserved	RsvdP	Not Support.
31:20	Memory Limit Address [31:20]	RW	Defines the top address of an address range for the Bridge to determine when to forward memory transactions from one interface to the other. The upper 12 bits correspond to address bits [31:20] and are writable. The lower 20 bits corresponding to address bits [19:0] are assumed to be FFFFFh.  Reset to 000h.

## 7.2.19 PREFETCHABLE MEMORY BASE ADDRESS REGISTER - OFFSET 24h

BIT	FUNCTION	TYPE	DESCRIPTION
3:0	64-bit addressing	RO	Read as 0001b to indicate 64-bit addressing.
15:4	Prefetchable Memory Base Address [31:20]	RW	Defines the bottom address of an address range for the Bridge to determine when to forward memory read and write transactions from one interface to the other. The upper 12 bits correspond to address bits [31:20] and are writable. The lower 20 bits are assumed to be 0. The memory base register upper 32 bits contain the upper half of the base address.  Reset to 000h.







#### 7.2.20 PREFETCHABLE MEMORY LIMIT ADDRESS REGISTER - OFFSET 24h

BIT	FUNCTION	TYPE	DESCRIPTION
19:16	64-bit addressing	RO	Read as 0001b to indicate 64-bit addressing.
31:20	Prefetchable Memory Limit Address [31:20]	RW	Defines the top address of an address range for the Bridge to determine when to forward memory read and write transactions from one interface to the other. The upper 12 bits correspond to address bits [31:20] and are writable. The lower 20 bits are assumed to be FFFFFh. The memory limit upper 32 bits register contains the upper half of the limit address.  Reset to 000h.

# 7.2.21 PREFETCHABLE MEMORY BASE ADDRESS UPPER 32-BITS REGISTER – OFFSET 28h

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	Prefetchable Memory Base Address, Upper 32-bits [63:32]	RW	Defines the upper 32-bits of a 64-bit bottom address of an address range for the Bridge to determine when to forward memory read and write transactions from one interface to the other.  Reset to 0000_0000h.

# 7.2.22 PREFETCHABLE MEMORY LIMIT ADDRESS UPPER 32-BITS REGISTER – OFFSET 2Ch

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	Prefetchable Memory Limit Address, Upper 32-bits [63:32]	RW	Defines the upper 32-bits of a 64-bit top address of an address range for the Bridge to determine when to forward memory read and write transactions from one interface to the other.  Reset to 0000_0000h.

#### 7.2.23 VO BASE ADDRESS UPPER 16-BITS REGISTER - OFFSET 30h

BIT	FUNCTION	TYPE	DESCRIPTION
15:0	I/O Base Address, Upper 16-bits [31:16]	RW	Defines the upper 16-bits of a 32-bit bottom address of an address range for the Bridge to determine when to forward I/O transactions from one interface to the other.  Reset to 0000h.

## 7.2.24 VO LIMIT ADDRESS UPPER 16-BITS REGISTER - OFFSET 30h

BIT	FUNCTION	TYPE	DESCRIPTION
31:16	I/O Limit Address, Upper 16-bits [31:16]	RW	Defines the upper 16-bits of a 32-bit top address of an address range for the Bridge to determine when to forward I/O transactions from one interface to the other.  Reset to 0000h.





#### 7.2.25 CAPABILITY POINTER REGISTER – OFFSET 34h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Capability Pointer	RO	Pointer points to the PCI power management registers.
,			Reset to 40h.

## 7.2.26 INTERRUPT LINE REGISTER - OFFSET 3Ch

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Interrupt Line	RW	Reset to 00h.

## 7.2.27 INTERRUPT PIN REGISTER - OFFSET 3Ch

BIT	FUNCTION	TYPE	DESCRIPTION
15:8	Interrupt Pin	RO	The Switch implements INTA virtual wire interrupt signals to represent hotplug events at downstream ports. The default value on the downstream ports may be changed by SMBus or auto-loading from EEPROM.  Reset to 00h.

# 7.2.28 BRIDGE CONTROL REGISTER - OFFSET 3Ch

BIT	FUNCTION	TYPE	DESCRIPTION
16	Parity Error Response	RW	0b: Ignore Poisoned TLPs on the secondary interface 1b: Enable the Poisoned TLPs reporting and detection on the secondary interface  Reset to 0b.
17	S_SERR# enable	RW	0b: Disables the forwarding of EER_COR, ERR_NONFATAL and ERR_FAT AL from secondary to primary interface 1b: Enables the forwarding of EER_COR, ERR_NONFATAL and ERR_FAT AL from secondary to primary interface  Reset to 0b.
18	ISA Enable	RW	Ob: Forwards downstream all I/O addresses in the address range defined by the I/O Base, I/O Base, and Limit registers  1b: Forwards upstream all I/O addresses in the address range defined by the I/O Base and Limit registers that are in the first 64KB of PCI I/O address space (top 768 bytes of each 1KB block)  Reset to 0b.
19	VGA Enable	RW	0b: Ignores access to the VGA memory or IO address range 1b: Forwards transactions targeted at the VGA memory or IO address range VGA memory range starts from 000A 0000h to 000B FFFFh VGA IO addresses are in the first 64KB of IO address space. AD [9:0] is in the ranges 3B0 to 3BBh and 3C0h to 3DFh.  Reset to 0b.
20	VGA 16-bit decode	RW	0b: Executes 10-bit address decoding on VGA I/O accesses 1b: Executes 16-bit address decoding on VGA I/O accesses Reset to 0b.
21	Master Abort Mode	RO	Does not apply to PCI Express. Must be hardwired to 0b.





BIT	FUNCTION	TYPE	DESCRIPTION
22	Secondary Bus Reset	RW	0b: Does not trigger a hot reset on the corresponding PCI Express Port 1b: Triggers a hot reset on the corresponding PCI Express Port At the downstream port, it asserts PORT_RST# to the attached downstream device. At the upstream port, it asserts the PORT_RST# at all the downstream ports.  Reset to 0b.
23	Fast Back-to-Back Enable	RO	Does not apply to PCI Express. Must be hardwired to 0b.
24	Primary Master Timeout	RO	Does not apply to PCI Express. Must be hardwired to 0b.
25	Secondary Master Timeout	RO	Does not apply to PCI Express. Must be hardwired to 0b.
26	Master Timeout Status	RO	Does not apply to PCI Express. Must be hardwired to 0b.
27	Discard Timer SERR# enable	RO	Does not apply to PCI Express. Must be hardwired to 0b.
31:28	Reserved	RsvdP	Not Support.

## 7.2.29 POWER MANAGEMENT CAPABILITY REGISTER - OFFSET 40h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Enhanced Capabilities ID	RO	Read as 01h to indicate that these are power management enhanced capability registers.
15:8	Next Item Pointer	RO	The pointer points to the Vital Protocol Data (VPD) capability register/the Message capability register.  Reset to 5Ch (Upstream port). Reset to 4Ch (Downstream ports).
18:16	Power Management Revision	RO	Read as 011b to indicate the device is compliant to Revision 1.2 of PCI Power Management Interface Specifications.
19	PME# Clock	RO	Does not apply to PCI Express. Must be hardwired to 0b.
20	Reserved	RsvdP	Not Support.
21	Device Specific Initialization	RO	Read as 0b to indicate Switch does not have device specific initialization requirements. The default value may be changed by SMBus or auto-loading from EEPROM.
24:22	AUX Current	RO	Reset as 111b to indicate the Switch needs 375 mA in D3 state. The default value may be changed by SMBus or auto-loading from EEPROM.
25	D1 Power State Support	RO	Read as 1b to indicate Switch supports the D1 power management state. The default value may be changed by SMBus or auto-loading from EEPROM.
26	D2 Power State Support	RO	Read as 1b to indicate Switch supports the D2 power management state. The default value may be changed by SMBus or auto-loading from EEPROM.
31:27	PME# Support	RO	Read as 11111b to indicate Switch supports the forwarding of PME# message in all power states. The default value may be changed by SMBus or autoloading from EEPROM.

## 7.2.30 POWER MANAGEMENT DATA REGISTER - OFFSET 44h

BIT	<b>FUNCTION</b>	TYPE	DESCRIPTION
1:0	Power State	RW	Indicates the current power state of the Switch. Writing a value of D0 when the previous state was D3 cause a hot reset without asserting DWNRST_L.  00b: D0 state 01b: D1 state 10b: D2 state 11b: D3 hot state Reset to 00b.
2	Reserved	RsvdP	Not Support.
3	No_Soft_Reset	RO	When set, this bit indicates that device transitioning from D3hot to D0 does





BIT	FUNCTION	TYPE	DESCRIPTION
			not perform an internal reset. When clear, an internal reset is performed when power state transits from D3hot to D0. This bit can be rewritten with EEPROM programming. The default value may be changed by SMBus or auto-loading from EEPROM.
			Reset to 1b.
7:4	Reserved	RsvdP	Not Support.
8	PME# Enable	RWS	When asserted, the Switch will generate the PME# message.  Reset to 0b.
12:9	Data Select	RW	Select data registers.  Reset to 0h.
14:13	Data Scale	RO	Reset to 00b.
15	PME status	ROS	Read as 0b as the PME# message is not implemented.  Reset to 0b.

#### 7.2.31 PPB SUPPORT EXTENSIONS - OFFSET 44h

BIT	FUNCTION	TYPE	DESCRIPTION
21:16	Reserved	RsvdP	Not Support.
22	B2_B3 Support for D3 <sub>HOT</sub>	RO	Does not apply to PCI Express. Must be hardwired to 0b.
23	Bus Power / Clock Control Enable	RO	Does not apply to PCI Express. Must be hardwired to 0b.

## 7.2.32 DATA REGISTER - OFFSET 44h

BIT	FUNCTION	TYPE	DESCRIPTION
31:24	Data Register	RO	Data Register. The default value may be changed by SMBus or auto-loading from EEPROM.
			Reset to 00h.


# 7.2.33 MSI CAPABILITY REGISTER – OFFSET 4Ch (Downstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Enhanced Capabilities ID	RO	Read as 05h to indicate that this is message signal interrupt capability register.
15:8	Next Item Pointer	RO	Pointer points to the Vendor specific capability register.  Reset to 64h.

# 7.2.34 MESSAGE CONTROL REGISTER - OFFSET 4Ch (Downstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
16	MSI Enable	RW	Ob: The function is prohibited from using MSI to request service  1b: The function is permitted to use MSI to request service and is prohibited from using its INTx# pin  Reset to 0b.
19:17	Multiple Message Capable	RO	Read as 000b.
22:20	Multiple Message Enable	RW	Reset to 000b.







BIT	FUNCTION	TYPE	DESCRIPTION
23	64-bit address capable	RO	0b: The function is not capable of generating a 64-bit message address 1b: The function is capable of generating a 64-bit message address Reset to 1b.
31:24	Reserved	RsvdP	Not Support.

## 7.2.35 MESSAGE ADDRESS REGISTER – OFFSET 50h (Downstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
1:0	Reserved	RsvdP	Not Support.
31:2	Message Address	RW	If the message enable bit is set, the contents of this register specify the DWORD aligned address for MSI memory write transaction.
			Reset to 0000_0000h.

# 7.2.36 MESSAGE UPPER ADDRESS REGISTER – OFFSET 54h (Downstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	Message Upper Address	RW	This register is only effective if the device supports a 64-bit message address is set.  Reset to 0000 0000h.

# 7.2.37 MESSAGE DATA REGISTER – OFFSET 58h (Downstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
15:0	Message Data	RW	Reset to 0000h.
31:16	Reserved	RsvdP	Not Support.

## 7.2.38 VPD CAPABILITY REGISTER – OFFSET 5Ch (Upstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Enhanced Capabilities ID	RO	Read as 03h to indicate that these are VPD enhanced capability registers.
15:8	Next Item Pointer	RO	Pointer points to the Vendor specific capability register.  Reset to 64h.

## 7.2.39 VPD REGISTER – OFFSET 5Ch (Upstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
17:16	Reserved	RsvdP	Not Support.
23:18	VPD Address	RW	Contains DWORD address that is used to generate read or write cycle to the VPD table stored in EEPROM.  Reset to 00_0000b.
30:24	Reserved	RsvdP	Not Support.





17C			

BIT	FUNCTION	TYPE	DESCRIPTION
31	VPD operation	RW	Ob: Performs VPD read command to VPD table at the location as specified in VPD address. This bit is kept '0' and then set to '1' automatically after EEPROM cycle is finished  1b: Performs VPD write command to VPD table at the location as specified in VPD address. This bit is kept '1' and then set to '0' automatically after EEPROM cycle is finished.  Reset to 0b.

## 7.2.40 VPD DATA REGISTER – OFFSET 60h (Upstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	VPD Data	RW	When read, it returns the last data read from VPD table at the location as specified in VPD Address.  When written, it places the current data into VPD table at the location as specified in VPD Address.  Reset to 0000_0000h.

## 7.2.41 VENDOR SPECIFIC CAPABILITY REGISTER - OFFSET 64h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Enhanced Capabilities ID	RO	Read as 09h to indicate that these are vendor specific capability registers.
15:8	Next Item Pointer	RO	Pointer points to the SSID/SSVID capability register.  Reset to B0h.
31:16	Length Information	RO	The length field provides the information for number of bytes in the capability structure (including the ID and Next pointer bytes).  Reset to 0034h.

# 7.2.42 XPIP CSR0 – OFFSET 68h (Test Purpose Only)

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	XPIP_CSR0	RW	Reset to 0400_1060h.

# 7.2.43 XPIP CSR1 – OFFSET 6Ch (Test Purpose Only)

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	XPIP_CSR1	RW	Reset to 0400_0800h.

## 7.2.44 REPLAY TIME-OUT COUNTER - OFFSET 70h

BIT	<b>FUNCTION</b>	TYPE	DESCRIPTION
11:0	User Replay Timer	RW	A 12-bit register contains a user-defined value. The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 000h.
12	Enable User Replay Timer	RW	When asserted, the user-defined replay time-out value is be employed. The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.





BIT	FUNCTION	TYPE	DESCRIPTION
13	Power Management Capability Disable	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
14	MSI Capability Disable	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
15	Reserved	RsvdP	Not Support.

## 7.2.45 ACKNOWLEDGE LATENCY TIMER - OFFSET 70h

BIT	FUNCTION	TYPE	DESCRIPTION
29:16	User ACK Latency Timer	RW	A 14-bit register contains a user-defined value. The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0000h.
30	Enable User ACK Latency	RW	When asserted, the user-defined ACK latency value is be employed. The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
31	VGA decode enable	RO	Enable the VGA range decode.  Reset to 1b.

# 7.2.46 SWITCH OPERATION MODE – OFFSET 74h (Upstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
0	Store-Forward	RW	When set, a store-forward mode is used. Otherwise, the chip is working under cut-through mode. The default value may be changed by SMBus or autoloading from EEPROM.  Reset to 0b.
2:1	Cut-through Threshold	RW	Cut-through Threshold. When forwarding a packet from low-speed port to high-speed mode, the chip provides the capability to adjust the forwarding threshold. The default value may be changed by SMBus or auto-loading from EEPROM.  Ob: the threshold is set at the middle of forwarding packet 01b: the threshold is set ahead 1-cycle of middle point 10b: the threshold is set ahead 2-cycle of middle point 11b: the threshold is set ahead 3-cycle of middle point Reset to 01b.
3	Port Arbitration Mode	RW	When set, the round-robin arbitration will stay in the arbitrated port even if the credit is not enough but request is pending.  When clear, the round-robin arbitration will always go to the requesting port, which the outgoing credit is enough for the packet queued in the port.  The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
4	Credit Update Mode	RW	When set, the frequency of releasing new credit to the link partner will be all types per update.  When clear, the frequency of releasing new credit to the link partner will be type oriented per update.  The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.





BIT	FUNCTION	TYPE	DESCRIPTION
5	Ordering on Different Egress Port Mode	RW	When set, there has ordering rule on packets for different egress port. The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
6	Ordering on Different Tag of Completion Mode	RW	When set, there has ordering rule between completion packet with different tag. The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
7	Reserved	RsvdP	Not Support.
13:8	Power management Control parameter	RW	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 00 0001b.
14	RX Polarity Inversion Disable	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
15	Compliance pattern Parity Control Disable	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
20:16	C_DRV_LVL_3P5_ NOM	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 1_0011b.
25:21	C_DRV_LVL_6P0_ NOM	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 1_0011b.
30:26	C_DRV_LVL_HALF _NOM	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0_0010b.
31	Reserved	RsvdP	Not Support.

# 7.2.47 SWITCH OPERATION MODE – OFFSET 74h (Downstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Reserved	RsvdP	Not Support.
13:8	Power Management Control Parameter	RW	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 00_0001b.
14	RX Polarity Inversion Disable	HwInt RO	The default value may be changed by the status of strapped pin, SMBus or auto-loading from EEPROM.  Reset to the status of RXPOLINV_DIS strapped pin.
15	Compliance Pattern Parity Control Disable	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
20:16	C_DRV_LVL_3P5_ NOM	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 1 0011b.
25:21	C_DRV_LVL_6P0_ NOM	RO	.The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 1_0011b.
30:26	C_DRV_LVL_6P0_ NOM	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0_0010b.





BIT	FUNCTION	TYPE	DESCRIPTION
31	Reserved	RsvdP	Not Support.

# 7.2.48 XPIP\_CSR2 - OFFSET 78h

BIT	FUNCTION	TYPE	DESCRIPTION
15:0	XPIP_CSR2	RO	The default value may be changed by SMBus or auto-loading from EEPROM.
			Reset to 0080h.

## 7.2.49 PHY PARAMETER 1 – OFFSET 78h

BIT	FUNCTION	TYPE	DESCRIPTION
20:16	C_EMP_POST_ GEN1_3P5_NOM	RO	The default value may be changed by SMBus or auto-loading from EEPROM.
			Reset to 1_0101b.
25:21	C_EMP_POST_ GEN2_3P5_NOM	RO	The default value may be changed by SMBus or auto-loading from EEPROM.
			Reset to 1 0101b.
30:26	C_EMP_POST_ GEN2_6P0_NOM	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 1 1101b.
			=
31	Reserved	RsvdP	Not Support.

## 7.2.50 PHY PARAMETER 2 – OFFSET 7Ch

BIT	FUNCTION	TYPE	DESCRIPTION
3:0	C_TX_PHY_ LATENCY	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0111b.
6:4	C_REC_DETECT_ USEC	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 010b.
7	Reserved	RsvdP	Not Support.
8	P_CDR_FREQLOOP _EN	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 1b.
10:9	P_CDR_ THRESHOLD	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 10b.
12:11	P_CDR_FREQLOOP _GAIN	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 11b.
15:13	Reserved	RsvdP	Not Support.
16	P_DRV_LVL_MGN_ DELATA_EN	RO	The default value may be changed by SMBus or auto-loading from EEPROM.
			Reset to 0b.





BIT	FUNCTION	TYPE	DESCRIPTION
17	P_DRV_LVL_NOM_ DELATA_EN	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b
18	P_EMP_POST_MGN _DELATA_EN	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
19	P_EMP_POST_NOM _DELATA_EN	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
21:20	P_RX_SIGDET_LVL	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 01b.
25:22	P_RX_EQ_1	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0110b.
29:26	P_RX_EQ_2	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 1000b.
30	P_TXSWING	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
31	Reserved	RsvdP	Not Support.

# 7.2.51 XPIP\_CSR3 - OFFSET 80h

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	XPIP_CSR3	RW	The default value may be changed by SMBus or auto-loading from EEPROM.
			Reset to 000F_0000h.

# 7.2.52 XPIP\_CSR4 - OFFSET 84h

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	XPIP_CSR4	RO	The default value may be changed by SMBus or auto-loading from EEPROM.
			Reset to 0000_0000h.

# 7.2.53 XPIP\_CSR5 - OFFSET 88h

BIT	FUNCTION	TYPE	DESCRIPTION
29:0	XPIP_CSR5	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 7308_3333h (Upstream port). Reset to 3308_3333h (Downstream ports).
30	DO_CHG_DATA_ RATE_CTRL	RO	The default value may be changed by SMBus, I2C or auto-loading from EEPROM.  Reset to 1b (Upstream port). Reset to 0b (Downstream ports).





BIT	FUNCTION	TYPE	DESCRIPTION
31	Gen1_Cap_Only	RO	The default value may be changed by SMBus, I2C or auto-loading from EEPROM.
			Reset to 0b.

# 7.2.54 TL\_CSR - OFFSET 8Ch

BIT	FUNCTION	TYPE	DESCRIPTION
0	TX_SOF_FORM	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
1	PM Data Select Register R/W Capability	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
2	FC_UPDATE_ MODE	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
3	4K Boundary Check Enable	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
4	FIFOERR_FIX_SEL	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 1b.
5	MW Overpass Disable	RW	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
6	Ordering Frozen Disable	RW	Disable the RO ordering rule.  The default value may be changed by SMBus or auto-loading from EEPROM  Reset to 0b.
7	GNT_FAIL2IDLE	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
9:8	DO_CHG_DATA_ CNT_SEL	RO	The trying number for doing change data rate. The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 00b.
10	Port Disable	RO	Disable this port. The default value may be changed by SMBus or autoloading from EEPROM.  Reset to 0b.
11	Reset Select	RO	Reset to 0b.  Reset to 0b.
12	ARB_VCFLG_SEL	RO	Reset to 0b.
15:13	Reserved	RsvdP	Not Support.
23:16	XPIP_CSR6	RO	XPIP_CSR6 Value. The default value may be changed by SMBus or autoloading from EEPROM.  Reset to 79h.
25:24	REV_TS_CTR	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 00b.
	1		





BIT	FUNCTION	TYPE	DESCRIPTION
29:26	MAC Control Parameter	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0h.
30	Reserved	RsvdP	Not Support.
31	P35_GEN2_MODE	RO	The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.

## 7.2.55 PHY PARAMETER 3 – OFFSET 90h

BIT	<b>FUNCTION</b>	TYPE	DESCRIPTION
6:0	PHY Parameter 3 (per lane)	RO	PHY's Lane mode.  Reset to 00h.
14:7	Reserved	RsvdP	Not Support.
31:15	PHY Parameter 3 (global)	RO	PHY's delta value setting.  Reset to 0_0001h.

## 7.2.56 PHY PARAMETER 4 - OFFSET 94h

BIT	<b>FUNCTION</b>	TYPE	DESCRIPTION
15:0	PHY TX Margin	RO	Reset to 116Bh.
23:16	Multilane RXEO	RO	Upstream p Port only. Reset to 86h.
23.10	Multilalie KAEQ	KO	Reserved for Downstream Port. Reset to 00h.
31:24	Reserved	RsvdP	Not Support.

## 7.2.57 OPERATION MODE –OFFSET 98h

BIT	FUNCTION	TYPE	DESCRIPTION
15:0	Operation mode	RO	{ 7'd0, SCAN_MODE, PKG_SEL[2:0], PHY_MODE, DEBUG_MODE, FAST_MODE, IDDQB, SROM_BYPASS}
20:16	Clock buffer control	HwInt RO	For Reference clock buffer control. The default value may be changed by the status of strapped pin, SMBus or auto-loading from EEPROM.  Bit [20]: Reset to the status of CLKBUF_PD strapped pin. Bit [19:16]: Reset to Fh.  Bit [20]: enable or disable reference clock outputs  0b: enable reference clock outputs  1b: disable reference clock outputs  Bit [19]: reserved  Bit [18:16]: enable or disable REFCLKO_P/N[2:0]  0b: disable  1b: enable
31:21	Reserved	RsvdP	Not Support.

## 7.2.58 SSID/SSVID CAPABILITY REGISTER - OFFSET B0h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	SSID/SSVID Capabilities ID	RO	Read as 0Dh to indicate that these are SSID/SSVID capability registers.





BIT	FUNCTION	TYPE	DESCRIPTION
15:8	Next Item Pointer	RO	Pointer points to the PCI Express capability register.
13.0	TVCAC TCHITT OHICE	RO	Reset to C0h.

## 7.2.59 SUBSYSTEM VENDOR ID REGISTER - OFFSET B4h

BIT	FUNCTION	TYPE	DESCRIPTION
15:0	SSVID	RO	It indicates the sub-system vendor id. The default value may be changed by SMBus or auto-loading from EEPROM.
			SMBus or auto-loading from EEPROM.  Reset to 0000h.

## 7.2.60 SUBSYSTEM ID REGISTER - OFFSET B4h

BIT	FUNCTION	TYPE	DESCRIPTION
31:16	SSID	RO	It indicates the sub-system device id. The default value may be changed by
			SMBus or auto-loading from EEPROM.
			Reset to 0000h.

# 7.2.61 GPIO CONTROL REGISTER – OFFSET B8h (Upstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
0	GPIO [0] Input	RO	State of GPIO [0] pin
1	GPIO [0] Output Enable	RW	0b: GPIO [0] is an input pin 1b: GPIO [0] is an output pin Reset to 0b.
2	GPIO [0] Output Register	RW	Value of this bit will be output to GPIO [0] pin if GPIO [0] is configured as an output pin.  Reset to 0b.
3	Reserved	RsvdP	Not Support.
4	GPIO[1] Input	RO	State of GPIO [1] pin.
5	GPIO [1] Output Enable	RW	0b: GPIO [1] is an input pin 1b: GPIO [1] is an output pin  Reset to 0b.
6	GPIO [1] Output Register	RW	Value of this bit will be output to GPIO [1] pin if GPIO [1] is configured as an output pin.  Reset to 0b.
7	Reserved	RsvdP	Not Support.
8	GPIO [2] Input	RO	State of GPIO [2] pin
9	GPIO [2] Output Enable	RW	0b: GPIO [2] is an input pin 1b: GPIO [2] is an output pin Reset to 0b.
10	GPIO [2] Output Register	RW	Value of this bit will be output to GPIO [2] pin if GPIO [2] is configured as an output pin.  Reset to 0b.
11	Reserved	RsvdP	Not Support.
12	GPIO [3] Input	RO	State of GPIO [3] pin.
13	GPIO [3] Output Enable	RW	0b: GPIO [3] is an input pin 1b: GPIO [3] is an output pin
		l	Reset to 0b.





BIT	FUNCTION	TYPE	DESCRIPTION
D11	Terre norr	1112	Value of this bit will be output to GPIO [3] pin if GPIO [3] is configured as
	GPIO[3] Output		an output pin.
14	Register	RW	
			Reset to 0b.
15	Reserved	RsvdP	Not Support.
16	GPIO [4] Input	RO	State of GPIO [4] pin.
			0b: GPIO [4] is an input pin
1.7	GPIO [4] Output	DIV	1b: GPIO [4] is an output pin
17	Enable	RW	
			Reset to 0b.
			Value of this bit will be output to GPIO [4] pin if GPIO [4] is configured as
1.0	GPIO [4] Output	RW	an output pin.
18	Register	KW	
			Reset to 0b.
19	Reserved	RsvdP	Not Support.
20	GPIO [5] Input	RO	State of GPIO [5] pin.
			0b: GPIO [5] is an input pin
21	GPIO [5] Output	RW	1b: GPIO [5] is an output pin
21	Enable	ICVV	
			Reset to 0b.
			Value of this bit will be output to GPIO [5] pin if GPIO [5] is configured as
22	GPIO [5] Output	RW	an output pin.
22	Register	1644	
			Reset to 0b.
23	Reserved	RsvdP	Not Support.
24	GPIO [6] Input	RO	State of GPIO [6] pin.
	CD TO F CLO		0b: GPIO [6] is an input pin
25	GPIO [6] Output	RW	1b: GPIO [6] is an output pin
20	Enable	10,,	D 01
			Reset to 0b.
	CDIO [6] O 4 = 4		Value of this bit will be output to GPIO [6] pin if GPIO [6] is configured as
26	GPIO [6] Output	RW	an output pin.
	Register		Donat to Ob
27	Reserved	RsvdP	Reset to 0b.
27	GPIO [7] Input	RSVaP	Not Support.  State of GPIO [7] pin.
28	Gr10[/]Input	KU	State of GPIO [7] pin.  Ob: GPIO [7] is an input pin
	GPIO [7] Output		1b: GPIO [7] is an output pin
29	Enable	RW	10. Or 10 [7] is an output pin
	Ellable		Reset to 0b.
-			Value of this bit will be output to GPIO [7] pin if GPIO [7] is configured as
	GPIO [7] Output		an output pin.
30	Register	RW	an output pin.
	register		Reset to 0b.
31	Reserved	RsvdP	Not Support.
<i>J</i> 1	10001 7 00	165741	The support.

# 7.2.62 EEPROM CONTROL REGISTER – OFFSET BCh (Upstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
0	EEPROM Start	RW	Starts the EEPROM read or write cycle.  Reset to 0b.
1	EEPROM Command	RW	Sends the command to the EEPROM.  0b: EEPROM read 1b: EEPROM write  Reset to 0b.
2	EEPROM Error Status	RO	1b: EEPROM acknowledge was not received during the EEPROM cycle.  Reset to 0b.





BIT	FUNCTION	TYPE	DESCRIPTION
3	EEPROM Autoload Success	RO	Ob: EEPROM autoload was unsuccessful or is disabled  1b: EEPROM autolad occurred successfully after RESET. Configuration registers were loaded with values in the EEPROM  It will be cleared when read at this bit.
4	EEPROM Autoload Status	RO	0b: EEPROM autoload was unsuccessful or is disabled 1b: EEPROM autoload occurred successfully after PREST. Configuration registers were loaded with values stored in the EEPROM Reset to 0b.
5	EEPROM Autoload Disable	RW	0b: EEPROM autoload enabled 1b: EEPROM autoload disabled Reset to 1b.
7:6	EEPROM Clock Rate	RW	Determines the frequency of the EEPROM clock, which is derived from the primary clock.  00b: Reserved 01b: PEXCLK / 1024 (PEXCLK is 125MHz) 10b: Reserved 11b: Test Mode  Reset to 01b.

## 7.2.63 EEPROM ADDRESS REGISTER – OFFSET BCh (Upstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
8	Reserved	RsvdP	Not Support.
15:9	EEPROM Address	RW	Contains the EEPROM address.  Reset to 0000h.

# 7.2.64 EEPROM DATA REGISTER – OFFSET BCh (Upstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
31:16	EEPROM Data	RW	Contains the data to be written to the EEPROM. After completion of a read cycle, this register will contain the data from the EEPROM.
			Reset to 0000h.

## 7.2.65 PCI EXPRESS CAPABILITY REGISTER - OFFSET C0h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Enhanced Capabilities ID	RO	Read as 10h to indicate that these are PCI express enhanced capability registers.
15:8	Next Item Pointer	RO	Read as 00h. No other ECP registers.
19:16	Capability Version	RO	Read as 0010b to indicate the device is compliant to Revision .2.0a of PCI Express Base Specifications.
23:20	Device/Port Type	RO	Indicates the type of PCI Express logical device.  Reset to 0101b (Upstream port).  Reset to 0110b (Downstream ports).
24	Slot Implemented	HwInt RO	When set, indicates that the PCIe Link associated with this Port is connected to a slot. This field is valid for downstream port of the Switch. The default value may be changed by the status of strapped pin, SMBus or auto-loading from EEPROM.  Reset to the status of SLOT_IMP strapped pin.





BIT	FUNCTION	TYPE	DESCRIPTION
29:25	Interrupt Message Number	RO	Read as 0b. No MSI messages are generated in the transparent mode.
31:30	Reserved	RsvdP	Not Support.

## 7.2.66 DEVICE CAPABILITIES REGISTER - OFFSET C4h

BIT	FUNCTION	TYPE	DESCRIPTION
2:0	Max_Payload_Size Supported	HwInt RO	Indicates the maximum payload size that the device can support for TLPs. The default value may be changed by the status of strapped pin, SMBus or auto-loading from EEPROM.  Reset to 001b when PL_512B strapped pin is set to 0. Reset to 010b when PL_512B strapped pin is set to 1.
4:3	Phantom Functions Supported	RO	Indicates the support for use of unclaimed function numbers as Phantom functions. Read as 00b, since the Switch does not act as a requester.  Reset to 00b.
5	Extended Tag Field Supported	RO	Indicates the maximum supported size of Tag field as a Requester. Read as 0, since the Switch does not act as a requester.  Reset to 0b.
8:6	Endpoint L0s Acceptable Latency	RO	Acceptable total latency that an Endpoint can withstand due to the transition from L0s state to the L0 state. For Switch, the ASPM software would not check this value.  Reset to 000b.
11:9	Endpoint L1 Acceptable Latency	RO	Acceptable total latency that an Endpoint can withstand due to the transition from L1 state to the L0 state. For Switch, the ASPM software would not check this value.  Reset to 000b.
14:12	Reserved	RsvdP	Not Support.
15	Role_Based Error Reporting	RO	When set, indicates that the device implements the functionality originally defined in the Error Reporting ECN. The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 1b.
17:16	Reserved	RsvdP	Not Support.
25:18	Captured Slot Power Limit Value	RO	It applies to Upstream Port only. In combination with the Slot Power Limit Scale value, specifies the upper limit on power supplied by slot.  This value is set by the Set_Slot_Power_Limit message or hardwired to 00h.  Reset to 00h.
27:26	Captured Slot Power Limit Scale	RO RsvdP	It applies to Upstream Port only. Specifies the scale used for the Slot Power Limit Value.  This value is set by the Set_Slot_Power_Limit message or hardwired to 00b.  Reset to 00b.  Not Support.
31.20	Nesel veu	KSVUP	Not support.

## 7.2.67 DEVICE CONTROL REGISTER - OFFSET C8h

BIT	FUNCTION	TYPE	DESCRIPTION
			0b: Disable Correctable Error Reporting
0	Correctable Error Reporting Enable	RW	1b: Enable Correctable Error Reporting
	1 0		Reset to 0b.





BIT	FUNCTION	TYPE	DESCRIPTION
1	Non-Fatal Error Reporting Enable	RW	0b: Disable Non-Fatal Error Reporting 1b: Enable Non-Fatal Error Reporting
2	Fatal Error Reporting Enable	RW	Reset to 0b.  0b: Disable Fatal Error Reporting 1b: Enable Fatal Error Reporting  Reset to 0b.
3	Unsupported Request Reporting Enable	RW	0b: Disable Unsupported Request Reporting 1b: Enable Unsupported Request Reporting Reset to 0b.
4	Enable Relaxed Ordering	RO	When set, it permits the device to set the Relaxed Ordering bit in the attribute field of transaction. Since the Switch can not either act as a requester or alter the content of packet it forwards, this bit always returns '0' when read.  Reset to 0b.
7:5	Max_Payload_Size	RW	This field sets maximum TLP payload size for the device. Permissible values that can be programmed are indicated by the Max_Payload_Size Supported in the Device Capabilities register. Any value exceeding the Max_Payload_Size Supported written to this register results into clamping to the Max_Payload_Size Supported value.  Reset to 000b.
8	Extended Tag Field Enable	RW	Does not apply to PCI Express Switch. Returns '0' when read.  Reset to 0b.
9	Phantom Function Enable	RW	Does not apply to PCI Express Switch. Returns '0' when read.  Reset to 0b.
10	Auxiliary (AUX) Power PM Enable	RWS	When set, indicates that a device is enabled to draw AUX power independent of PME AUX power.  Reset to 0b.
11	Enable No Snoop	RO	When set, it permits to set the No Snoop bit in the attribute field of transaction. Since the Switch can not either act as a requester or alter the content of packet it forwards, this bit always returns '0' when read.  Reset to 0b.
14:12	Max_Read_ Request_Size	RO	This field sets the maximum Read Request size for the device as a Requester. Since the Switch does not generate read request by itself, these bits are hardwired to 000b.  Reset to 000b.
15	Reserved	RsvdP	Not Support.

# 7.2.68 DEVICE STATUS REGISTER - OFFSET C8h

BIT	FUNCTION	TYPE	DESCRIPTION
16	Correctable Error Detected	RW1C	Asserted when correctable error is detected. Errors are logged in this register regardless of whether error reporting is enabled or not in the Device Control register.  Reset to 0b.
17	Non-Fatal Error Detected	RW1C	Asserted when non-fatal error is detected. Errors are logged in this register regardless of whether error reporting is enabled or not in the Device Control register.  Reset to 0b.
18	Fatal Error Detected	RW1C	Asserted when fatal error is detected. Errors are logged in this register regardless of whether error reporting is enabled or not in the Device Control register.  Reset to 0b.





BIT	FUNCTION	TYPE	DESCRIPTION
19	Unsupported Request Detected	RW1C	Asserted when unsupported request is detected. Errors are logged in this register regardless of whether error reporting is enabled or not in the Device Control register.
			Reset to 0b.
20	AUX Power Detected	RO	Asserted when the AUX power is detected by the Switch
	Beteeted		Reset to 1b.
21	Transactions Pending	RO	Each port of Switch does not issue Non-posted Requests on its own behalf, so this bit is hardwired to 0b.
			Reset to 0b.
31:22	Reserved	RsvdP	Not Support.

## 7.2.69 LINK CAPABILITIES REGISTER - OFFSET CCh

BIT	FUNCTION	TYPE	DESCRIPTION
3:0	Maximum Link Speed	RO	Indicates the maximum speed of the Express link. The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0010b (5 Gb/s).
9:4	Maximum Link Width	RO	Indicates the maximum width of the given PCIe Link.  Reset to 00_0001b (x1).
11:10	Active State Power Management (ASPM) Support	RO	Indicates the level of ASPM supported on the given PCIe Link. Each port of Switch supports L0s and L1 entry. The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 00b.
14:12	L0s Exit Latency	RO	Indicates the L0s exit latency for the given PCIe Link. The length of time this port requires to complete transition from L0s to L0 is in the range of 256ns to less than 512ns. The default value may be changed by SMBus or auto-loading from EEPROM.
17:15	L1 Exit Latency	RO	Reset to 011b.  Indicates the L1 exit latency for the given PCIe Link.  The length of time this port requires to complete transition from L1 to L0 is in the range of 16us to less than 32us. The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 000b.
19:18	Reserved	RsvdP	Not Support.
20	Data Link Layer Active Reporting Capable	RO	For a Downstream Port, this bit must be set to 1 b if the component supports the optional capability of reporting the DL_Active state of the Data Link Control and Management State Machine. For a hot-plug capable Downstream Port, this bit must be set to 1 b.  For Upstream Port, this bit must be hardwired to 0 b.  Reset to 0 b.
21	Tinlahaan atifaaan	DO.	Reset to 0b (Upstream port).
21	Link bw notify cap	RO	Reset to 1b (Downstream ports).
23:21	Reserved	RsvdP	Not Support.
31:24	Port Number	RO	Indicates the PCIe Port Number for the given PCIe Link. The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 00h for Port 0. Reset to 01h for Port 1. Reset to 02h for Port 2.





## 7.2.70 LINK CONTROL REGISTER - OFFSET D0h

BIT	FUNCTION	TYPE	DESCRIPTION
1:0	Active State Power Management (ASPM) Control	RW	00b: ASPM is Disabled 01b: L0s Entry Enabled 10b: L1 Entry Enabled 11b: L0s and L1 Entry Enabled  Note that the receiver must be capable of entering L0s even when the field is disabled.  Reset to 00b.
2	Reserved	RsvdP	Not Support.
3	Read Completion Boundary (RCB)	RO	Does not apply to PCI Express Switch. Returns '0' when read.  Reset to 0b.
4	Link Disable	RW	At upstream port, it is not allowed to disable the link, so this bit is hardwired to '0'. For downstream ports, it disables the link when this bit is set.  Reset to 0b.
5	Retrain Link	RW	At upstream port, it is not allowed to retrain the link, so this bit is hardwired to 0b. For downstream ports, it initiates Link Retraining when this bit is set.  This bit always returns 0b when read.
6	Common Clock Configuration	RW	Ob: The components at both ends of a link are operating with asynchronous reference clock  1b: The components at both ends of a link are operating with a distributed common reference clock  Reset to 0b.
7	Extended Synch	RW	When set, it transmits 4096 FTS ordered sets in the L0s state for entering L0 state and transmits 1024 T S1 ordered sets in the L1 state for entering L0 state.  Reset to 0b.
8	Reserved	RsvdP	Not Support.
9	HW Autonomous width Disable	RW	Reset to 0b.
10	Link Bandwidth Management Interrupt Enable	RO/RW	For upstream Port is RO. For downstream Port is RW.  Reset to 0b.
11	Link Autonomous Bandwidth Interrupt Enable	RO/RW	For upstream Port is RO. For downstream Port is RW. Reset to 0b.
15:12	Reserved	RsvdP	Not Support.

## 7.2.71 LINK STATUS REGISTER - OFFSET D0h

BIT	FUNCTION	TYPE	DESCRIPTION
19:16	Link Speed	RO	Indicate the negotiated speed of the Express link.  0001b: 2.5 Gb/s.  0010b: 5 Gb/s.  Reset to 0010b.
25:20	Negotiated Link Width	RO	Indicates the negotiated width of the given PCIe link.  Reset to 00_0001b(x1).
26	Training Error	RO	When set, indicates a Link training error occurred.  This bit is cleared by hardware upon successful training of the link to the L0 link state.  Reset to 0b.





BIT	FUNCTION	TYPE	DESCRIPTION
27	Link Training	RO	When set, indicates the link training is in progress. Hardware clears this bit once link training is complete.  Reset to 0b.
28	Slot Clock Configuration	HwInt RO	Ob: the Switch uses an independent clock irrespective of the presence of a reference on the connector  1b: the Switch uses the same reference clock that the platform provides on the connector  The default value may be changed by the status of strapped pin, SMBus or auto-loading from EEPROM.  Reset to the status of SLOTCLK strapped pin.
29	Data Link Layer Link Active	RO	Indicates the status of the Data Link Control and Management State Machine. It returns a 1b to indicate the DL_Active state, 0b otherwise.  Reset to 0b.
31:30	Reserved	RsvdP	Not Support.

# 7.2.72 SLOT CAPABILITIES REGISTER – OFFSET D4h (Downstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
0	Attention Button Present	RO	When set, it indicates that an Attention Button is implemented on the chassis for this slot. The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
1	Power Controller Present	RO	When set, it indicates that a Power Controller is implemented for this slot. The default value may be changed by SMBus or auto-loading from EEPROM. Reset to 0b.
2	Reserved	RsvdP	Not Support.
3	Attention Indicator Present	RO	When set, it indicates that an Attention Indicator is implemented on the chassis for this slot. The default value may be changed by SMBus or autoloading from EEPROM.  Reset to 0b.
4	Power Indicator Present	RO	When set, it indicates that a Power Indicator is implemented on the chassis for this slot. The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
5	Hot-Plug Surprise	RO	When set, it indicates that a device present in this slot might be removed from the system without any prior notification. The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
6	Hot-Plug Capable	RO	When set, it indicates that this slot is capable of supporting Hot-Plug operation. The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0b.
14:7	Slot Power Limit Value	RW	It applies to Downstream Port only. In combination with the Slot Power Limit Scale value, specifies the upper limit on power supplied by slot. Writes to this register also cause the Port to send the Set_Slot_Power_Limit message. The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 00h.
16:15	Slot Power Limit Scale	RW	It applies to Downstream Port only. Specifies the scale used for the Slot Power Limit Value. Writes to this register also cause the Port to send the Set_Slot_Power_Limit message. The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 00b.





BIT	FUNCTION	TYPE	DESCRIPTION
18:17	Reserved	RsvdP	Not Support.
31:19	Physical Slot Number	RO	It indicates the physical slot number attached to this Port. The default value may be changed by SMBus or auto-loading from EEPROM.  Reset to 0000h.

# 7.2.73 SLOT CONTROL REGISTER – OFFSET D8h (Downstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
0	Attention Button Pressed Enable	RW	When set, it enables the generation of Hot-Plug interrupt or wakeup event on an attention button pressed event.  Reset to 0b.
1	Power Fault Detected Enable	RW	When set, it enables the generation of Hot-Plug interrupt or wakeup event on a power fault event.
2	Reserved	RsvdP	Reset to 0b. Not Support.
3	Presence Detect Changed Enable	RW	When set, it enables the generation of Hot-Plug interrupt or wakeup event on a presence detect changed event.  Reset to 0b.
4	Command Completed Interrupt Enable	RW	When set, it enables the generation of Hot-Plug interrupt when the Hot-Plug Controller completes a command.  Reset to 0b.
5	Hot-Plug Interrupt Enable	RW	When set, it enables generation of Hot-Plug interrupt on enabled Hot-Plug events.  Reset to 0b.
7:6	Attention Indicator Control	RW	Controls the display of Attention Indicator.  00b: Reserved 01b: On 10b: Blink 11b: Off  Writes to this register also cause the Port to send the ATTENTION_INDICATOR_* Messages.  Reset to 11b.
9:8	Power Indicator Control	RW	Controls the display of Power Indicator.  00b: Reserved 01b: On 10b: Blink 11b: Off  Writes to this register also cause the Port to send the POWER_INDICATOR_* Messages.  Reset to 11b.
10	Power Controller Control	RW	0b: reset the power state of the slot (Power On) 1b: set the power state of the slot (Power Off) Reset to 0b.
11	Reserved	RsvdP	Not Support.
12	Data Link Layer State Changed Enable	RW	If the Data Link Layer Link Active capability is implemented, when set to 1b, this field enables software notification when Data Link Layer Link Active field is changed.  Reset to 0b.
15:13	Reserved	RsvdP	Not Support.
10.10	130501 V Cu	100 V UI	The support.





# 7.2.74 SLOT STATUS REGISTER OFFSET D8h (Downstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
16	Attention Button Pressed	RW1C	When set, it indicates the Attention Button is pressed.  Reset to 0b.
17	Power Fault Detected	RW1C	When set, it indicates a Power Fault is detected.  Reset to 0b.
18	MRL Sensor Changed	RO	When set, it indicates a MRL Sensor Changed is detected.  Reset to 0b.
19	Presence Detect Changed	RW1C	When set, it indicates a Presence Detect Changed is detected.  Reset to 0b.
20	Command Completed	RW1C	When set, it indicates the Hot-Plug Controller completes an issued command.  Reset to 0b.
21	MRL Sensor State	RO	Reflects the status of MRL Sensor.  0b: MRL Closed 1b: MRL Opened Reset to 0b.
22	Presence Detect State	HwInt RO	Indicates the presence of a card in the slot.  Ob: Slot Empty 1b: Card Present in slot  This register is implemented on all Downstream Ports that implement slots. For Downstream Ports not connected to slots (where the Slot Implemented bit of the PCI Express Capabilities register is 0b), this bit returns 1b.  Reset to 1b when PRSNT strapped pin is set to 0. Reset to 0b when PRSNT strapped pin is set to 1.
23	Reserved	RsvdP	Not Support.
24	Data Link Layer State Changed	RW1C	This bit is set when the value reported in the Data Link Layer Link Active field of the Link Status register is changed.  Reset to 0b.
31:25	Reserved	RsvdP	Not Support.

#### 7.2.75 DEVICE CAPABILITIES REGISTER 2 – OFFSET E4h

BIT	FUNCTION	TYPE	DESCRIPTION
10:0	Device Capabilities 2	RO	Reset to 000h.
11	LTR Mechanism Supported	RO	A value of 1b indicates support for the optional Latency Tolerance Reporting (LTR) mechanism.  Reset to 1b.
17:12	Device Capabilities 2	RO	Reset to 00h.
19:18	OBFF Supported	RO	This field indicates if OBFF is supported.  Reset to 01b.
31:20	Device Capabilities 2	RO	Reset to 000h.

## 7.2.76 DEVICE CONTROL REGISTER 2 – OFFSET E8h

ſ	BIT	FUNCTION	TYPE	DESCRIPTION
ſ	9:0	Device Control2	RO	Reset to 000h.





BIT	FUNCTION	TYPE	DESCRIPTION
10	LTR Mechanism Enable	RW	Enable LTR Mechanism.  Reset to 0b.
12:11	Device Control2	RO	Reset to 00b.
14:13	OBFF enable	RW	Enable OBFF Mechanism and select the signaling method.  Reset to 00b.
15	Device Control2	RO	Reset to 0b.

## 7.2.77 DEVIDE STATUS REGISTER 2 – OFFSET E8h

BIT	FUNCTION	TYPE	DESCRIPTION
31:16	Device status 2	RO	Reset to 0000h.

#### 7.2.78 LINK CAPABILITIES REGISTER 2 – OFFSET ECh

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	Link Capabilities 2	RO	Reset to 0000_0000h.

## 7.2.79 LINK CONTROL REGISTER 2 - OFFSET F0h

BIT	FUNCTION	TYPE	DESCRIPTION
3:0	Target Link Speed	RWS	Reset to 0010b.
4	Enter Compliance	RWS	Reset to 0b.
5	HW_AutoSpeed_Dis	RW	Reset to 0b.
6	Select Deemp	RO	Reset to 0b (Upstream port).
0	Sciect_Decimp	RO	Reset to 1b (Downstream ports).
9:7	Tran_Margin	RWS	Reset to 000b.
10	Enter Modify	RWS	Reset to 0b.
10	Compliance	KW S	
11	Compliance SOS	RWS	Reset to 0b.
12	Compliance_Deemp	RWS	Reset to 0b.
15:13	Reserved	RsvdP	Not Support.

#### 7.2.80 LINK STATUS REGISTER 2 - OFFSET F0h

BIT	FUNCTION	TYPE	DESCRIPTION
16	Current De-	RO	Reset to 0b (Upstream port).
	emphasis Level		Reset to 1b (Downstream ports).
31:17	Link Status 2	RO	Reset to 0000h.

## 7.2.81 SLOT CAPABILITIES REGISTER 2 – OFFSET F4h

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	Slot Capabilities 2	RO	Reset to 0000_0000h.

## 7.2.82 SLOT CONTORL REGISTER 2 - OFFSET F8h

BIT	FUNCTION	TYPE	DESCRIPTION
15:0	Slot Control2	RO	Reset to 0000h.





## 7.2.83 SLOT STATUS REGISTER 2 - OFFSET F8h

BIT	FUNCTION	TYPE	DESCRIPTION
31:16	Slot Status 2	RO	Reset to 0000h.

# 7.2.84 PCI EXPRESS ADVANCED ERROR REPORTING CAPABILITY REGISTER – OFFSET 100h

BIT	FUNCTION	TYPE	DESCRIPTION
15:0	Extended Capabilities ID	RO	Read as 0001h to indicate that these are PCI express extended capability registers for advance error reporting.
19:16	Capability Version	RO	Read as 1h. Indicates PCI-SIG defined PCI Express capability structure version number.
31:20	Next Capability Offset	RO	Pointer points to the PCI Express Extended VC capability register.  Reset to 140h.

## 7.2.85 UNCORRECTABLE ERROR STATUS REGISTER - OFFSET 104h

BIT	FUNCTION	TYPE	DESCRIPTION
0	Training Error Status	RW1CS	When set, indicates that the Training Error event has occurred.  Reset to 0b.
3:1	Reserved	RsvdP	Not Support.
4	Data Link Protocol Error Status	RW1CS	When set, indicates that the Data Link Protocol Error event has occurred.  Reset to 0b.
11:5	Reserved	RsvdP	Not Support.
12	Poisoned TLP Status	RW1CS	When set, indicates that a Poisoned TLP has been received or generated.  Reset to 0b.
13	Flow Control Protocol Error Status	RW1CS	When set, indicates that the Flow Control Protocol Error event has occurred.  Reset to 0b.
14	Completion Timeout Status	RW1CS	When set, indicates that the Completion Timeout event has occurred.  Reset to 0b.
15	Completer Abort Status	RW1CS	When set, indicates that the Completer Abort event has occurred.  Reset to 0b.
16	Unexpected Completion Status	RW1CS	When set, indicates that the Unexpected Completion event has occurred.  Reset to 0b.
17	Receiver Overflow Status	RW1CS	When set, indicates that the Receiver Overflow event has occurred.  Reset to 0b.
18	Malformed TLP Status	RW1CS	When set, indicates that a Malformed TLP has been received.  Reset to 0b.
19	ECRC Error Status	RW1CS	When set, indicates that an ECRC Error has been detected.  Reset to 0b.
20	Unsupported Request Error Status	RW1CS	When set, indicates that an Unsupported Request event has occurred.  Reset to 0b.
21	ACS Violation Status	RW1CS	When set, indicates that an ACS Violation event has occurred  Reset to 0b.





BIT	FUNCTION	TYPE	DESCRIPTION
31:21	Reserved	RsvdP	Not Support.

## 7.2.86 UNCORRECTABLE ERROR MASK REGISTER - OFFSET 108h

BIT	FUNCTION	TYPE	DESCRIPTION
0	Training Error Mask	RWS	When set, the Training Error event is not logged in the Header Log register and not issued as an Error Message to RC either.
			Reset to 0b.
3:1	Reserved	RsvdP	Not Support.
4	Data Link Protocol Error Mask	RWS	When set, the Data Link Protocol Error event is not logged in the Header Log register and not issued as an Error Message to RC either.
11.5	D 1	D	Reset to 0b.
11:5	Reserved	RsvdP	Not Support.
12	Poisoned TLP Mask	RWS	When set, an event of Poisoned TLP has been received or generated is not logged in the Header Log register and not issued as an Error Message to RC either.
			Reset to 0b.
13	Flow Control Protocol Error Mask	RWS	When set, the Flow Control Protocol Error event is not logged in the Header Log register and not issued as an Error Message to RC either.
			Reset to 0b.
14	Completion Timeout Mask	RWS	When set, the Completion Timeout event is not logged in the Header Log register and not issued as an Error Message to RC either.
	Witton		Reset to 0b.
15	Completer Abort Mask	RWS	When set, the Completer Abort event is not logged in the Header Log register and not issued as an Error Message to RC either.
	Witton		Reset to 0b.
16	Unexpected Completion Mask	RWS	When set, the Unexpected Completion event is not logged in the Header Log register and not issued as an Error Message to RC either.
	1		Reset to 0b.
17	Receiver Overflow Mask	RWS	When set, the Receiver Overflow event is not logged in the Header Log register and not issued as an Error Message to RC either.
			Reset to 0b.
18	Malformed TLP Mask	RWS	When set, an event of Malformed TLP has been received is not logged in the Header Log register and not issued as an Error Message to RC either.
			Reset to 0b.
19	ECRC Error Mask	RWS	When set, an event of ECRC Error has been detected is not logged in the Header Log register and not issued as an Error Message to RC either.
			Reset to 0b.
20	Unsupported Request Error Mask	RWS	When set, the Unsupported Request event is not logged in the Header Log register and not issued as an Error Message to RC either.
			Reset to 0b.
21	ACS violation mask	RWS	Reset to 0b
31:22	Reserved	RsvdP	Not Support.





# 7.2.87 UNCORRECTABLE ERROR SEVERITY REGISTER - OFFSET 10Ch

BIT	FUNCTION	TYPE	DESCRIPTION
0	Training Error Severity	RWS	0b: Non-Fatal 1b: Fatal Reset to 1b.
3:1	Reserved	RsvdP	Not Support.
4	Data Link Protocol Error Severity	RWS	0b: Non-Fatal 1b: Fatal
11:5	Reserved	RsvdP	Reset to 1b.  Not Support.
12	Poisoned TLP Severity	RWS	0b: Non-Fatal 1b: Fatal Reset to 0b.
13	Flow Control Protocol Error Severity	RWS	0b: Non-Fatal 1b: Fatal Reset to 1b.
14	Completion Timeout Error Severity	RWS	0b: Non-Fatal 1b: Fatal Reset to 0b.
15	Completer Abort Severity	RWS	0b: Non-Fatal 1b: Fatal Reset to 0b.
16	Unexpected Completion Severity	RWS	0b: Non-Fatal 1b: Fatal Reset to 0b.
17	Receiver Overflow Severity	RWS	0b: Non-Fatal 1b: Fatal Reset to 1b.
18	Malformed TLP Severity	RWS	0b: Non-Fatal 1b: Fatal Reset to 1b.
19	ECRC Error Severity	RWS	0b: Non-Fatal 1b: Fatal Reset to 0b.
20	Unsupported Request Error Severity	RWS	0b: Non-Fatal 1b: Fatal Reset to 0b.
21	ACS violation severity	RWS	0b: Non-Fatal 1b: Fatal Reset to 0b.
31:21	Reserved	RsvdP	Not Support.

## 7.2.88 CORRECTABLE ERROR STATUS REGISTER - OFFSET 110 h

BIT	FUNCTION	TYPE	DESCRIPTION
			When set, the Receiver Error event is detected.
0	Receiver Error Status	RW1CS	
			Reset to 0b.
5:1	Reserved	RsvdP	Not Support.





BIT	FUNCTION	TYPE	DESCRIPTION
6	Bad TLP Status	RW1CS	When set, the event of Bad T LP has been received is detected.  Reset to 0b.
7	Bad DLLP Status	RW1CS	When set, the event of Bad DLLP has been received is detected.  Reset to 0b.
8	REPLAY_NUM Rollover status	RW1CS	When set, the REPLAY_NUM Rollover event is detected.  Reset to 0b.
11:9	Reserved	RsvdP	Not Support.
12	Replay Timer Timeout status	RW1CS	When set, the Replay Timer Timeout event is detected.  Reset to 0b.
13	Advisory Non-Fatal Error status	RW1CS	When set, the Advisory Non-Fatal Error event is detected.  Reset to 0b.
31:14	Reserved	RsvdP	Not Support.

## 7.2.89 CORRECTABLE ERROR MASK REGISTER - OFFSET 114 h

BIT	<b>FUNCTION</b>	TYPE	DESCRIPTION
0	Receiver Error Mask	RWS	When set, the Receiver Error event is not logged in the Header Log register and not issued as an Error Message to RC either.
			Reset to 0b.
5:1	Reserved	RsvdP	Not Support.
6	Bad TLP Mask	RWS	When set, the event of Bad TLP has been received is not logged in the Header Log register and not issued as an Error Message to RC either.  Reset to 0b
7	Bad DLLP Mask	RWS	When set, the event of Bad DLLP has been received is not logged in the Header Log register and not issued as an Error Message to RC either.  Reset to 0b.
8	REPLAY_NUM Rollover Mask	RWS	When set, the REPLAY_NUM Rollover event is not logged in the Header Log register and not issued as an Error Message to RC either.  Reset to 0b.
11:9	Reserved	RsvdP	Not Support.
12	Replay Timer Timeout Mask	RWS	When set, the Replay Timer Timeout event is not logged in the Header Log register and not issued as an Error Message to RC either.  Reset to 0b
13	Advisory Non-Fatal Error Mask	RWS	When set, the Advisory Non-Fatal Error event is not logged in the Header Long register and not issued as an Error Message to RC either.  Reset to 1b.
31:14	Reserved	RsvdP	Not Support.

# 7.2.90 ADVANCE ERROR CAPABILITIES AND CONTROL REGISTER – OFFSET 118h

BIT	FUNCTION	TYPE	DESCRIPTION
4:0	First Error Pointer	ROS	It indicates the bit position of the first error reported in the Uncorrectable Error Status register.  Reset to 0_0000b.
5	ECRC Generation Capable	RO	When set, it indicates the Switch has the capability to generate ECRC.  Reset to 1b.





BIT	FUNCTION	TYPE	DESCRIPTION
6	ECRC Generation Enable	RWS	When set, it enables the generation of ECRC when needed.  Reset to 0b.
7	ECRC Check Capable	RO	When set, it indicates the Switch has the capability to check ECRC.  Reset to 1b.
8	ECRC Check Enable	RWS	When set, the function of checking ECRC is enabled.  Reset to 0b.
31:9	Reserved	RsvdP	Not Support.

## 7.2.91 HEADER LOG REGISTER - OFFSET From 11Ch to 128h

BIT	FUNCTION	TYPE	DESCRIPTION
31:0	1 <sup>st</sup> DWORD	ROS	Hold the 1st DWORD of TLP Header. The Head byte is in big endian.
63:32	2 <sup>nd</sup> DWORD	ROS	Hold the 2nd DWORD of TLP Header. The Head byte is in big endian.
95:64	3 <sup>rd</sup> DWORD	ROS	Hold the 3rd DWORD of TLP Header. The Head byte is in big endian.
127:96	4 <sup>th</sup> DWORD	ROS	Hold the 4th DWORD of TLP Header. The Head byte is in big endian.

# 7.2.92 PCI EXPRESS VIRTUAL CHANNEL CAPABILITY REGISTER – OFFSET 140h

BIT	FUNCTION	TYPE	DESCRIPTION
15:0	Extended Capabilities ID	RO	Read as 0002h to indicate that these are PCI express extended capability registers for virtual channel.
19:16	Capability Version	RO	Read as 1h. Indicates PCI-SIG defined PCI Express capability structure version number.
31:20	Next Capability Offset	RO	Pointer points to the PCI Express Power Budgeting Capability register.  Reset to 20Ch.

## 7.2.93 PORT VC CAPABILITY REGISTER 1 – OFFSET 144h

BIT	FUNCTION	TYPE	DESCRIPTION
2:0	Extended VC Count	HwInt RO	It indicates the number of extended Virtual Channels in addition to the default VC supported by the Switch. The default value may be changed by the status of strapped pin, or auto-loading from EEPROM.  Bit[2:1]: Reset to 00b. Bit[0]: Reset to the status of VC1 EN strapped pin.
3	Reserved	RsvdP	Not Support.
6:4	LowPriority Extended VC Count	RO	It indicates the number of extended Virtual Channels in addition to the default VC belonging to the low-priority VC (LPVC) group. The default value may be changed by auto-loading from EEPROM.  Reset to 000b.
7	Reserved	RsvdP	Not Support.
9:8	Reference Clock	RO	It indicates the reference clock for Virtual Channels that support time-based WRR Port Arbitration. Defined encoding is 00b for 100 ns reference clock.  Reset to 00b.
11:10	Port Arbitration Table Entry Size	RO	Read as 10b to indicate the size of Port Arbitration table entry in the device is 4 bits.  Reset to 10b.
31:12	Reserved	RsvdP	Not Support.





#### 7.2.94 PORT VC CAPABILITY REGISTER 2 – OFFSET 148h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	VC Arbitration Capability	RO	It indicates the types of VC Arbitration supported by the device for the LPVC group. This field is valid when LPVC is greater than 0. The Switch supports Hardware fixed arbitration scheme, e.g., Round Robin and Weight Round Robin arbitration with 32 phases in LPVC.  Reset to 03h if offset 144h.bit[0]=1. Reset to 00h if offset 144h.bit[0]=0.
23:8	Reserved	RsvdP	Not Support.
31:24	VC Arbitration Table Offset	RO	It indicates the location of the VC Arbitration Table as an offset from the base address of the Virtual Channel Capability register in the unit of DQWD (16 bytes).  Reset to 03h if offset 144h.bit[0]=1. Reset to 00h if offset 144h.bit[0]=0.

#### 7.2.95 PORT VC CONTROL REGISTER - OFFSET 14Ch

BIT	FUNCTION	TYPE	DESCRIPTION
0	Load VC Arbitration Table	RW	When set, the programmed VC Arbitration Table is applied to the hardware. This bit always returns 0b when read.
3:1	VC Arbitration Select	RW	Reset to 0b.  This field is used to configure the VC Arbitration by selecting one of the supported VC Arbitration schemes. The valid values for the schemes supported by Switch are 0b and 1b. Other value than these written into this register will be treated as default.  Reset to 000b.
15:4	Reserved	RsvdP	Not Support.

## 7.2.96 PORT VC STATUS REGISTER - OFFSET 14Ch

BIT	FUNCTION	TYPE	DESCRIPTION
16	VC Arbitration Table Status	RO	When set, it indicates that any entry of the VC Arbitration Table is written by software. This bit is cleared when hardware finishes loading values stored in the VC Arbitration Table after the bit of "Load VC Arbitration Table" is set.  Reset to 0b.
31:17	Reserved	RsvdP	Not Support.

# 7.2.97 VC RESOURCE CAPABILITY REGISTER (0) – OFFSET 150h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Port Arbitration Capability	RO	It indicates the types of Port Arbitration supported by the VC resource. The Switch supports Hardware fixed arbitration scheme, e.g., Round Robin, Weight Round Robin (WRR) arbitration with 128 phases (3~4 enabled ports) and Time-based WRR with 128 phases (3~4 enabled ports). Note that the Time-based WRR is only valid in VC1.  Reset to 19h.
13:8	Reserved	RsvdP	Not Support.
14	Advanced Packet Switching	RO	When set, it indicates the VC resource only supports transaction optimized for Advanced Packet Switching (AS).  Reset to 0b.





BIT	FUNCTION	TYPE	DESCRIPTION
15	Reject Snoop Transactions	RO	This bit is not applied to PCle Switch.  Reset to 0b.
22:16	Maximum Time Slots	RO	It indicates the maximum numbers of time slots (minus one) are allocated for Isochronous traffic. The default value may be changed by auto-loading from EEPROM.  Reset to 7Fh.
23	Reserved	RsvdP	Not Support.
31:24	Port Arbitration Table Offset	RO	It indicates the location of the Port Arbitration Table (n) as an offset from the base address of the Virtual Channel Capability register in the unit of DQWD (16 bytes).  Reset to 04h for Port Arbitration Table (0).

## 7.2.98 VC RESOURCE CONTROL REGISTER (0) – OFFSET 154h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	T C/VC Map	RW	This field indicates the TCs that are mapped to the VC resource. Bit locations within this field correspond to TC values. When the bits in this field are set, it means that the corresponding TCs are mapped to the VC resource. The default value may be changed by auto-loading from EEPROM.  Reset to FFh.
15:8	Reserved	RsvdP	Not Support.
16	Load Port Arbitration Table	RW	When set, the programmed Port Arbitration Table is applied to the hardware. This bit always returns 0b when read.  Reset to 0b.
19:17	Port Arbitration Select	RW	This field is used to configure the Port Arbitration by selecting one of the supported Port Arbitration schemes. The permissible values for the schemes supported by Switch are 000b and 011b at VC0, other value than these written into this register will be treated as default.  Reset to 000b.
23:20	Reserved	RsvdP	Not Support.
26:24	VC ID	RO	This field assigns a VC ID to the VC resource.  Reset to 000b.
30:27	Reserved	RsvdP	Not Support.
31	VC Enable	RW	0b: disables this Virtual Channel 1b: enables this Virtual Channel Reset to 1b.

#### 7.2.99 VC RESOURCE STATUS REGISTER (0) – OFFSET 158h

BIT	FUNCTION	TYPE	DESCRIPTION
15:0	Reserved	RsvdP	Not Support.
16	Port Arbitration Table Status	RO	When set, it indicates that any entry of the Port Arbitration Table is written by software. This bit is cleared when hardware finishes loading values stored in the Port Arbitration Table after the bit of "Load Port Arbitration Table" is set.  Reset to 0b.
17	VC Negotiation Pending	RO	When set, it indicates that the VC resource is still in the process of negotiation. This bit is cleared after the VC negotiation is complete.  Reset to 0b.
31:18	Reserved	RsvdP	Not Support.





#### 7.2.100 VC RESOURCE CAPABILITY REGISTER (1) - OFFSET 15Ch

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Port Arbitration Capability	RO	It indicates the types of Port Arbitration supported by the VC resource. The Switch supports Hardware fixed arbitration scheme, e.g., Round Robin, Weight Round Robin (WRR) arbitration with 128 phases (3-4 enabled ports) and Time-based WRR with 128 phases (3-4 enabled ports). Note that the Time-based WRR is only valid in VC1.  Reset to 19h if offset 144h.bit[0]=1.  Reset to 00h if offset 144h.bit[0]=0.
13:8	Reserved	RsvdP	Not Support.
14	Advanced Packet Switching	RO	When set, it indicates the VC resource only supports transaction optimized for Advanced Packet Switching (AS).  Reset to 0b.
15	Reject Snoop Transactions	RO	This bit is not applied to PCIe Switch.  Reset to 0b.
22:16	Maximum Time Slots	RO	It indicates the maximum numbers of time slots (minus one) are allocated for Isochronous traffic. The default value may be changed by auto-loading from EEPROM.  Reset to 7Fh if offset 144h.bit[0]=1. Reset to 00h if offset 144h.bit[0]=0.
23	Reserved	RsvdP	Not Support.
31:24	Port Arbitration Table Offset	RO	It indicates the location of the Port Arbitration Table (n) as an offset from the base address of the Virtual Channel Capability register in the unit of DQWD (16 bytes).  Reset to 08h for Port Arbitration Table (1) if offset 144h.bit[0]=1.  Reset to 00h if offset 144h.bit[0]=0.

### 7.2.101 VC RESOURCE CONTROL REGISTER (1) - OFFSET 160h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	T C/VC Map	RW (Exception for bit0)	This field indicates the TCs that are mapped to the VC resource. Bit locations within this field correspond to TC values. When the bits in this field are set, it means that the corresponding TCs are mapped to the VC resource. Bit 0 of this filed is read-only and must be set to "0" for the VC1. The default value may be changed by auto-loading from EEPROM.  Reset to 00h.
15:8	Reserved	RsvdP	Not Support.
16	Load Port Arbitration Table	RW	When set, the programmed Port Arbitration Table is applied to the hardware. This bit always returns 0b when read.  Reset to 0b.
19:17	Port Arbitration Select	RW	This field is used to configure the Port Arbitration by selecting one of the supported Port Arbitration schemes. The permissible values for the schemes supported by Switch are 000b, 011b and 100b at VC1, other value than these written into this register will be treated as default.  Reset to 000b.
23:20	Reserved	RsvdP	Not Support.
26:24	VC ID	RW	This field assigns a VC ID to the VC resource.  Reset to 001b if offset 144h.bit[0]=1.  Reset to 000b if offset 144h.bit[0]=0.
30:27	Reserved	RsvdP	Not Support.
31	VC Enable	RW	0b: disables this Virtual Channel 1b: enables this Virtual Channel Reset to 0b.



### 7.2.102 VC RESOURCE STATUS REGISTER (1) – OFFSET 164h

BIT	FUNCTION	TYPE	DESCRIPTION
15:0	Reserved	RsvdP	Not Support.
16	Port Arbitration Table Status	RO	When set, it indicates that any entry of the Port Arbitration Table is written by software. This bit is cleared when hardware finishes loading values stored in the Port Arbitration Table after the bit of "Load Port Arbitration Table" is set.  Reset to 0b.
17	VC Negotiation Pending	RO	When set, it indicates that the VC resource is still in the process of negotiation. This bit is cleared after the VC negotiation is complete.  Reset to 0b.
31:18	Reserved	RsvdP	Not Support.

#### 7.2.103 VC ARBITRATION TABLE REGISTER - OFFSET 170h

The VC arbitration table is a read-write register array that contains a table for VC arbitration. Each table entry allocates four bits, of which three bits are used to represent VC ID and one bit is reserved. A total of 32 entries are used to construct the VC arbitration table. The layout for this register array is shown below.

Table 7-1 Register Array Layout for VC Arbitration

31 - 28	27 - 24	23 - 20	19 - 16	15 - 12	11 - 8	7 - 4	3 - 0	Byte Location
Phase	Phase	Phase	Phase	Phase	Phase	Phase	Phase	00h
[7]	[6]	[5]	[4]	[3]	[2]	[1]	[0]	OOH
Phase	Phase	Phase	Phase	Phase	Phase	Phase	Phase	04h
[15]	[14]	[13]	[12]	[11]	[10]	[9]	[8]	0411
Phase	Phase	Phase	Phase	Phase	Phase	Phase	Phase	08h
[23]	[22]	[21]	[20]	[19]	[18]	[17]	[16]	Uoli
Phase	Phase	Phase	Phase	Phase	Phase	Phase	Phase	0Ch
[31]	[30]	[29]	[28]	[27]	[26]	[25]	[24]	UCII

## 7.2.104 PORT ARBITRATION TABLE REGISTER (0) and (1) – OFFSET 180h and 1C0h

The Port arbitration table is a read-write register array that contains a table for Port arbitration. Each table entry allocates two bits to represent Port Number. The table entry size is dependent on the number of enabled ports (refer to bit 10 and 11 of Port VC capability register 1). The arbitration table contains 128 entries if three or four ports are to be enabled. The following table shows the register array layout for the size of entry equal to two.

Table 7-2 Table Entry Size in 4 Bits

63 - 56	55 - 48	47 - 40	39 - 32	31 - 24	23 - 16	15 - 8	7 - 0	Byte Location
Phase	00h							
[15:14]	[13:12]	[11:10]	[9:8]	[7:6]	[5:4]	[3:2]	[1:0]	OOH
Phase	08h							
[31:30]	[29:28]	[27:26]	[25:24]	[23:22]	[21:20]	[19:18]	[17:16]	0011
Phase	10h							
[47:46]	[45:44]	[43:42]	[41:40]	[39:38]	[37:36]	[35:34]	[33:32]	1011
Phase	18h							
[63:62]	[61:60]	[59:58]	[57:56]	[55:54]	[53:52]	[51:50]	[49:48]	1011
Phase	20h							





63 - 56	55 - 48	47 - 40	39 - 32	31 - 24	23 - 16	15 - 8	7 - 0	Byte Location
[79:78]	[77:76]	[75:74]	[73:72]	[71:70]	[69:68]	[67:66]	[65:64]	
Phase	28h							
[95:94]	[93:92]	[91:90]	[89:88]	[87:86]	[85:84]	[83:82]	[81:80]	2011
Phase	30h							
[111:110]	[109:108]	[107:106]	[105:104]	[103:102]	[101:100]	[99:98]	[97:96]	3011
Phase	38h							
[127:126]	[125:124]	[123:122]	[121:120]	[119:118]	[117:116]	[115:114]	[113:112]	3611

## 7.2.105 PCI EXPRESS POWER BUDGETING CAPABILITY REGISTER – OFFSET 20Ch

BIT	FUNCTION	TYPE	DESCRIPTION
15:0	Extended Capabilities ID	RO	Read as 0004h to indicate that these are PCI express extended capability registers for power budgeting.
19:16	Capability Version	RO	Read as 1h. Indicates PCI-SIG defined PCI Express capability structure version number.
31:20	Next Capability Offset	RO	Pointer points to the PCI Express Extended ACS capability register/LTR capability register.  Reset to 230h (Upstream port). Reset to 220h (Downstream ports).

#### 7.2.106 DATA SELECT REGISTER - OFFSET 210h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Data Selection	RW	It indexes the power budgeting data reported through the data register.  When 00h, it selects D0 Max power budget When 01h, it selects D0 Sustained power budget Other values would return zero power budgets, which means not supported Reset to 00h.
31:8	Reserved	RsvdP	Not Support.

#### 7.2.107 POWER BUDGETING DATA REGISTER - OFFSET 214h

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Base Power	RO	It specifies the base power value in watts. This value represents the required power budget in the given operation condition. The default value may be changed by auto-loading from EEPROM.  Reset to 04h.
9:8	Data Scale	RO	It specifies the scale to apply to the base power value.  Reset to 00b.
12:10	PM Sub State	RO	It specifies the power management sub state of the given operation condition. It is initialized to the default sub state.  Reset to 000b.
14:13	PM State	RO	It specifies the power management state of the given operation condition. It defaults to the D0 power state.  Reset to 00b.
17:15	Туре	RO	It specifies the type of the given operation condition. It defaults to the Maximum power state.  Reset to 111b.





BIT	FUNCTION	TYPE	DESCRIPTION
20:18	Power Rail	RO	It specifies the power rail of the given operation condition.  Reset to 010b.
31:21	Reserved	RsvdP	Not Support.

#### 7.2.108 POWER BUDGET CAPABILITY REGISTER - OFFSET 218h

BIT	FUNCTION	TYPE	DESCRIPTION	
0	System Allocated	RO	When set, it indicates that the power budget for the device is included within the system power budget. The default value may be changed by auto-loading from EEPROM.  Reset to 0b.	
31:1	Reserved	RsvdP	Not Support.	

# 7.2.109 ACS EXTENDED CAPABILITY HEADER – OFFSET 220h (Downstream Port Only)

BIT	FUNCTION N	TYPE	DESCRIPTION
15:0	PCI Express Extended Capability ID	RO	Read as 000Dh to indicate PCI Express Extended Capability ID for ACS Extended Capability.
19:16	Capability Version	RO	Read as 1h. Indicates PCI-SIG defined PCI Express capability structure version number.
31:20	Next Capability ID	RO	Read as 000h. No other ECP registers.

#### 7.2.110 ACS CAPABILITY REGISTER - OFFSET 224h (Downstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION	
0	ACS Source Validation	RO	Indicated the implements of ACS Source Validation.  Reset to 1b.	
1	ACS Translation Blocking	RO	Indicated the implements of ACST ranslation Blocking.  Reset to 1b.	
2	ACS P2P Request Redirect	RO	Indicated the implements of ACSP2P Request Redirect.  Reset to 1b.	
3	ACS P2P Completion Redirect	RO	Indicated the implements of ACSP2P Completion Redirect.  Reset to 1b.	
4	ACS Upstream Forwarding	RO	Indicated the implements of ACS Upstream Forwarding.  Reset to 1b.	
5	ACS P2P Egress control	RO	Indicated the implements of ACSP2P Egress control.  Reset to 1 b.	
6	ACS Direct Translated P2P	RO	Indicated the implements of ACS Direct Translated P2P.  Reset to 1b.	
7	Reserved	RsvdP	Not Support.	
15:8	Egress Control Vector Size	RO	Encodings 01h – FFh directly indicate the number of applicable bits in the Egress Control Vector.  Reset to 08h.	
16	ACS Source Validation Enable	RW	Enable the source validation.  Reset to 0b.	





BIT	FUNCTION	TYPE	DESCRIPTION
17	ACS Translation Blocking Enable	RW	Enable ACS Translation Blocking.  Reset to 0b.
18	ACS P2P Request Redirect	RW	Enable ACS P2P Request Redirect.  Reset to 0b.
19	ACS P2P Completion Redirect Enable	RW	Enable ACS P2P Completion Redirect Reset to 0b.
20	ACS Upstream Forwarding Enable	RW	Enable ACS Upstream Forwarding.  Reset to 0b.
21	ACS P2P Egress control Enable	RW	Enable ACS P2P Egress control.  Reset to 0b.
22	ACS Direct Translated P2P Enable	RW	Enable ACS Direct Translated P2P.  Reset to 0b.
31:23	Reserved	RsvdP	Not Support.

#### 7.2.111 EGRESS CONTROL VECTOR – OFFSET 228h (Downstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION
7:0	Egress Control Vector	RW	When a given bit is set, peer-to-peer requests targeting the associated Port are blocked or redirected.  Reset to 00h.
31:8	Reserved	RsvdP	Not Support.


# 7.2.112 LTR EXTENDED CAPABILITY HEADER – OFFSET 230h (Upstream Port Only)

BIT	FUNCTION N	TYPE	DESCRIPTION
15:0	PCI Express Extended Capability ID	RO	Read as 0018h to indicate PCI Express Extended Capability ID for LTR Extended Capability.
19:16	Capability Version	RO	Read as 1h. Indicates PCI-SIG defined PCI Express capability structure version number.
31:20	Next Capability ID	RO	Read as 000h. No other ECP registers.

### 7.2.113 MAX SNOOP LATENCY REGISTER - OFFSET 234h (Upstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION	
9:0	Max Snoop Latency Value	RW	. Specifies the maximum snoop latency that a device is permitted to request  Reset to 000h.	
12:10	Max Snoop Latency Scale	RW	This register provides a scale for the value contained within the Maximum Snoop Latency Value field  Reset to 000b	
15:13	Reserved	RsvdP	Not Support.	







# 7.2.114 MAX NO-SNOOP LATENCY REGISTER – OFFSET 234h (Upstream Port Only)

BIT	FUNCTION	TYPE	DESCRIPTION	
25:16	Max No-Snoop Latency Value	RW	. Specifies the maximum no-snoop latency that a device is permitted to request  Reset to 000h.	
28:26	Max No-Snoop Latency Scale	RW	This register provides a scale for the value contained within the Maximum No-Snoop Latency Value field  Reset to 000b	
31.29	Reserved	RsvdP	Not Support	





#### 8 CLOCK SCHEME

The built-in Integrated Reference Clock Buffer of the PI7C9X2G303EL supports three reference clock outputs. The clock buffer feature can be enabled and disabled by strapping the CLKBUF PD pin.

When CLKBUF\_PD pin is asserted low, the clock buffer is enabled. The clock buffer distributes a single 100MHz reference clock input to three Reference Clock Output Pairs, REFCLKO\_P[2:0] and REFCLKO\_N[2:0]. The clock buffer requires 100MHz differential clock inputs through REFCLKI\_P and REFCLKI\_N Pins as show in the following table.

When CLKBUF\_PD pin is asserted high, the clock buffer is in power down mode and disabled. The 100MHz Reference Clock Output Pairs are disabled, and The PI7C9X2G303EL requires 100MHz differential clock inputs through REFCLKP and REFCLKN Pins as shown in the following table.

**Table 8-1 AC Switching Characteristics** 

Symbol	Parameters	Min.	Тур.	Max.	Unit
$F_{IN}$	Reference Clock Frequency		100		MHz
Trise/Tfall	Rise and Fall Time in 20-80%	175		700	ps
DT rise/DT fall	Rise and Fall Time Variation			125	ps
T <sub>pd</sub>	Propagation Delay	2.5		6.5	ns
V <sub>swing</sub> 1	Voltage Including Overshoot	550		1150	mV
$T_{DC}^{2}$	Duty Cycle	45		55	%

#### Note:

- 1. Measurement taken from Single Ended waveform.
- 2. Measurement taken from Differential waveform.
- 3.In general rule, use ac-coupling when differential input >500mV; use dc-coupling when differential input <400mV, such as LVDS drive with 100 ohmacross at the inputs.





#### 9 IEEE 1149.1 COMPATIBLE JTAG CONTROLLER

An IEEE 1149.1 compatible Test Access Port (TAP) controller and associated TAP pins are provided to support boundary scan in PI7C9X2G303EL for board-level continuity test and diagnostics. The TAP pins assigned are TCK, TDI, TDO, TMS and TRST L. All digital input, output, input/output pins are tested except TAP pins.

#### 9.1 INSTRUCTION REGISTER

The IEEE 1149.1 Test Logic consists of a TAP controller, an instruction register, and a group of test data registers including Bypass and Boundary Scan registers. The TAP controller is a synchronous 16-state machine driven by the Test Clock (TCK) and the Test Mode Select (TMS) pins. An independent power on reset circuit is provided to ensure the machine is in TEST LOGIC RESET state at power-up.

PI7C9X2G303EL implements a 5-bit Instruction register to control the operation of the JTAG logic. The defined instruction codes are shown in the following table. Those bit combinations that are not listed are equivalent to the BYPASS (11111) instruction.

**Table 9-1 Instruction Register Codes** 

Instruction	Operation Code (binary)	Register Selected	Operation
EXTEST	00000	Boundary Scan	Drives / receives off-chip test data
SAMPLE	00001	Boundary Scan	Samples inputs / pre-loads outputs
HIGHZ	00101	Bypass	Tri-states out put and I/O pins except TDO pin
CLAMP	00100	Bypass	Drives pins from boundary-scan register and selects Bypass register for shifts
IDCODE	01100	Device ID	Accesses the Device ID register, to read manufacturer ID, part number, and version number
BYPASS	11111	Bypass	Selected Bypass Register
INT_SCAN	00010	Internal Scan	Scan test
PHY_TEST_SIG	01001	Private	Private
MEM_BIST	01010	Memory BIST	Memory BIST test

#### 9.2 BYPASS REGISTER

The required bypass register (one-bit shift register) provides the shortest path between TDI and TDO when a bypass instruction is in effect. This allows rapid movement of test data to and from other components on the board. This path can be selected when no test operation is being performed on the PI7C9X2G303EL.

#### 9.3 DEVICE ID REGISTER

This register identifies Pericom as the manufacturer of the device and details the part number and revision number for the device.

Table 9-2 JTAG Device ID Register

Bit	Type	Value	Description
31-28	RO	0001	Version number
27-12	RO	0000010100001000	Last 4 digits (hex) of the die part number
11-1	RO	01000111111	Pericom identifier assigned by JEDEC
0	RO	1	Fixed bit equal to 1'b1





#### 9.4 BOUNDARY SCAN REGISTER

The boundary scan register has a set of serial shift-register cells. A chain of boundary scan cells is formed by connected the internal signal of the PI7C9X2G303EL package pins. The VDD, VSS, and JTAG pins are not in the boundary scan chain. The input to the shift register is TDI and the output from the shift register is TDO. There are 4 different types of boundary scan cells, based on the function of each signal pin.

The boundary scan register cells are dedicated logic and do not have any system function. Data may be loaded into the boundary scan register master cells from the device input pins and output pin-drivers in parallel by the mandatory SAMPLE and EXTEST instructions. Parallel loading takes place on the rising edge of TCK.

#### 9.5 JTAG BOUNDARY SCAN REGISTER ORDER

Table 9-3 JTAG Boundary Scan Register Definition

Boundary Scan Register Number	Pin Name	Ball Location	Туре	Tri-state Control Cell
0	DWNRST_L[1]	F1	Output2	
1	DWNRST_L[2]	J3	Output2	
2			Internal	
3	TEST1	N3	Input	
4	PERST_L	M1	Input	
5	TEST2	T1	Input	
6	TEST3	V1	Birdir	12
7	VC1_EN	W3	Birdir	12
8	PRSNT[1]	Y1	Birdir	12
9	PRSNT[2]	AA3	Birdir	12
10			Internal	
11	TEST4	AD1	Birdir	12
12	1201 .	1.01	Control	
13	RXPOLINV DIS	AE3	Birdir	12
14	TEST 5	AF1	Birdir	12
15	SMBCLK	AH1	Birdir	12
16	SMBDATA	AK1	Birdir	12
17	PWR SAV	AJ3	Birdir	12
18	SLOTCLK	AR7	Birdir	12
19	GPIO[0]	AR9	Birdir	20
20	G. 10[0]	1110	Control	
21	GPIO[1]	AU6	Birdir	22
22			Control	
23	GPIO[2]	AU8	Birdir	24
24			Control	
25	GPIO[3]	AR11	Birdir	26
26	[- ]		Control	
27	GPIO[4]	AU10	Birdir	28
28			Control	
29	GPIO[5]	AU12	Birdir	30
30			Control	
31	GPIO[6]	AR13	Birdir	32
32			Control	
33	GPIO[7]	AU14	Birdir	34
34			Control	
35	SLOT_IMP[1]	AR15	Birdir	45
36	SLOT_IMP[2]	AU16	Birdir	45
37	,		Internal	
38			Internal	
39	TEST6	AR21	Birdir	45
40			Internal	
41	PL 512B	AR23	Birdir	45
42	_	-	Internal	-




## A Product Line of Diodes Incorporated



PI7C9X2G303EL

Boundary Scan Register Number	Pin Name	Ball Location	Туре	Tri-state Control Cell
43			Internal	
44			Internal	
45			Control	
46			Internal	
47	CLKBUF_PD	AR29	Birdir	45
48			Internal	
49			Internal	
50			Internal	
51	EECLK	AJ35	Output2	
52	EEPD	AK37	Birdir	53
53			Control	







#### 10 POWER MANAGEMENT

The PI7C9X2G303EL supports D0, D1, D2, D3-hot, and D3-cold Power States. The PCI Express Physical Link Layer of the PI7C9X2G303EL device supports the PCI Express Link Power Management with L0, L0s, L1, L2/L3 ready and L3 Power States.

During the transition from D3-hot to D3-cold state, the main power supplies of VDDC and VDDR are turned off to save power while keeping the VDDCAUX and VAUX with the auxiliary power supplies to maintain all necessary information to be restored to the full power D0 state. PI7C9X2G303EL has been designed to have sticky registers that are powered by auxiliary power supplies. PI7C9X2G303EL forwards power management messages to the upstream Switches or root complex.

PI7C9X2G303EL also supports ASPM (Active State Power Management) to facilitate the link power saving.





#### 11 POWER SEQUENCE

As long as PERST# is active, all PCI Express functions are held in reset. The main supplies ramp up to their specified levels (3.3V). Sometime during this stabilization time, the REFCLK starts and stabilizes. After there has been time (100 ms) for the power and clock to become stable, PERST# is deasserted high and the PCI Express functions can start up.

It is recommended to power up the I/O voltage (3.3V) first and then the core voltage (1.0V) or power up I/O voltage and core voltage simultaneously for both Aux and Main power rails.




Figure 11-1 Initial Power-Up Sequence

Power-down sequence is the reverse of power-up sequence



#### 12 ELECTRICAL AND TIMING SPECIFICATIONS

#### 12.1 ABSOLUTE MAXIMUM RATINGS

#### Table 12-1 Absolute Maximum Ratings

(Above which the useful life may be impaired. For user guidelines, not tested.)

Item	Absolute Max. Rating
Storage Temperature (T <sub>store</sub> )	-65°C to 150°C
Junction Temperature $(T_j)$	125 °C
Digital core and analog supply voltage to ground potential (VDDC, AVDD and VDDCAUX)	-0.3v to 1.5v
Digital I/O and analog high supply voltage to ground potential (VDDR, CVDDR, AVDDH and VAUX)	-0.3v to 4.0v
DC input voltage for Digital I/O signals	-0.3v to 4.0v

#### Note:

Stresses greater than those listed under MAXIMUM RATINGS may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods of time may affect reliability.

#### 12.2 DC SPECIFICATIONS

**Table 12-2 DC Electrical Characteristics** 

Symbol	Description	Min.	Тур.	Max.	Unit
VDDC1	Digital Core Power	0.95	1.0	1.1	
VDDR	Digital I/O Power	3.0	3.3	3.6	
CVDDR	Reference Clock Power	3.0	3.3	3.6	
VDDCAUX	Auxiliary Core Power	0.95	1.0	1.1	
VAUX	Auxiliary I/O Power	3.0	3.3	3.6	
AVDD	PCI Express Analog Power	0.95	1.0	1.1	V
AVDDH	PCI Express Analog High Voltage Power	3.0	3.3	3.6	
$V_{IH}$	Input High Voltage	2.0		5.5	
V <sub>IL</sub>	Input Low Voltage	-0.3		0.8	
V <sub>OH</sub>	Output High Voltage	2.4			
$V_{OL}$	Output Low Voltage			0.4	
$R_{PU}$	Pull-up Resistor	63K	92K	142K	Ω
$R_{PD}$	Pull-down Resistor	57K	91K	159K	2.2
RST# <sub>Slew</sub> <sup>2</sup>	PERST_L Slew Rate	50			mV/ns

#### Note:

- In order to support auxiliary power management fully, it is recommended to have VDDC and VDDCAUX separated.
- 2. The min. value for PERST\_L Slew Rate is 50 mV/ns, which translates to the requirement that the time for PERST\_L from 0V to 3.3V should be less than 66 ns.

#### 12.3 AC SPECIFICATIONS

Table 12-3 PCI Express Interface - Differential Transmitter (TX) Output (5.0 Gbps) Characteristics

Parameter	Symbol	Min	Тур	Max	Unit
Unit Interval	UI	199.94	200.0	200.06	ps
Differential p-p TX voltage swing	V <sub>TX-DIFF-P-P</sub>	800	-	-	mV
					ppd
Lowpower differential p-pTX voltage	V <sub>TX-DIFF-P-P-LOW</sub>	400	-	-	mV





Parameter	Symbol	Min	Тур	Max	Unit
swing					ppd
TX de-emphasis level ratio	V <sub>TX-DE-RATIO-3.5dB</sub>	-3.0	-	-4.0	dB
TX de-emphasis level ratio	V <sub>TX-DE-RATIO-6dB</sub>	-5.5		-6.5	dB
Transmitter Eye including all jitter sources	T <sub>TX-EYE</sub>	0.75	-	-	UI
TX deterministic jitter>1.5 MHz	T <sub>TX-HF-DJ-DD</sub>	-	-	0.15	UI
TX RMS jitter < 1.5 MHz	T <sub>TX-LF-RMS</sub>	-	-	3.0	Ps
					RMS
Transmitter rise and fall time	T <sub>TX-RISE-FALL</sub>	0.15	-	-	UI
TX rise/fall mismatch	T <sub>RF-MISMATCH</sub>	-	-	0.1	UI
Maximum TXPLL Bandwidth	BW <sub>TX-PLL</sub>	-	-	16	MHz
Minimum TX PLL BW for 3dB peaking	BW <sub>TX-PLL-LO-3DB</sub>	8	-	-	MHz
TX PLL peaking with 8 MHz min BW	PKG <sub>TX-PLL1</sub>	-	-	3.0	dB
DC Differential TX Impedance	Z <sub>TX-DIFF-DC</sub>	80	-	120	Ω
Transmitter Short-Circuit Current Limit	I <sub>TX-SHORT</sub>	-	-	90	mA
TX DC Common Mode Voltage	V <sub>TX-DC-CM</sub>	0	-	3.6	V
Absolute Delta of DC Common Mode	V <sub>TX-CM-DC-ACTIVE-IDLE-</sub>	0	-	100	mV
Voltage During L0 and Electrical Idle	DELTA				
Absolute Delta of DC Common Mode	V <sub>TX-CM-DC-LINE-DELTA</sub>	0	-	25	mV
Voltage between D+ and D-					
Electrical Idle Differential Peak Output	V <sub>TX-IDLE-DIFF-AC-p</sub>	0	-	20	mV
Voltage					
DC Electrical Idle Differential Output	V <sub>TX-IDLE-DIFF-DC</sub>	0	-	5	mV
Voltage					
The Amount of Voltage Change Allowed	V <sub>TX-RCV-DETECT</sub>	-	-	600	mV
During Receiver Detection					
Lane-to-Lane Output Skew	L <sub>TX-SKEW</sub>	-	-	500 ps	ps
				+ 4 UI	

#### Table 12-4 PCI Express Interface - Differential Transmitter (TX) Output (2.5 Gbps) Characteristics

Parameter	Symbol	Min	Тур	Max	Unit
Unit Interval	UI	399.88	400.0	400.12	ps
Differential p-p TX voltage swing	V <sub>TX-DIFF-P-P</sub>	800	-	-	mV
					ppd
Low power differential p-pTX voltage	V <sub>TX-DIFF-P-P-LOW</sub>	400	-	-	mV
swing					ppd
TX de-emphasis level ratio	V <sub>TX-DE-RATIO</sub>	-3.0	-	-4.0	dB
Minimum TX eye width	T <sub>TX-EYE</sub>	0.75	-	·	UI
Maximum time between the jitter median	T <sub>TX-EYE-MEDIAN-to-MAX</sub> -	-	-	0.125	UI
and max deviation from the median	JITTER				
Transmitter rise and fall time	T <sub>TX-RISE-FALL</sub>	0.125	-	-	UI
Maximum TXPLL Bandwidth	BW <sub>TX-PLL</sub>	-	-	22	MHz
Maximum TXPLL BW for 3dB peaking	BW <sub>TX-PLL-LO-3DB</sub>	1.5	-	-	MHz
Absolute Delta of DC Common Mode	V <sub>TX-CM-DC-ACTIVE-IDLE</sub> -	0	-	100	mV
Voltage During L0 and Electrical Idle	DELTA				
Absolute Delta of DC Common Mode	V <sub>TX-CM-DC-LINE-DELTA</sub>	0	-	25	mV
Voltage between D+ and D-					
Electrical Idle Differential Peak Output	V <sub>TX-IDLE-DIFF-AC-p</sub>	0	-	20	mV
Voltage					
The Amount of Voltage Change Allowed	V <sub>TX-RCV-DETECT</sub>	-	-	600	mV
During Receiver Detection					
Transmitter DC Common Mode Voltage	$V_{TX-DC-CM}$	0	-	3.6	V
Transmitter Short-Circuit Current Limit	I <sub>TX-SHORT</sub>	-	-	90	mA
DC Differential TX Impedance	Z <sub>TX-DIFF-DC</sub>	80	100	120	Ω
Lane-to-Lane Output Skew	L <sub>TX-SKEW</sub>	-	-	500 ps	ps
				+ 2 UI	

Table 12-5 PCI Express Interface - Differential Receiver (RX) Input (5.0 Gbps) Characteristics

Parameter	Symbol	Min	Тур	Max	Unit
Unit Interval	UI	199.94	200.0	200.06	ps
Differential RX Peak-to-Peak Voltage	V <sub>RX-DIFF-PP-CC</sub>	120	-	1200	mV
Total jitter tolerance	$TJ_{RX}$	0.68	-	-	UI
Receiver DC common mode impedance	$Z_{RX-DC}$	40	-	60	Ω



Parameter	Symbol	Min	Тур	Max	Unit
RX AC Common Mode Voltage	V <sub>RX-CM-AC-P</sub>	-	-	150	mV
Electrical Idle Detect Threshold	V <sub>RX-IDLE-DET-DIFFp-p</sub>	65	-	175	mV

Table 12-6 PCI Express Interface - Differential Receiver (RX) Input (2.5 Gbps) Characteristics

Parameter	Symbol	Min	Тур	Max	Unit
Unit Interval	UI	399.88	400.0	400.12	ps
Differential RX Peak-to-Peak Voltage	V <sub>RX-DIFF-PP-CC</sub>	175	-	1200	mV
Receiver eye time opening	T <sub>RX-EYE</sub>	0.4	-	-	UI
Maximum time delta between median and	T <sub>RX-EYE-MEDIAN-to-MAX</sub> -	-	-	0.3	UI
deviation from median	JITTER				
Receiver DC common mode impedance	$Z_{RX-DC}$	40	-	60	Ω
DC differential impedance	Z <sub>RX-DIFF-DC</sub>	80	-	120	Ω
RX AC Common Mode Voltage	V <sub>RX-CM-AC-P</sub>	-	-	150	mV
DC input CM input impedance during reset	Z <sub>RX-HIGH-IMP-DC</sub>	200	-	-	kΩ
or power down					
Electrical Idle Detect Threshold	V <sub>RX-IDLE-DET-DIFFp-p</sub>	65	-	175	mV
Lane to Lane skew	L <sub>RX-SKEW</sub>	-	-	20	ns

#### 12.4 OPERATING AMBIENT TEMPERATURE

#### **Table 12-7 Operating Ambient Temperature**

(Above which the useful life may be impaired.)

Item	Min.	Max.	Units
Ambient Temperature with power applied	-40	85	°C

Note:

Exposure to high temperature conditions for extended periods of time may affect reliability.

#### 12.5 POWER CONSUMPTION

**Table 12-8 Power Consumption** 

Active Lane	1.0V	DDC	1.0V	AUX	1.0A	VDD	3.3AV	/DDH	3.3V	DDR	3.3V	AUX	To	otal	Unit
per Port	Тур	Max	Тур	Max	Тур	Max	Тур	Max	Тур	Max	Тур	Max	Тур	Max	Unit
1/1/1	123.20	327.91	2.20	2.42	144.10	346.06	35.31	38.84	319.44	351.38	0.03	0.03	624.28	1,066.65	mW
1/1/1, ec <sup>1</sup>	123.20	327.91	2.20	2.42	144.10	346.06	35.31	38.84	6.60	7.26	0.03	0.03	311.44	722.52	mW


Test Conditions:

- Typical power measured under the conditions of 1.0V/3.3V power rail without device usage on all downstream ports.
- Maximum power measured under the conditions of 1.1V/3.63V with PCIe2 devices usage on all downstream ports.
- Ambient Temperature at 25°C
- Power consumption in the table is a reference, be affected by various environments, bus traffic and power supply etc.

Note:

1: Use external clock buffer, Disable internal clock buffer.







#### 13 PACKAGE INFORMATION

The package of PI7C9X2G303EL is a 8mm x 8mm aQFN (136 Pin) package. The following are the package information and mechanical dimension:

Figure 13-1 Package outline drawing










Figure 13-2 Package bottom view









#### 14 ORDERING INFORMATION

Part Number	Temperature Range	Package	Pb-Free & Green
PI7C9X2G303EL□ZXEX	-40° to 85°C	136-pin aQFN	Yes
	(Industrial Temperature)	8mm x 8mm	

