


Recommend PCB Layout

Specifications :  
 Voltage rating: 250V AC / DC  
 Current rating: 7A AC / DC  
 Withstanding voltage: 1500V AC/minute  
 Temperature range: -25°C~+85°C  
 Insulation resistance: >1000MΩ  
 Contact resistance: ≤10mΩ  
 After environmental testing: ≤20mΩ



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	3.96	7.92	09	31.68	35.64
03	7.92	11.88	10	35.64	39.60
04	11.88	15.84	11	39.60	43.56
05	15.84	19.80	12	43.56	47.52
06	19.80	23.76	13	47.52	51.48
07	23.76	27.72	14	51.48	55.44
08	27.72	31.68	15	55.44	59.40

APPROVALS		DATE	DRAWING NO.		SCALE	SHEET
DRAWN	G.M.Chen	2015/5/29	EPCALON 德之隆® ELECTRONICS CO.,LTD		1:1	1 OF 1
CHECKED			TITLE: 3.96mm Crimp Style Connectors			
APPROVALS			PART NO. VH-XXAW			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
TOLERANCES ARE: 30~40L ±0.30 ANGLE UNIT: mm SCALE: 1:1 SHEET 1 OF 1 10~30 ±0.20 ±2° DRAWING NO. PROJ.						