		2.00 0.197	0.079]						U				
		ى ب											
			0.5[0.16]] [] [[0.08]	7.8[0.307]		1 80.01 0.0 0.3 [0.01	1.2[0.047]					
	[Г	1			F			٦	RATING			0.3A 50V DC
	4	Terminal		4	Brass	(0.30t)	ag Plated			CIRCUIT			1P2T
		Base				ic Resin			-	CONTACT	RESIST	ANCE	100mΩ MAX
	(3)	Cover —		1	Sus		Natural		-	TRAVEL			2mm
	3	Cover			Out	5	i tatarar						
	(3) (2) (1)	Cover Keystake		1	Pa		Black			OPERATIN	G FORC	E	250±100gf
	2	Keystake	 TER,NO	1 QTY		66		REMARK	<				
T	2	Keystake	TER,NO	1 QTY	Pa	66	Black		J 	OPERATIN OPERATIN	G LIFE((CYCLES)	250±100gf 10,000
T	2	Keystake	TER,NO		Pa	66 RIAL	Black	UNIT	MM	OPERATIN OPERATIN PROJCTED	G LIFE((CYCLES) PRODUCT N	250±100gf 10,000 AME:
T	2	Keystake	 TER,NO		Pa6 MATE	COMMON	Black FINISHING	UNIT DRAWN BY	MM FUYUAN	OPERATIN OPERATIN PROJCTED CHECKED BY	G LIFE((⊕ ₽ COCO	CYCLES) PRODUCT N MODEL NO:	250±100gf 10,000 AME: SK-13D07-5
	2	Keystake			Pa6 MATEI	66 RIAL	Black FINISHING TOLERANCE ± 0.10 ± 0.15	UNIT DRAWN BY DATE	MM	OPERATIN OPERATIN PROJCTED CHECKED BY APPROVAL B	G LIFE((⊕ COCO ALEN	PRODUCT N MODEL NO: Https:	250±100gf 10,000 AME: SK-13D07-5 www.rocpu.tw
		Keystake		RO	Pa6 MATE	66 RIAL COMMON	Black FINISHING	UNIT DRAWN BY	MM FUYUAN	OPERATIN OPERATIN PROJCTED CHECKED BY	G LIFE((⊕ COCO ALEN	CYCLES) PRODUCT N MODEL NO:	250±100gf 10,000 AME: SK-13D07-5 www.rocpu.tw

D

п

Е

F

G

В

–12.80 [0.50]–

Α

4.4[0.173]

1

С