


			EM F	PAPT NAME TER,NO		R,NO	QTY MATER		L	FINISHING	REMARK		OPERATING LIFE			10000	
5	A4								COMMON	TOLERANCE	UNIT		MM	PROJCTED		PRODUCT NAME:	
	A3									TOLENANCE	DRAWN	ΒY	FUYUAN	CHECKED BY	COCO	MODEL NO: SS-14D07-3	
	A2						台	普	X.XX	± 0.10	DATE		2019	APPROVAL B	ALEN	Https:	www.rocpu.tw
	A1				ROCE	<u></u>	X.X	± 0.15 ± 0.25		ROCPU TECHNOLONGY CO., LTC							
F	REV	DATE	REVISION DESCRIPTION ISSUE		ISSUE			ANGULA			opies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of appara			,			
			Α	A		В	B		C		D			E		F	G

D

4	Terminal		6	Brass (0.30t)	ag Plated	
3	Base		1	Phenolic Resin		
2	Cover		1	Sus	Natural	
\bigcirc	Keystake		1	Pa66	Black	
ITEM	PAPT NAME	TER,NO	QTY	MATERIAL	FINISHING	REMARK








С

В

Α



RATING

CIRCUIT

CONTACT RESISITANCE

TRAVEL

OPERATING FORCE

0.3A 50V DC

1P2T

100MΩ MAX

2MM

250±100gf

6 6 6 6 6 0 0

F

G

2

3

Е