



PCB LAND DIMENSION



CIRCUIT DIAGRAM



RATING: DC 12V 50mA  
 CONTACT RESISTANCE: 100mΩ MAX  
 GENERAL TOLERANCE: ±0.3  
 Gram force: 180±50gf  
 service life: 300,000 cycles

7	STEM	1	PA6T	
6	COVER	1	BRASS	Ag plating
5	PRESSURE PAD	1	SUS	
4	RUBBER PAD	1	SILICA GEL	
3	CONTACT	1	PPA	Ag plating
2	TERMINAL	1	SUS	Ag plating
1	BASE	1	PA66	
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

A4				
A3				
A2				
A1				
REV	DATE	REVISION DESCRIPTION	ISSUE	



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TPS645-SNQ70LFS
DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw

**ROCPU TECHNOLOGY CO., LTD**

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission