


Led Color	Part No	VR	IF	Recommended Operating	IF	
					Nom	Max
White	TM-002-M2-01	DC5V	20mA	20mA	3.0V	3.6V
Red	TM-002-M2-02	DC5V	20mA	20mA	1.7V	2.4V
Blue	TM-002-M2-03	DC5V	20mA	20mA	3.0V	3.6V
Green	TM-002-M2-04	DC5V	20mA	20mA	1.9V	2.4V
Yellow	TM-002-M2-05	DC5V	20mA	20mA	1.9V	2.4V

ITEM	PAPT NAMF	TER.NO	QTY	MATERIAL	FINISHING	REMARK
7	LED		1			
6	Hat		1	ABS		
5	Terminal	---	4	Brass (0.30t)	ag Plated	---
4	Contact	---	1	F.ag/SUS		---
3	Base	---	1	PA66		---
2	Cover	---	1	PA66		---
1	Keystake	---	1	PA66		---



广东星坤科技股份有限公司

生	日期
救	
文件	工程
章	

DSND		DATE		SCALE: N/A	MODEL TYPE: LED SWITCH
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm/in	DWG NO.: TM-002-M2-X
APPD		DATE		SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED					WEIGHT: 1.0g
					SHEET: 1/1
					REVISION: A0

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					units: mm
ΔX					tolerance: X.X ±0.2mm
ΔX					X.XX ±0.1mm
ΔX					X.XXX ±0.05mm