



**规格说明: Specifications:**

**电气特性: Electrical:**

1. 额定电流: Current Rating  
1.0A/contact terminal
2. 额定电压: Voltage Rating  
30V DC
3. 接触阻抗: Contact Resistance  
50 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage:  
300 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance:  
100MEGA ohms MIN

**物理性能: Mechanical:**

1. 插拔力: Connector Mate and Umate Force  
Mate force: 3.0kgf (MAX)  
Urmate force: 0.7kgf (MIN)
2. 端子保持力: Terminal Retention  
0.5kgf (MIN)

**原材料: Material:**

1. 塑胶: Housing:  
Hig Temperature Tnermaplastics,  
UI 94V-0 LCP Black
  2. 端子: Contact: Copper Alloy H65-EH
  3. 外壳: Shell: H65-H
- 电镀: Finish:**
1. 端子: Contact: Plated Gold in Mating Area;  
Tin On Solder Tails
  2. 外壳: Shell:  
Nickel Plating (能过炉自动上锡)

GENERAL TOLERANCES		
DIMENSIONS	II	III
X,XXX	±0.01	±0.02
X,XX	±0.02	±0.03
X,X	±0.05	±0.10
X	±0.10	±0.20
ANGLE	±0.5°	±1.0°

RECOMMENDED PCB LAYOUT  
TOLERANCE: ±0.05

表面处理 PLATED	料号 PART NO.	图号 DRAWING NO.	图名 TITLE
材料 MATERIAL	比例 SCALE	单位 UNIT	页次 PAGE

品名 TITLE	料号 PART NO.	图号 DRAWING NO.	图名 TITLE
规格 SPEC.	比例 SCALE	单位 UNIT	页次 PAGE

III000 USB B TYPE B. 00000 插拔1.0MM 平口 长针	德艺隆电子有限公司
绘图 DRAWING	
审核 CHECKED	
批准 APPROVED	