



Specifications:

1. Electrical:
 - 1.1 Current Rating: 1.8A/contact terminal
 - 1.2 Voltage Rating: 30V DC
 - 1.3 Contact Resistance: 50 milliohms Max
 - 1.4 Dielectric Withstanding Voltage: 300 V AC AT Sea Level
- 1.5 Insulation resistance: 100MEGA ohms MIN
2. Mechanical:
 - 2.1 Connector Mate and Unmate Force
 - Mate force: 3.0kgf (Max)
 - Unmate force: 0.7kgf (MIN)
 - 2.2 Durability: 2000 cycles
3. Material:
 - 3.1 Housing:
 - Hing Temperature Thermoplastics,
 - U1 94V-0 LCP Black
 - 3.2 Contact C5191-EH
 - 3.3 Shell: H65 EH0.3MM
4. PLATING:
 - 4.1 Contact: Plated Gold in Mating Area; Tin On Solder Tails
 - 4.2 Shell: Nickel 50u"Min Plated.

REV.	ECN NO	LOCATIONS	DESCRIPTION	DATE

PART NO:	AO1SBXXXXXXXX1-067
MODEL NO:	XX
UNIT:	MM
SIZE:	A4
TOLERANCE UNSPECIFIED	
.x	0.25
.xx	0.15
.xxx	0.10
Ang.	2'

TITLE:		德艺隆电子有限公司
MATERIAL:		MIRCO USB SS B TYPE 四脚全插(牛角型)短针
FINISH:		
COLOR:		
DR:		
CHK:		
APP:		
SCALE:	5:1	DATE: 2012.05.02
REV:	A	