






Kinghelm®

型号: KH-FG0.5-H2.0-(4-60)PIN

| 序号 | 品名 | 材质 |
|----|----------------|----------------|
| ① | 0.5掀盖胶芯 (H2.0) | LCP UL94V-0 本色 |
| ② | 0.5掀盖端子 (H2.0) | 磷青铜/表面镀锡 |
| ③ | 0.5掀盖后盖 (H2.0) | LCP UL94V-0 黑色 |
| ④ | 0.5掀盖焊片 (H2.0) | 黄铜/表面镀锡 |



适用扁平线

| CKT | DIMA | DIMB | DIMC | CKT | DIMA | DIMB | DIMC |
|-----|-------|-------|-------|-----|-------|-------|-------|
| 4 | 1.50 | 2.60 | 6.40 | 33 | 16.00 | 17.10 | 20.90 |
| 5 | 2.00 | 3.10 | 6.90 | 34 | 16.50 | 17.60 | 21.40 |
| 6 | 2.50 | 3.60 | 7.40 | 35 | 17.00 | 18.10 | 21.90 |
| 7 | 3.00 | 4.10 | 7.90 | 36 | 17.50 | 18.60 | 22.40 |
| 8 | 3.50 | 4.60 | 8.40 | 37 | 18.00 | 19.10 | 22.90 |
| 9 | 4.00 | 5.10 | 8.90 | 38 | 18.50 | 19.60 | 23.40 |
| 10 | 4.50 | 5.60 | 9.40 | 39 | 19.00 | 20.10 | 23.90 |
| 11 | 5.00 | 6.10 | 9.90 | 40 | 19.50 | 20.60 | 24.40 |
| 12 | 5.50 | 6.60 | 10.40 | 41 | 20.00 | 21.10 | 24.90 |
| 13 | 6.00 | 7.10 | 10.90 | 42 | 20.50 | 21.60 | 25.40 |
| 14 | 6.50 | 7.60 | 11.40 | 43 | 21.00 | 22.10 | 25.90 |
| 15 | 7.00 | 8.10 | 11.90 | 44 | 21.50 | 22.60 | 26.40 |
| 16 | 7.50 | 8.60 | 12.40 | 45 | 22.00 | 23.10 | 26.90 |
| 17 | 8.00 | 9.10 | 12.90 | 46 | 22.50 | 23.60 | 27.40 |
| 18 | 8.50 | 9.60 | 13.40 | 47 | 23.00 | 24.10 | 27.90 |
| 19 | 9.00 | 10.10 | 13.90 | 48 | 23.50 | 24.60 | 28.40 |
| 20 | 9.50 | 10.60 | 14.40 | 49 | 24.00 | 25.10 | 28.90 |
| 21 | 10.00 | 11.10 | 14.90 | 50 | 24.50 | 25.60 | 29.40 |
| 22 | 10.50 | 11.60 | 15.40 | 51 | 25.00 | 26.10 | 29.90 |
| 23 | 11.00 | 12.10 | 15.90 | 52 | 25.50 | 26.60 | 30.40 |
| 24 | 11.50 | 12.60 | 16.40 | 53 | 26.00 | 27.10 | 30.90 |
| 25 | 12.00 | 13.10 | 16.90 | 54 | 26.50 | 27.60 | 31.40 |
| 26 | 12.50 | 13.60 | 17.40 | 55 | 27.00 | 28.10 | 31.90 |
| 27 | 13.00 | 14.10 | 17.90 | 56 | 27.50 | 28.60 | 32.40 |
| 28 | 13.50 | 14.60 | 18.40 | 57 | 28.00 | 29.10 | 32.90 |
| 29 | 14.00 | 15.10 | 18.90 | 58 | 28.50 | 29.60 | 33.40 |
| 30 | 14.50 | 15.60 | 19.40 | 59 | 29.00 | 30.10 | 33.90 |
| 31 | 15.00 | 16.10 | 19.90 | 60 | 29.50 | 30.60 | 34.40 |
| 32 | 15.50 | 16.60 | 20.40 | | | | |

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25°C~85°C。
3. 额定电压: 50V, AC/DC(等效)。
4. 接触电阻: ≤0.03Ω。
5. 绝缘电阻: ≥500MΩ

深圳市金航标电子有限公司 WWW.BDS666.COM

KH-FG0.5-H2.0-37PIN 0755-83044319

品名 (TITLE) 0.5 Pitch掀盖卧式下接(H=2.0) 制图 (DR) 王涛

料号 (DWG.NO) 2045-XXXX 校对 (CHKD) 吴鹏

比例 (SCALE) 1:1 单位 (UNITS) mm 审核 (APPD) 黄志明

张数 (SHEET) 1 OF 1 SIZE A4 REV 1

一般公差 (TOLERANCE)
 X ±0.50 XX ±1.0
 X ±0.20 XXX ±0.05
 ANGLES ±1°