


Technical Data  
 Material:  
 Contact material: Phosphor bronze  
 Plating: Gold Flash  
 Insulator material: Black polyester UL94V-0  
 Standard: PA6T+30%G.F



Electrical:  
 Current rating: 1.0amps/contact max.  
 Contact resistance:  $\leq 20m\Omega$ /contact  
 Insulation resistance:  $\geq 1000M\Omega$  at V=100V  
 Withstanding voltage: 300V AC/minute

Mechanical:  
 Soldering temperature: +260°C, 10s max  
 UNSPECIFIED TOLERANCE:  $\pm 0.20$



PCB Layout

A=1.27\* $n$ P+0.4 $\pm$ 0.3  
 B=1.27\* $n$ P-1.27 $\pm$ 0.2  
 Pin Number=2 ~ 50

APPROVALS		DATE	DRAWN		G.M.Chen	2015/5/22	EPCALON 德之隆® ELECTRONICS CO.,LTD		TITLE: CONNECTOR		
CHECKED			APPROVALS				PART NO.		DW127R-11-XX-34		
TOLERANCES ARE		30 $\pm$ 0.15 10 $\pm$ 0.10 5 $\pm$ 0.10	±0.30 ±0.20 ±0.15		ANGLE		UNIT: mm		SCALE: 1:1		
CHANGE.			CHECK.			APPRO.		DRAWING NO.		SHEET 1 OF 1	
ECN NO.		REV.	DATE.		DESCRIPTION.		NEW		PROJ.		