


Technical Data
 Material: Brass
 Contact material: Brass
 Plating: Gold Flash
 Insulator material: Black polyester UL94V-0
 Standard: PBT+30%G. F



Electrical:
 Current rating: 1.5Amps/contact max.
 Contact resistance: $\leq 20m\Omega$ /contact
 Insulation resistance: $\geq 1000M\Omega$ at V=100V
 Withstanding voltage: 450V AC/minute
 Mechanical:
 Soldering temperature: +220°C, 4s max
 UNSPECIFIED TOLERANCE: ± 0.20



PCB Layout

A=2.0*0*NP ± 0.40
 B=2.0*0*NP-2.0 ± 0.20
 Pin Number=1~40

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2015/7/17	D2200R-11-XX-39	
CHECKED			ELECTRONICS CO.,LTD	
APPROVALS			CONNECTOR	
TOLERANCES ARE		30 ± 0.15	± 0.30	ANGLE
		10 ± 0.10	± 0.20	UNIT: mm
		5 ± 0.10	± 0.15	SCALE: 1:1
				SHEET 1 OF 1
ECN NO.	REV.	DATE.	DESCRIPTION.	PROJ.
	A		NEW	