


Technical Data
 Material: Brass
 Contact material: Brass
 Plating: Gold Flash
 Insulator material: Black polyester UJ94V-0
 Standard: PBT+30%GF

Electrical:
 Current rating: 3Amps/contact max.
 Contact resistance: $\leq 20m\Omega$ /contact
 Insulation resistance: $\leq 1000M\Omega$ at V=100V
 Withstanding voltage: 550V AC/minute

Mechanical:
 Soldering temperature: +220°C, 4s max

UNSPECIFIED TOLERANCE: ± 0.20



PCB Layout

A=2.54*P ± 0.50
 B=2.54*nP-2.54 ± 0.20
 Pin Number=1~40

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2015/7/17	D2254R-11-XX-63	
CHECKED			ELECTRONICS CO.,LTD	
APPROVALS			CONNECTOR	
TOLERANCES ARE		ANGLE	UNIT: mm	SCALE: 1:1
30 ^{max} ±0.1	±0.30	±2°		SHEET 1 OF 1
10 ^{max} ±0.1	±0.20			PROJ.
5 ^{max} ±0.1	±0.15			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.
	A		NEW	