





环保物料

TEL:0769-82001899



P.C.B Hole Layout

SPECIFICATIONS

Insulator Material: Polyester(UL94V-0)
 Current Rating: 1AMP
 Contact Resistance: 20MΩ Max
 Insulation Resistance: 500mΩ min
 Withstanding Voltage: AC 300V
 Contact Material: Phosphor Copper
 Standard : Nylon-6T
 Contact Plating: Gold/Tin Over Nickel
 Operating Temperature: -40° C+105° C
 Max.Processing Temp : 240° C for30-60seconds
 (260° C for10seconds)

TOLERANCE UNLESS OTHERWISE

X.	±0.30	X°	±5°
.X	±0.20	.X°	±2°
.XX	±0.08	.XX°	±1°
.XXX	±0.03	.XXX°	±0.5°

DRAWN CK tan

CHKD

APPD

VIEW

XFCN 兴飞连接器有限公司
 XFCN CONNECTORS CO.,LTD.

PRODUCT NAME 1.27mm Female Header Connectors

PART. NO. PM127VS-W-F-12-xx-H43

SHEET 1/1

DATE 2020.04.12

UNITS mm

SCALE 1:1

DWG. NO. 009

AO

VER

MODIFICATION

DRAW

DATE

1 2 3 4 5 6 7 8 9 10