



截面 B-B

Specifications:

规格:

- Voltage rating: 250V AC/DC
- 额定电压: 250V AC/DC
- Current rating: 3A AC/DC
- 额定电流: 3A AC/DC
- Withstanding voltage: 1000V AC/minute
- 耐受电压: 1000V AC/分钟
- Temperature range: -25°C ~ +85°C
- 温度范围: -25°C ~ +85°C
- Insulation resistance: ≥1000MΩ
- 绝缘电阻: ≥1000MΩ
- Contact resistance: ≤10mΩ
- 接触电阻: ≤10mΩ
- After environmental testing: ≤20mΩ
- 环境测试后: ≤20兆欧

Poles	Dimension(mm)			
	A	B	C	D
10	12.00	8.00	10.60	5.10
12	14.00	10.00	12.60	6.80
14	16.00	12.00	14.60	6.80
16	18.00	14.00	16.60	6.80
18	20.00	16.00	18.60	6.80
20	22.00	18.00	20.60	6.80
22	24.00	20.00	22.60	6.80
24	26.00	22.00	24.60	6.80
26	28.00	24.00	26.60	6.80
28	30.00	26.00	28.60	6.80
30	32.00	28.00	30.60	6.80
32	34.00	30.00	32.60	6.80
34	36.00	32.00	34.60	6.80
36	38.00	34.00	36.60	6.80
38	40.00	36.00	38.60	6.80
40	42.00	38.00	40.60	6.80

X2026 H X- 2xXX HF-N0 XX

① ②③ ④ ⑤ ⑥ ⑦

1. Series No
2. Category: H-HSG
3. Appearance type: Blank-Ordinary
4. Row No-Pin No: 2xXX-2x02P~2x22P
5. Plug the Pin&special No:
HF-Halogen Free
6. Material: NO-PA66 94V-0
7. Color: Blank-Natural Color
BK-Black

X2008H-2xXX-N0	Nylon 66 UL 94V-0	X2008W	X2008T
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm/in	2.00mm Crimp Style Connectors
APPD		DATE		SIZE: A4	DWG NO.:
					X2081H-2xXX-N0
			KXB INDUSTRIAL PRECISION CO., LIMITED		WEIGHT
					1.0g
					SHEET
					1/1
					REVISION
					A0

					units: mm
ΔX					tolerance:
ΔX					X.X ±0.2mm
ΔX					X.XX ±0.1mm
MARK	DESCRIPTION	DATE	REVISED	APPROVED	X.XXX ±0.05mm
REVISIONS					
UNSPECIFIED TOLERANCES					
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn					