



Technical Data

Material

Contact Material: Brass/Phosphor Bronze
 Contact plating: Nicker/Gold Flash
 Insulator Material: Black Polyester UL94V-0
 Standard: PBT+30%G F

Electrical

Current rating: 3.0Amps/contact max
 Contact resistance: $\leq 20\text{m}\Omega$ / contact
 Insulation resistance: $\geq 1000\text{M}\Omega$ at $V=100\text{V}$
 Withstanding Voltage: 1000V AC/minute

Mechanical

Operaing temperature: -40 C to+105C

X2540-B 1 X X

HOUSING COLOR:
 B:BLACK BL:BLUE Y:YELLOW
 W:WHITE GR:GREEN R:RED

CONTACT PLATING:
 GF:FULL GOLD FLASH
 NI:NICKEL
 GN:GOLD+NICKEL

HEIGHT:
 0:6mm
 1:6.5mm

HOUSING TYPE:
 A:OPEN B:CLOSE C:LONG

REVISIONS						UNSPECIFIED TOLERANCES		DSND	DATE	SCALE: N/A	MODEL TYPE:		
					ANGLAR	$\pm 5^\circ$					2.54 CONN		
ΔX					$L \leq 4$	± 0.2		DWN	DATE	VIEW:	PART NO.:		
ΔX					$4 < L \leq 16$	± 0.3		CHKD	DATE	UNIT: mm/in	DWG NO.:		
ΔX					$16 < L \leq 63$	± 0.4		APPD	DATE	SIZE: A4	X2540-B1XX		
MARK	DESCRIPTION	DATE	REVISED	APPROVED	$L > 63$	± 0.5							
								XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn											1.0g	1/1	A0