



P.C.B LAYOUT  
TOP VIEW



Rating: 0.5A 30V DC  
 Contact Resistance: 100 mΩ Max.  
 Operating temperature: -20℃~70℃  
 Operating force: 3~20N  
 Operating Life: 5,000cycles

PIN	φ200	φ250
APPD.		

ITEM	PART NAME	QTY.	MATERIAL	FINISHING
⑥	PIN	1	BRASS	Ni-Plating
⑤	FLAT FOOT	1	BRASS	Sn-Plating
④	COVER PIECE	1	BRASS	Sn-Plating
③	SPRING PIECE	1	BRONZE	Sn-Plating
②	COVER	1	PBT	
①	HOUSING	1	PBT	

APPROVALS		DATE
DRAWN	G.M.Chen	2018/3/15
CHECKED		
APPROVALS		

PART NO.		DC-DD005B-XXX	
TITLE:		DC JACK	
DRAWING NO.			
SCALE:		1:1	
SHEET		1 OF 1	
PROJECT			

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			