




Rating: 0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3~20N
 Operating Life:5,000cycles



PIN	①	②	③
APPD.	∅1.65	∅2.0	∅2.5



SCHEMATIC

ITEM	PART NAME	QTY.	MATERIAL	FINISHING
⑦	COVER	1	SUS301	Ni-Plating
⑥	CONTACT FOOT	1	BRONZE	Ag-Plating
⑤	PIN	1	H59 BRASS	Ni-Plating
④	CONTACT FOOT	1	BRASS	Ag-Plating
③	CURVER PIECE	1	BRASS	Ag-Plating
②	SPRING PIECE	1	SUS301	Ag-Plating
①	HOUSING	1	PA9T	

APPROVALS	DATE
DRAWN G.M.Chen	2018/3/15
CHECKED	
APPROVALS	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	30±0.15 10±0.10 5±0.05	±0.30 ±0.20 ±0.15	ANGLE	±2°	PART NO.	DC-DD044A-XXX	SHEET	1 OF 1
	A		NEW												

P.C.B LAYOUT
TOP VIEW

DEALON 德之隆
ELECTRONICS CO.,LTD