



Rating:7A 20V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles

ITEM	PART NAME	QTY.	MATERIAL	FINISHING
⑥	round	1	SUS	Natural
⑤	Shielding	1	Brass	Ag-Plated
④	PIN	1	Brass	Au-Plated
③	Terminal	1	SUS	Ni-Plated
②	Tip Spring	1	Copper alloy	Ni-Plated
①	Body	1	Pd9t	Black

APPROVALS		DATE	TITLE:
DRAWN	G.M.Chen	2015/3/20	DC JACKS
CHECKED			
APPROVALS			

DEALON 德之隆
 ELECTRONICS CO.,LTD

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	ANGLE	UNIT:	SCALE:	SHEET	PROJ.
	A		NEW				30~0.1± 10~0.30 5~0.10 ~5	±2°	mm	1:1	1 OF 1	