



Technical Data  
 Material:  
 Contact material: Phosphor bronze  
 Plating: Gold Flash  
 Insulator material: Black polyester UL94V-0  
 Standard: 6T+30%G, F

Electrical:  
 Current rating: 1.5amps/contact max.  
 Contact resistance:  $\leq 20m\Omega$  /contact  
 Insulation resistance:  $\leq 1000M\Omega$  at V=100V  
 Withstanding voltage: 450V AC/minute

Mechanical:  
 Soldering temperature: +260°C, 4s max  
 UNSPECIFIED TOLERANCE:  $\pm 0.20$



PCB Layout

A=2.00\* $\pi$ P+0.4 $\pm$ 0.3  
 B=2.00\* $\pi$ P-0.2 $\pm$ 0.2

APPROVALS		DATE	DRAWING NO.		SHEET
DRAWN	G.M.Chen	2015/7/17	DW200R-11-XX-43		1 OF 1
CHECKED			CONNECTOR		
APPROVALS			PART NO.		
			UNIT: mm		
			SCALE: 1:1		
			DRAWING NO.		
			PROJ.		
ECN NO.	REV.	DATE.	DESCRIPTION.		
	A		NEW		
			CHANGE.		
			CHECK.		
			APPRO.		
			TOLERANCES ARE		
			30 $\pm$ 0.15	±0.30	ANGLE
			10 $\pm$ 0.10	±0.20	
			5 $\pm$ 0.10	±0.15	±2°
			~5	±0.10	

DEALON 德之隆  
 ELECTRONICS CO.,LTD