

Technical Data

Material: Brass
 Contact material: Brass
 Plating: Gold Flash
 Insulator material: Black polyester UL94V-0
 Standard: PBT+30%G.F



Electrical:

Current rating: 3Amps/contact max.
 Contact resistance: ≤20mΩ/contact
 Insulation resistance: ≥1000MΩ at V=100V
 Withstanding voltage: 550V AC/minute

Mechanical:

Soldering temperature: +220°C, 4s max

UNSPECIFIED TOLERANCE: ±0.20



PCB Layout

A=2.54*nP±0.50

B=2.54*nP-2.54±0.20

Pin Number=1~40

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2015/7/17	D/2254W-11-XX-65	
CHECKED			ELECTRONICS CO.,LTD	
APPROVALS			CONNECTOR	
TOLERANCES ARE		ANGLE	PART NO.	SHEET 1 OF 1
30 ^{±0.15}	±0.30	±2°	D/2254W-11-XX-65	PROJ.
10 ^{±0.10}	±0.20			
5 ^{±0.10}	±0.15			
ECN NO.	REV.	DATE.	DESCRIPTION.	
	A		NEW	