







修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
AO		NEW RELEASE	黄艳兰	2021-04-12



3D VIEW




PIN数	A±0.1	B±0.1	C±0.1
2P	8.00	4.70	2.00
3P	10.00	6.70	4.00
4P	12.00	8.70	6.00
5P	14.00	10.70	8.00
6P	16.00	12.70	10.00
7P	18.00	14.70	12.00
8P	20.00	16.70	14.00
9P	22.00	18.70	16.00
10P	24.00	20.70	18.00



序号	品名	材质	电镀/颜色	备注
C	插片	黄铜	镀镍锡	
B	插针	黄铜	镀镍锡	
A	基座	LCP	本色	

- Specifications:
- 1.Rated Voltage : 250V AC/DC
  - 2.Rated Current : 5A AC,DC
  - 3.Withstand Voltage : 1000V AC/minute
  - 4.Contact Resistance : 50mΩ(MAX.)
  - 5.Insulation Resistance : 1000MΩ(MIN.)
  - 6.Storage Temperature Range:-40°C~+85°C;
  - 7.Operation Temperature Range:-25°C~+70°C;



## 深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD  
TEL : 0755-27129737 FAX : 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: 产品名称: PH2.0针座卧贴	
X.X	±0.30	X.X°	±3°	APPD: 核准: 谢亮	PART NO: 产品编号: HDGC2001WR-S-XP
X.XX	±0.30	X.XX°	±2°	CHECK: 校对: 王建业	DATE
X.XXX	±0.10	X.XXX°	±1°	DRAW: 绘图: 黄艳兰	SCALE
					UNIT
					CODE NUMBER