


2.54mm (0.1") PIN HEADER DUAL ROW STRAIGHT H=2.54

MATERIALS

Insulator :PA6T+30%GlassFiber, (UL94V-0)
 Contact :Brass
 Contact Plating :Gold/Tin over Nickel

SPECIFICATONS

Current Rating :3A
 Operation Temperature :-40°C to +105°C
 Insulation Resistance :1000MΩ Min at DC 500V
 contact resistance :20MΩ Max at DC 1A



Ordering Information



PH2.54 × H-2 × nP-x/x-xx-xx

Packing: 1=Bag 2=Box
 Contact Plating:

G.4	0.4U" Gold Flash	G05	5U" Gold Flash
G.8	0.8U" Gold Flash	G10	10U" Gold Flash
G01	1U" Gold Flash	G15	15U" Gold Flash
G02	2U" Gold Flash	G30	50U" Gold Flash
G03	3U" Gold Flash	S50	50U" Sn Flash

Pin Length: X/X=C/D
 Total Rows: n=01~40

H=2.5



PCB LAYOUT

3*4P 对应惟赞编码: 01.5.5.1.304.03

Insulator Material	
PBT	OK
PA6T	
LCP	

深圳市惟赞电子有限公司

SHENZHEN REALRUN ELECTRONIC CO., LTD.

PRODUCT NAME: 2.54 PIN HEADER		DWG NO.:		SCALE:		FIT	
		VER: 02		UNIT: mm		SHEET: 1/1	
SPECIFICATION: PH2.54*2.5-3*nP		CHECKED BY: 白文星		DRAWN BY: Mikel		DATE: 2010.3.17	
		ECN:					