



XKB Connectivity

MATERIAL 材料:

HOUSING 外壳: PBT,UL94V-0,BLACK.

TERMINAL 端子: PHOSPHOR BRONZE ,Ø=0.46MM,
GOLD PLATING ON CONTACT AREA.

MECHANICAL 机械:

DURABILITY 耐用性: 750 CYCLES MIN.12.5MM/MINUTE

INSERTION FORCE 插入力: 2.2KG.F MAX

RETENTION STRENGTH 固位力:7.7KG.F BETWEEN JACK AND PLUG

OPERATING TEMPERATURE 工作温度: -40°C~+85°C.

STORAGE TEMPERATURE 储存温度: -40°C~+85°C.

ALL CRITICAL DIMENSIONS WITH ***

ELECTRICAL 电动:

VOLTAGE 电压:125 VOLTS AC

CURRENT RATING 额定电流:1.5AMP

DIELECTRIC STRENGTH 介电强度:1000 VAC RMS 50HZ OR 60HZ,1MIN

INSULATION RESISTANCE 绝缘电阻:500 MEGA OHMS MIN.INITIAL

AFTER 500V DC FOR 1 MINUTE

CONTACT RESISTANCE 接触电阻:SINGLE TERMINAL 30 MILLIOHMS MAX

INITIAL 50 MILLIOHMS MAX.AFTER

DURABILITY TEST

							DSND		DATE		SCALE: N/A	MODEL TYPE: RJ JACK
							DWN		DATE		VIEW:	PART NO.:
							CHKD		DATE		UNIT: mm/in	DWG NO.:
							APPD		DATE		SIZE: A4	X08ADIWA1DY1017
REVISIONS							UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED			
MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°	WEIGHT	SHEET	REVISION			
Δx					L ≤ 4	±0.2	1.0g	1/1	A0			
Δx					4 < L ≤ 16	±0.3						
Δx					16 < L ≤ 63	±0.4						
					L > 63	±0.5						
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn												