

备注 NOTES:

1.材质 Material:



- 1.1胶芯 Plastic core: LCP+30%G.F
- 1.2端子 Terminal: C7025, T=0.15mm; Nickel base,gold plated
- 1.3外壳 shell: SUS, T=0.30mm; Nickel plated on the surface
- 1.4卡片 shell fragment: SUS, T=0.15mm;

2.电气特性 ELECTRICAL CHARACTERISTIC:

- 2.1额定电流 Rated current: 3A
- 2.2接触阻抗 Contact resistance: 40mΩ MAX
- 2.3绝缘阻抗 Insulation resistance: 100MΩ MIN 250V DC
- 2.4耐压 WITHSTANDING VOLTAGE: 100V AC
- 2.5沾锡性: 温度245±5℃, 时间5±0.5s
- 2.6插入力 INSERTION FORCE: 2.0kgf MAX
拔出力 EXTRACTION FORCE:0.6kgf MIN
- 2.7使用寿命 Service life: 5000次
- 2.8工作温度 Operating temperature: -25℃~+80℃

PIN ASSIGNMENT:

Pin No.	Signal Name	Pin No.	Signal Name
A1	GND	B12	GND
A2		B11	
A3		B10	
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	D+	B7	D-
A7	D-	B6	D+
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10		B3	
A11		B2	
A12	GND	B1	GND



RECOMMENDED P.C.B LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

U262-16XN-4BSS73-T

- 1: Au 10μ
- 2: Au 50μ
- 3: Au 10μ
- 6: Au 30μ
- W: WHITE
- B: BLACK
- 1: PBT
- 2: PA6T
- 3: PA9T
- 4: LCP

REVISIONS					ANGLAR	±5°	DSND	DATE	SCALE: N/A	MODEL TYPE:		
ΔX					L ≤ 4	±0.2	DWN	DATE	VIEW:	3.1 TYPE C		
ΔX					4 < L ≤ 16	±0.3	CHKD	DATE	UNIT: mm/in	PART NO.:		
ΔX					16 < L ≤ 63	±0.4	APPD	DATE	SIZE: A4	DWG NO.:		
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5				U262-16XN-4BSS73-T		
					UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn										1.0g	1/1	A0