



Specification

Operating Life	200,000 cycles
Operating Force	F
Maximum Voltage	12 VDC
Max Current	50 mA
Dielectric Strength	250 V AC(1mm)
Contact Resistance	<100 mΩ
Insulation Resistance	>100M Ω
Bounce Time	<5 ms
Storage Temperature	-30° C to 85° C

F(force)

NO.	Force
M	180gf±50
K	250gf±50

H(height)

NO.	Height	X. ±0.50	X.° ±2°	UNITS	
43	4.3mm	.X ±0.30	.X° ±1°	mm	
43P	4.3mm with pgs	.XX ±0.10	.XX° ±0.5°	MAT'L	
73	7.3mm	.XXX ±0.05			
73P	7.3mm with pgs	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD			
85	8.5mm				FINISH
85P	8.5mm with pgs				Q'TY
12	12mm				

	深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO., LTD							
	PART NO. YTS125SXXX	TITLE: TACTILE SWITCH						
APPD: ROGER	DWG NO.: YTS125SXXX							
CHKD: ROC								
DR: BILLY WANG 2020/08/21	<table border="1"> <tr> <td>SCALE</td> <td>SHEET</td> <td>REV.</td> </tr> <tr> <td>1/1</td> <td>1/1</td> <td>A1</td> </tr> </table>		SCALE	SHEET	REV.	1/1	1/1	A1
SCALE	SHEET	REV.						
1/1	1/1	A1						