SD103AX

SD103AX Schottky Barrier Diode

General description

Schottky Barrier Diode in a SOD-523 Plastic Package.

FEATURES


- Low Forward Voltage Drop
- Guard Ring Construction for Transient Protection
- Negligible Reverse Recovery Time
- Low Capacitance

APPLICATION

- Polarity Protection Diode
- Re-Circulating Diode
- Switching Diode

MECHANICAL DATA

Case: SOD-523



Absolute Maximum Ratings(Ta=25°C)

Parameter	Symbol	Value	Unit	
Peak Repetitive Reverse Voltage	VRRM 40		V	
Reverse Voltage	VR	40	V	
Average Forward Rectified Current	IF(AV)	350	mA	
Non-Repetitive Peak Forward Surge Current at t = 1 s	IFSM	2	A	
Power Dissipation	Ptot	150	mW	
Operating and Storage Temperature Range	Tj, Tstg	- 65 to + 125	OC	
Thermal Resistance, Junction to Ambient Air	R0JA	667	°C/W	


Parameter		Symbol	Min.	Тур.	Max.	Unit
Reverse Breakdown Voltage at IR =100uA		V(BR)R	40			V
Reverse Leakage Current at VR =30V		IR			5	μA
Forward Voltage	at IF = 20 mA	VF			0.37	v
	at IF = 200 mA				0.6	
Total Capacitance at VR = 0 V, f = 1 MHz		СТ		50		pF
Reverse Recovery Time at IF = IR = 200 mA, Irr = 0.1 IR, RL = 100 Ω		trr		10		ns





SD103AX


Electrical Characteristic Curve





Package Dimensions: SOD-523

Plastic surface mounted package; 2 leads





Important Notice and Disclaimer

DOESHARE has used reasonable care in preparing the information included in this document, but DOESHARE does not warrant that such information is error free. DOESHARE assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.

DOESHARE no warranty, representation or guarantee regarding the documents, circuits and products specification, DOESHARE reservation rights to make changes for any documents, products, circuits and specifications at any time without notice.

Purchasers are solely responsible for the choice, selection and use of the DOESHARE products and services described herein, and DOESHARE assumes no liability whatsoever relating to the choice, selection or use of the products and services described herein.

No license, express or implied, by implication or otherwise under any intellectual property rights of DOESHARE.

Resale of DOESHARE products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by DOESHARE for the DOESHARE product or service described herein and shall not create or extend in any manner whatsoever, any liability of DOESHARE.