




PRODUCT NO.
61729-*




TYPE"1" FULL BACK



TYPE"2" PARTIAL BACK



TYPE"3" PARTIAL BACK WITH SHORT SOLDER TAIL AND SHELL TAIL FOR PIP PROCESS 61729-XXXQXLF



PRODUCT NUMBER CODE:

61729 - X X X X X P S LF

BASE PRODUCT NUMBER

HOUSING COLOR OPTION

0 - WHITE
1 - BLACK

HALOGEN OPTION

0 - WITH HALOGEN
1 - HF (HALOGEN FREE)

SHIELD OPTION

1 - FULL BACK
2 - PARTIAL BACK

3 - FULL BACK (SPECIAL PLATING IN ONLY)
S - FULL BACK (SPECIAL MATERIAL FOR 12,000 DURABILITY CYCLES)

P - PARTIAL BACK (SPECIAL MATERIAL FOR 12,000 DURABILITY CYCLES)

Q - PARTIAL BACK WITH SHORT TAIL FOR TYPE 3

TERMINAL PLATING OPTION

0 - 50u" NI UNDERPLATED
30u" GXT CONTACT AREA
100u" PURE TIN TAIL AREA

1 - 50u" NI UNDERPLATED
30u" GOLD OR 30u" GXT CONTACT AREA
100u" PURE TIN TAIL AREA

2 - 50u" NI UNDERPLATED
GOLD FLASH CONTACT AREA
100u" PURE TIN TAIL AREA

3 - 50u" NI UNDERPLATED
30u" GOLD CONTACT AREA
100u" PURE TIN TAIL AREA

PACKAGING OPTION

B - TUBES
R - TAPE & REEL

DATE CODE OPTION

P - WITH DATE CODE
DEFAULT: WITHOUT DATE CODE

ONLY FOR PANSONIC

LEAD FREE OPTION

mat'l. code	ecn no	dr	date	surface	tolerance	projection	product family
S N05-0242	PH	08/22/05	08/22/05	ISO 1302	ISO 406	ISO 1108	HPL 511 USB2.0
T N06-0103	HB	04/15/06	04/15/06	tolerances unless otherwise specified		mm	USB RECEPTACLE B TYPE
U N08-0238	RB	11/03/08	0±.2	linear	0.00±0.20	mm	
V N08-0246	RB	12/08/08	dr	Yuan-Yuan B00	0.0000±0.10	scale 1:1	dwg no
W ER-N-16533	LQ	12/17/13	eng	Yuan-Yuan B00			61729
X ER-N-29556	LZ	03/09/18	chr	Tim.Yao			sheet 1 of 2 size
Y ER-N-32780	YY	02/26/19	ppp	Tim.Yao			A3
sheet revision							type
index	sheet						Product Customer Drawing

