







REV	ECN	CONTENT	CHECK	DATE
V0.0		初版发行	YZG	2017.03.12
V1.0		整理图纸	WL	2019.09.25



- 技术要求:
- 额定电流:  
25mA, 24VDC (开与关切换时)  
100mA, 50VDC (开与关不切换时)
  - 接触阻抗:  
≤50mΩ (初始), ≤100mΩ (寿命测试后)
  - 绝缘电阻: ≥100MΩ / 500VDC
  - 耐电压: 500VAC / 1minute
  - 拨动力: 1000g max
  - 拨动行程: 0.9mm
  - 机械寿命: ≥2000 cycles
  - 电气寿命: ≥2000 cycles / 25mA, 24VDC
  - 使用温度: -40℃ ~ +85℃
  - 存储温度: -40℃ ~ +85℃
  - 符合RoHS要求

焊接说明:  
回流焊接: 240℃, 20S max, 峰值温度260℃  
手工焊接: 30W电烙铁, 320±5℃, 3S max  
焊接前保持开关在“OFF”状态

订购方式  
KF1027 B - XXP - X XX - XXX-XXX  
B: SMD Type  
产品型号 (贴片式)  
P数  
客户要求  
00: 无需贴膜, 管装  
TR: 正面贴膜, 载带包装  
G: 带预按钮, 高的  
L: 平按钮, 低的



General tolerance in mm		radii and chamfers		shorter angle side		— //	
over	over	over	over	over	over	over	over
0	3	6	30	120	400	1000	
±0.15	±0.2	±0.25	±0.3	±0.5	±0.8	±1.0	

Poles	Dim P	Dim L
1P	—	3.54
2P	2.54	6.08
3P	5.08	8.62
4P	7.62	11.16
5P	10.16	13.70
6P	12.70	16.24
7P	15.24	18.78
8P	17.78	21.32
9P	20.32	23.86
10P	22.86	26.40
11P	25.40	28.94
12P	27.94	31.48

序号	零件名称	零件编码	数量	材质	备注
1	盖板		1	工程塑料	UL94V-0
2	拨柄		P	工程塑料	UL94V-0
3	弹片		P	铜合金	镀金
4	PIN针		2P	铜合金	镀金
5	底座		1	工程塑料	UL94V-0
6	高温薄膜		1	POLYIMIDE	黄色, 选配

APP.	DATE	NAME	W20004321
CHK.	2019.9.25		
DWG.	2019.9.25		
UN			
S			
MM			
SHEET	1/1	PROJECTION-METHOD	



凯峰电子有限公司  
KAIFENG ELECTRONICS CO., LTD