


NOTES:

- Current Rating: 1AMP
- Contact Resistance: 20mΩ max
- Withstand Voltage: 500V AC/DC
- Insulation Resistance: 1000MΩ min
- Operation Temperature: -40°C to +105°C
- Contact Material: Brass
- Contact plating: Au or Sn Over Ni
- Insulator Material: PA9T+30%GF(UL94V-0)

Ordering Information

3130-XX M XX BK00 X 1

- | | | | |
|-------------|-------------------|-----------------|-----------------|
| No. of Pins | Contact Plating | Color Insulator | Packaging |
| 10 34 | G0=Gold Flash | B=Black | A=Tray |
| 14 40 | G1=3μr Gold | U=Blue | T=Tube |
| 16 44 | G2=5μr Gold | W=White | P=Tube+CAP |
| 20 50 | G3=10μr Gold | | R=Tube&Reel+CAP |
| 24 60 | G4=15μr Gold | | |
| 26 64 | G5=30μr Gold | | |
| 30 80 | S0=Gold Flash/Tin | | |
| 32 100 | S1=3μr Gold/Tin | | |
| | S2=5μr Gold/Tin | | |
| | S3=10μr Gold/Tin | | |
| | S4=15μr Gold/Tin | | |
| | S5=30μr Gold/Tin | | |
| | SN=Tin | | |



SECTION A-A

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	FIT	PART NO.	TITLE:	WCON-Dongguan	WCON-Kunshan
A2	2012/08/30	Modify CAP		XX	TsingSn	2012/08/30	mm		3130-XXMXXBK00X1	1.27 BOX HEADER SMT H=4.90	Http: www.wcon.com	
A1	2010/09/30	Change drawing		XXX	CHECK	DATE	inch	A4			Tel: +86 769 85358920	Tel: +86 512 57468408
A0	2008/04/25	NEW		XXXX	APPROVE	DATE	SHEET	1/1			Fax: +86 769 85358915	Fax: +86 512 57468468
				Angle			PROJ.		Customer NO.		E-mail: sales@wcon.com	E-mail: sales@wcon.com
				± 3'								



WCON-Dongguan
Tel: +86 769 85358920
Fax: +86 769 85358915
E-mail: sales@wcon.com

WCON-Kunshan
Tel: +86 512 57468408
Fax: +86 512 57468468
E-mail: sales@wcon.com