



SEVEN-PORT MANAGED 10/100 ROBOSWITCH™

FEATURES

- **Highly integrated, 65 nm process, seven-port 10/100 Switch integrating:**
 - Five 10/100 MACs with five integrated 10/100 PHYs
 - One 10/100 MAC with MII/RvMII/RMII interface
 - One 10/100/1000 MAC with RGMII/MII/RvMII/RMII interface
- **Performance**
 - 2K MAC
 - 2 KB max frame size
- **Virtual Local-Area Network (VLAN)**
 - 4K-entry port-based and 802.1Q VLAN (full 4K range)
 - VLAN based rate limiting
- **Quality of Service (QoS)**
 - 4 CoS queues – Port, 802.1p, and DiffServ
- **Security**
 - IEEE 802.1x support for secure user authentication
- **BroadSync™ HD**
 - Supports IEEE 802.1 Audio Video Bridging (AVB) draft standard
- **Traffic control and network resiliency**
 - Ingress rate limiting and egress rate shaping
 - Spanning Tree Protocol/Rapid Spanning Tree Protocol/Multiple Spanning Tree Protocol
 - Port mirroring
 - Full MIB counter set supported
 - IPv4 IGMP/IPv6 MLD snooping
 - Redirect reserved multicast MAC addresses to CPU
- **Low-Power Consumption**
 - Less than 0.7W full power
 - Green features including auto power down, sleep, and deep sleep modes
- **Technology and physical specifications**
 - State-of-the-art 65 nm LP, 6-layer metal technology
 - 1.2V core and 2.5V/3.3V I/O

SUMMARY OF BENEFITS

- Enables next-generation six Fast Ethernet + one Gigabit Ethernet switches with enhanced L2+ features
- High level of integration provides for cost-effective designs
- Utilizes field-proven 10BASE-T/100BASE-TX Fast Ethernet transceivers, lowering overall system interoperability and reliability risks.

VLAN feature insures proper layer-2 isolation and security
- Highly flexible 4K-entry VLAN implementation with support for full 4K range
- 802.1Q-based VLAN and flexible priority queues mapped to selectable protocols such as 802.1p, DiffServ, and COS enable the switch to be designed into a variety of applications for multimedia and data traffic.
- 802.1x port and MAC-based network security to keep the network running efficiently


Enables multicast switching with IGMP and MLD snooping without expensive L3 multicast routing

BroadSync™ HD enabled for guaranteed QoS and bandwidth, latency, and time-sync for audio/visual traffic between networked electronic devices
- WAN port allows for one of the ports to be specified for WAN connectivity
- Significant power savings with innovative green modes and 65 nm LP process technology

BCM53101 Applications



OVERVIEW



BCM53101 Block Diagram

Optimized for L2 switching, the BCM53101 is a feature-enhanced seven-port switch to the industry-leading BCM5325E RoboSwitch™. This device combines all the functions of a high-speed switch system, including packet buffers, PHY transceivers, MACs, address management, and a non-blocking switch fabric, into a 65 nm LP process.

The BCM53101 contains five full-duplex 10BASE-T/100BASE-TX Fast Ethernet transceivers connected to the five on-chip 10/100 MACs. In addition, a sixth 10/100 MAC is available through the MII/RvMII interface. The BCM53101 also features a 10/100/1000 MAC, which can be used to connect to an external CPU via the RGMII/MII/RvMII interface.

The BCM53101 also integrates several gigabit-class features such as 4K-entry VLAN, 2K-entry MAC addresses, ingress rate limiting and egress rate shaping, port mirroring, IGMP/MLD snooping, and trap reserved MAC addresses to CPU, among others.

The BCM53101 is designed from the ground up for lower power consumption. The power-efficient on-chip PHYs help lower power consumption by over 50% compared to its predecessor, the BCM5325E. Fabricated using 65 nm LP process, the device consumes less than 0.7W. Additionally, the BCM53101 incorporates several green modes such as auto-power down, sleep mode, and a deep sleep mode (needs external CPU).

Broadcom®, the pulse logo, Connecting everything®, and the Connecting everything logo are among the trademarks of Broadcom Corporation and/or its affiliates in the United States, certain other countries and/or the EU. Any other trademarks or trade names mentioned are the property of their respective owners.

Connecting
everything®



BROADCOM CORPORATION

5300 California Avenue
Irvine, California 92617

© 2009 by BROADCOM CORPORATION. All rights reserved.

53101-PB00-R 04/06/09

Phone: 949-926-5000
Fax: 949-926-5203
E-mail: info@broadcom.com
Web: www.broadcom.com