



Recommended PCB Layout

Specifications:

规格:

Voltage rating:250V AC/Min

额定电压: 250V AC/Min

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

X1270 W R -2xXX A -6T V01

① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-WAFER
- 3.Wedding Board Angle:R-Right 90°
- 4.Row No-Pin No:2xXX-2x05P~2x30P
- 5.A:No gap
- 6.Material:6T:PA6T UL94V-0
- 7.Plating Category: V01-All Gold Flash

PIN	A	B	C
10	5.08	11.25	12.65
14	7.62	13.79	15.19
16	8.89	15.06	16.46
20	11.43	17.60	19.00
26	15.24	21.41	22.81
30	17.78	23.95	25.35
34	20.32	26.49	27.89
40	24.13	30.30	31.70
50	30.48	36.65	38.05
60	36.83	43.00	44.40

X1270WR-2xXXA-6TV01	PA6T UL 94V-0	Brass	Gold Flash	X1270H
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)	Suitable XKB Housing

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	DSND	SCALE: N/A	MODEL TYPE: 1.27mm BTB Style Connectors
					ANGLAR ±5°			
ΔX					L ≤ 4 ±0.2	DWN	VIEW:	PART NO.:
ΔX					4 < L ≤ 16 ±0.3	CHKD	UNIT: mm/in	DWG NO.:
ΔX					16 < L ≤ 63 ±0.4	APPD	SIZE: A4	X1270WR-2xXXA-6TV01
					L > 63 ±0.5			WEIGHT
								SHEET
								REVISION
								1/1
								A0

