



8	绝缘盖	纸胶板	1																	
7	右长针	BRASS	1	SN-PLATED																
6	左长针	BRASS	1	SN-PLATED																
5	左短针	BRASS	1	SN-PLATED																
4	小直针	BRASS	1	SN-PLATED																
3	右短针	BRASS	1	SN-PLATED																
2	面板	BRASS	1	SN-PLATED																
1	底座	PBT	1																	

TOLERANCE		UNLESS SPECIFIED													
UP TO 5mm: ±0.1		ANGULAR		1		NO		DATE		UNIT : MM		ROHS COMPLIANT		REVISIONS	
ABOVE 5mm: ±0.2		±1°								SCALE: 1:1				BY APPD	
TITLE: DIN SOCKET														DWN	
MODEL: DIN-504A-M10														CHK'D	
														APPD	
														PRO.AGI.	
														REV :A0	