




SCHEMATIC



| | | | | | | | | | | | |
|-----|----------------|-----------------|-----------|-----|-----------|----------------------------|-------------|------------|----------------|----------|---------|
| NO. | PART | NAME | MATERIAL | QTY | FINISHING | TOLERANCE UNLESS SPECIFIED | | REVISIONS | | PRO.AGL: | REV: A0 |
| | | | | | | UP TO 5mm: ±0.1 | ANGULAR ±1° | NO | DATE | | |
| | | | | | | ABOVE 5mm: ±0.2 | | 1 | | | |
| 4 | 3#CONTACT FOOT | PHOSPHOR BRONZE | Ag-PLATED | 1 | | TITLE: PHONE JACK | | UNIT: MM | | | |
| 3 | 2#CONTACT FOOT | PHOSPHOR BRONZE | Ag-PLATED | 1 | | MODEL: PJ-320 | | SCALE: 1:1 | ROHS COMPLIANT | CHK'D | |
| 2 | 1#CONTACT FOOT | PHOSPHOR BRONZE | Ag-PLATED | 1 | | HAOYU(HONGKONG)LIMITED | | | | APPD | |
| 1 | HOUSING | PBT | BLACK | 1 | | 皓宇(香港)有限公司 | | | | | |
| | | | | | | HAOYU(HONGKONG)LIMITED | | | | | |