


NOTE:

1. Rating:DC12V 50mA;
2. Contact Resistance:100mΩ Max;
3. Insulation Resistance:100MΩ Min;
4. Withstanding Voltage:AC250V For 1 Minute;
5. Life Cycle:100,000 Cycle Min;
7. Travel:0.25±0.1mm.



Operating Force	A	100±30gf
	B	130±30gf
	C	160±30gf
	D	200±50gf
	E	250±50gf
	F	300±50gf

H	X
4.3	3.15
5.0	3.85
5.5	4.35
6.0	4.85
7.0	5.85
7.3	6.15
7.5	6.35
8.0	6.85
8.5	7.35
9.0	7.85
9.5	8.35
10.0	8.85
11.0	9.85
12.0	10.85
13.0	11.85
14.0	12.85
14.5	13.35
15.0	13.85
15.5	14.35
16.0	14.85
17.0	15.85

					TOLERANCE UNLESS SPECIFIED							
					UP TO 5mm:±0.1	ANGULAR ±1°						
					ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS	BY	APPD	
5	SHRAPNEL	PBS	2	AG-PLATED	TITLE:TACT SWITCH			UNIT : MM	ROHS COMPLIANT	DWN		
4	TERMINAL	BRASS	2	AG-PLATED	MODEL: TC-00100-050E			SCALE: 1:1	CHK'D			
3	COVER	SPCC	1	SN-PLATED	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司						APPD	
2	BUTTON	PPA	1								PRO.AGL:	
1	HOUSING	PA66	1									
NO.	PART NAME	MATERIAL	QTY	FINISHING								