


RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05



注: B:黑色胶舌 SU: 外壳为不锈钢

				TOLERANCE UNLESS SPECIFIED							
				UP TO 5mm:±0.1	ANGULAR						
				ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS		BY	APPD
3	CONTACT	BRASS	1	Au/Ni PLATED	TITLE: MICRO USB JACK		UNIT : MM	ROHS	DWN		
2	HOUSING	LCP	1		MODEL: USB-111-B-SU B型有柱		SCALE: 1:1	COMPLIANT	CHK'D		
1	SHELL	SUS	1	Sn/Ni PLATED	HAOYU(HONGKONG) LIMITED				APPD		
NO.	PART	NAME	MATERIAL	QTY	FINISHING	皓宇(香港)有限公司		PRO.AGL:		REV :A0	