RoHS

COMPLIANT

HALOGEN FREE


GREEN

(5-2008)



Vishay Semiconductors

Bidirectional Symmetrical (BiSy) Single Line ESD Protection Diode in Silicon Package



MARKING (example only)



1 = year code Open circle = month code and pin 1 XY = type code

DESIGN SUPPORT TOOLS AVAILABLE



FEATURES

- Ultra compact CLP0603 package
- Low package height < 0.3 mm
- 1-line ESD protection
- Working range ± 3.3 V
- Low leakage current < 0.1 μA
- Low load capacitance C_D < 14 pF
- ESD immunity acc. IEC 61000-4-2
 ± 30 kV contact discharge
 - ± 30 kV air discharge
- Lead plating: Au (e4)
- Lead material: Ni
- Topside coating
- e4 precious metal (e.g. Ag, Au, NiPd, NiPdAu) (no Sn)
- Material categorization: for definitions of compliance please see <u>www.vishav.com/doc?99912</u>

ORDERING INFORMATION						
	ENVIRONMENTAL AND QUAL	PACKAGING CODE				
PART NUMBER (EXAMPLE)	RoHS-COMPLIANT + LEAD (Pb)-FREE TERMINATIONS	GOLD PLATED	15K PER 7" REEL (8 mm TAPE)	ORDERING CODE (EXAMPLE)		
	GREEN		15K/BOX = MOQ			
VCUT03E1-SD0-	G	4	-08	VCUT03E1-SD0-G4-08		

PACKAGE DATA							
DEVICE NAME	PACKAGE NAME	TYPE CODE	WEIGHT	SOLDERING CONDITIONS			
VCUT03E1-SD0	CLP0603-2L	3E	0.12 mg	Peak temperature max. 260 °C Reflow soldering according JEDEC® STD-020			

ABSOLUTE MAXIMUM RATINGS						
PARAMETER	TEST CONDITIONS	SYMBOL	VALUE	UNIT		
Peak pulse current	acc. IEC 61000-4-5, 8/20 µs/single shot	I _{PPM}	6	А		
Peak pulse power	Pin 1 to pin 2 acc. IEC 61000-4-5; t _p = 8/20 μs; single shot	P _{PP}	78	W		
ESD immunity	Contact discharge acc. IEC 61000-4-2; 10 pulses	V	± 30	kV		
	Air discharge acc. IEC 61000-4-2; 10 pulses	— V _{ESD}	± 30			
Operating temperature	Junction temperature	TJ	-55 to +150	°C		
Storage temperature		T _{stg}	-55 to +150	°C		

CUT THE SPIKES WITH VCUT03E1-SD0

The VCUT03E1-SD0 is a Bidirectional and Symmetrical (BiSy) ESD protection device which clamps positive and negative overvoltage transients to ground. Connected between the signal or data line and the ground the VCUT03E1-SD0 offers a high isolation (low leakage current, low capacitance) within the specified working range. Due to the short leads and small package size of the tiny CLP0603 package the line inductance is very low, so that fast transients like and ESD strike can be clamped with minimal over- or undershoots.

ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITIONS/REMARKS	SYMBOL	MIN.	TYP.	MAX.	UNIT	
Protection paths	Number of lines which can be protected	nes which can be protected N _{channel}		1	lines		
Reverse stand-off voltage	Max. reverse working voltage	V_{RWM}	-	-	3.3	V	
Reverse voltage	at I _R = 0.1 μA	V _R 3.3 -		-	V		
Reverse current	at V _{RWM} = 3.3 V	I _R	-	-	0.1	μΑ	
Reverse breakdown voltage	at I _R = 1 mA	V_{BR}	6.5	8	9	V	
De consideration disco	at I _{PP} = 1 A	V _C	-	8.8	10	V	
Reverse clamping voltage	at I _{PP} = I _{PPM} = 6 A	V _C	-	11	13	V	
0	at V _R = 0 V; f = 1 MHz	C _D	-	13	14	pF	
Capacitance	at V _R = 2.5 V; f = 1 MHz	C _D	-	11	-	pF	
Clamping voltage	Transmission Line Pulse (TLP); $t_p = 100 \text{ ns}$ $I_{TLP} = 8 \text{ A}$	V _{C-TLP}	-	9.8	-	V	
Clamping voltage	Transmission Line Pulse (TLP); $t_p = 100 \text{ ns}$ $I_{TLP} = 16 \text{ A}$	V _{C-TLP} - 11 -		-	V		
Dynamic resistance	Transmission Line Pulse (TLP); $t_p = 100 \text{ ns}$	R _{DYN}	-	0.15	-	Ω	

TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 1 - ESD Discharge Current Wave Form acc. IEC 61000-4-2 (330 Ω /150 pF)




Fig. 2 - 8/20 µs Peak Pulse Current Wave Form acc. IEC 61000-4-5




Fig. 3 - Typical Capacitance C_D vs. Reverse Voltage V_R




Fig. 4 - Typical Reverse Voltage V_R vs. Reverse Current I_R




Fig. 5 - Typical Peak Clamping Voltage V_C vs. Peak Pulse Current I_{PP}




Fig. 6 - Typical Clamping Performance at 8 kV Contact Discharge acc. IEC 61000-4-2




Fig. 7 - Typical Clamping Performance at 8 kV Contact Discharge acc. IEC 61000-4-2






Fig. 8 - Typical Clamping Voltage at 100 ns Transmission Line Pulse





PACKAGE DIMENSIONS in millimeters (mils): CLP0603-2L





Package = chip dimensions in mm [mils]





	Millimeters			mils		
	min.	nom.	max.	min.	nom.	max.
Α	0.25	0.28	0.30	9.84	11.02	11.81
A1	0.01	0.01	0.02	0.39	0.39	0.79
A2	0.24	0.27	0.28	9.45	10.63	11.02
b	0.22	0.25	0.28	8.66	9.84	11.02
D	0.27	0.30	0.33	10.62	11.81	12.99
E	0.57	0.60	0.63	22.44	23.62	24.80
е		0.40			15.75	
e1		0.25			9.84	
L	0.12	0.15	0.18	4.72	5.91	7.09


22941


2 terminal leadless package (CLP) Document no.: S8-V-3906.04-023 (4) Created - Date: 22. Nov. 2010 Rev.8 - Date: 11. Nov. 2016

Footprint and soldering recommendation:

please see Application Note: www.vishay.com/doc?85917

CARRIER TAPE in millimeters: **CLP0603-2L**






Cummulative tolerances of 10 sprocket holes is +/-0.2mm

22591 Document no. S8-V-3906.04-0025 (4) Created - Date: 22. Nov. 2010

ORIENTATION IN CARRIER CLP0603-2L



22607

Orientation in Carrier Tape (CLP0603) S8-V-3906.04-026 (4) 22.10.2010



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.