



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material:Phosphoric bronze Tin-plated
- 8、Applicable Wire Sizes:AWG#22~28#

GENREL TOLERANCE		制图 DRAWING	钱岳生	料号 PART NO.	HC-XA-T	版本 REV.	A
X.±0.25	X.*±2'		2013、07、01		品名 TITLE	XA端子	页次 SHEET
.X±0.20	.X*±1'		审核 CHECK	张名	客户料号 CUTL NO.		
.XX±0.15	.XX*±0.5'		核准 APPROVAL	张名	2013、07、03		
.XXX±0.10	.XXX*±0.5'	单位 UNITS	MM	比例 SCALE	1:1	深圳市华灿天禄电子有限公司	