



Voidless Hermetically Sealed Unidirectional Transient Voltage Suppressors

Qualified per MIL-PRF-19500/551

*Qualified Levels:
JAN, JANTX, and
JANTXV*

DESCRIPTION

This surface mount series of 500 watt voidless hermetically sealed unidirectional Transient Voltage Suppressors (TVS) are military qualified to MIL-PRF-19500/551 and are ideal for high-reliability applications where a failure cannot be tolerated. Working peak “standoff” voltages are available from 5.0 to 51.6 volts. They are very robust, using a hard glass casing and internal Category 1 metallurgical bonds. These devices are also available in axial-leaded packages for thru-hole mounting.

Important: For the latest information, visit our website <http://www.microsemi.com>.

FEATURES

- Surface mount equivalent of JEDEC registered 1N6461 thru 1N6468 series.
- Available as 500 watt peak pulse power (P_{PP}).
- Working peak “standoff” voltage (V_{WM}) from 5.0 to 51.6 volt.
- High surge current and peak pulse power provides transient voltage protection for sensitive circuits.
- Triple-layer passivation.
- Internal “Category 1” metallurgical bonds.
- Voidless hermetically sealed glass package.
- JAN, JANTX, and JANTXV qualifications available per MIL-PRF-19500/551. Other screening in reference to MIL-PRF-19500 is also available.
(See [part nomenclature](#) for all available options.)
- RoHS compliant versions available (commercial grade only).


APPLICATIONS / BENEFITS

- Military and other high-reliability applications.
- Extremely robust construction.
- ESD and EFT protection per IEC61000-4-2 and IEC61000-4-4 respectively.
- Protection from secondary effects of lightning per select levels in IEC61000-4-5.
- Square-end-cap terminals for easy placement.
- Nonsensitive to ESD per MIL-STD-750 method 1020.
- Inherently radiation hard as described in Microsemi “[MicroNote 050](#)”.

MAXIMUM RATINGS @ 25 °C


Parameters/Test Conditions	Symbol	Value	Unit
Junction and Storage Temperature	T_J and T_{STG}	-55 to +175	°C
Thermal Resistance, Junction to Endcap	$R_{\theta JEC}$	20	°C/W
Forward Surge Current @ 8.3 ms half-sine	I_{FSM}	80	A
Forward Voltage @ 1 Amp	V_F	1.5	V
Peak Pulse Power @ 10/1000 μ s	P_{PP}	500	W
Reverse Power Dissipation ⁽¹⁾	P_R	2.5	W
Solder Temperature @ 10 s		260	°C

Notes: 1. Derate at 50 mW/°C (see [figure 4](#)).



**“B” SQ-MELF
Package**

Also available in:

“B” Package
(axial –leaded)
 [1N6461 - 1N6468](#)

MSC – Lawrence

6 Lake Street,
Lawrence, MA 01841
Tel: 1-800-446-1158 or
(978) 620-2600
Fax: (978) 689-0803

MSC – Ireland

Gort Road Business Park,
Ennis, Co. Clare, Ireland
Tel: +353 (0) 65 6840044
Fax: +353 (0) 65 6822298

Website:

www.microsemi.com

MECHANICAL and PACKAGING

- CASE: Hermetically sealed voidless hard glass with tungsten slugs.
- TERMINALS: Axial-leads are tin/lead over copper. RoHS compliant matte-tin is available for commercial grade only.
- MARKING: Body paint and part number.
- POLARITY: Cathode band.
- TAPE & REEL option: Standard per EIA-296. Contact factory for quantities.
- WEIGHT: Approximately 750 milligrams.
- See [Package Dimensions](#) on last page.

PART NOMENCLATURE

JAN 1N6461 US e3

Reliability Level

JAN = JAN Level
 JANTX = JANTX Level
 JANTXV = JANTXV Level
 CDS (reference JANS)
 Blank = commercial

JEDEC type number

See [Electrical Characteristics](#) table

RoHS Compliance

e3 = RoHS compliant ([available on commercial grade only](#))
 Blank = non-RoHS compliant

MELF Package
SYMBOLS & DEFINITIONS

Symbol	Definition
$\alpha_{V(BR)}$	Temperature Coefficient of Breakdown Voltage: The change in breakdown voltage divided by the change in temperature expressed in %/°C or mV/°C.
$V_{(BR)}$	Breakdown Voltage: The voltage across the device at a specified current $I_{(BR)}$ in the breakdown region.
V_{WM}	Rated working standoff voltage: The maximum-rated value of dc or repetitive peak positive cathode-to-anode voltage that may be continuously applied over the standard operating temperature.
I_D	Standby Current: The current through the device at rated stand-off voltage.
I_{PP}	Peak Impulse Current: The maximum rated random recurring peak impulse current or nonrepetitive peak impulse current that may be applied to a device. A random recurring or nonrepetitive transient current is usually due to an external cause, and it is assumed that its effect will have completely disappeared before the next transient arrives.
V_C	Clamping Voltage: The voltage across the device in a region of low differential resistance during the application of an impulse current (I_{PP}) for a specified waveform.
P_{PP}	Peak Pulse Power. The rated random recurring peak impulse power or rated nonrepetitive peak impulse power. The impulse power is the maximum-rated value of the product of I_{PP} and V_C .

ELECTRICAL CHARACTERISTICS

TYPE	MINIMUM BREAK DOWN VOLTAGE $V_{(BR)}$ @ $I_{(BR)}$	BREAKDOWN CURRENT $I_{(BR)}$	RATED WORKING STANDOFF VOLTAGE V_{WM}	MAXIMUM STANDBY CURRENT I_D @ V_{RWM}	MAXIMUM CLAMPING VOLTAGE V_C @ 10/1000 μs	MAXIMUM PEAK IMPULSE CURRENT I_{PP}		MAXIMUM TEMP. COEF. OF $\alpha V_{(BR)}$
						@ 8/20 μs	@ 10/1000 μs	
	Volts	mA	V (pk)	μA	V (pk)	A (pk)	A (pk)	%/°C
1N6461US	5.6	25	5	3000	9.0	315	56	-0.03, +0.045
1N6462US	6.5	20	6	2500	11.0	258	46	+0.060
1N6463US	13.6	5	12	500	22.6	125	22	+0.085
1N6464US	16.4	5	15	500	26.5	107	19	+0.085
1N6465US	27.0	2	24	50	41.4	69	12	+0.096
1N6466US	33.0	1	30.5	3	47.5	63	11	+0.098
1N6467US	43.7	1	40.3	2	63.5	45	8	+0.101
1N6468US	54.0	1	51.6	2	78.5	35	6	+0.103


GRAPHS


FIGURE 1
Peak Pulse Power vs Pulse Time




FIGURE 2
10/1000 μs Current Impulse Waveform

GRAPHS




FIGURE 3
8/20 μs Current Impulse Waveform






FIGURE 4
Derating Curve

PACKAGE DIMENSIONS


	Inch		Millimeters	
	Min	Max	Min	Max
BD	0.137	0.148	3.48	3.76
BL	0.200	0.225	5.08	5.72
ECT	0.019	0.028	0.48	0.71
S	0.003	---	0.08	---

NOTES:

1. Dimensions are in inches.
2. Millimeter equivalents are given for information only.
3. Referencing to dimension S, minimum clearance of glass body to mounting surface on all orientations.
4. Dimensions are pre-solder dip.
5. In accordance with ASME Y14.5M, diameters are equivalent to Φ x symbology.

PAD LAYOUT


	INCH	MILLIMETERS
A	0.288	7.32
B	0.070	1.78
C	0.155	3.94

Note: If mounting requires adhesive separate from the solder, an additional 0.080 inch diameter contact may be placed in the center between the pads as an optional spot for cement.