
Product Search Data Sheet



SCA3300-D01

In Production RoHS REACH

Appearance & Shape





Packaging Information

Packaging	Specifications	Standard Packing Quantity
-1	330mm Embossed Tape	100

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



Note: This datasheet may be out of date. Please download the latest datasheet of SCA3300-D01 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=SCA3300-D01



SCA3300-D01

Note: This datasheet may be out of date. Please download the latest datasheet of SCA3300-D01 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=SCA3300-D01



Output TypeSPIAxis3Maximum Range±1.5g/±3g/±6g/Supply Voltage3.3VOffset Temp. CharacteristcX,Y±10mg Z±15mgAmplitude Response88/10HzMass0.31g

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



2 of 2