


# RoHS




## SPECIFICATIONS

Rated Current: 3.0AMP  
 Contact Resistance: 20mΩ Max  
 Withstand Voltage: 1000V AC/DC  
 Insulation Resistance: 1000MΩ Min  
 Operation Temperature: -40°C to +105°C

Contact Material: Brass  
 Contact Plating: Au Over Ni  
 Insulator Material: Polyester (UL94V-0)  
 Standard: PBT  
 Max. Processing Temp: 180°C for 30-60 seconds  
 (200°C for 10 seconds)



Recommended P.C.B Layout (Top Side)  
 (PCB BOARD TOLERANCE ± 0.05)



Dimension antitheses list			
ITEM	PC	H	
Alternate	3.00	22.10	

深圳市连盛精密连接器有限公司

PART NO.

**BH-00113---B0023**

TITLE:

2.54Box 3H=8.8+2X2.5 12P DIP

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION		DRAW		SCALE		FIT	PART NO.
				X.X	±0.30	CHECK	UNIT	mm	SIZE		
A0	2012.10.05	NEW DRAWING		X.XX	±0.20		A4	1/1			
1				X.XXX	±0.10	APPROVE		1/1			
				Angle	±3°						
				DIM	TOL						